



3M Science.
Applied to Life.™



3M Automotive Aftermarket

3M Blue Abrasives.
The upgrade you've
been waiting for.



Blue goes head to head with any abrasive in its class.

Best-in-class value leaves the competition in the dust — literally.

3M Blue Abrasive Multi-hole Discs are specially designed to improve anti-loading and boost dust extraction for improved productivity and a cleaner work environment. The multi-hole pattern captures dust, keeping the abrasive open for a faster cut and consistent performance throughout the life of the disc.

3M™ Hookit™ universal multi-hole pattern with alignment guide:

- Reduces loading for improved performance
- Improves dust extraction efficiency compared to 6 and 7 hole patterns
- Aligns with majority of dust extraction back-up pads

Go Blue for Body Repair.

Cuts fast with consistent results.


3M™ Blue Abrasives are engineered with a ceramic mineral blend that cuts through paint and body filler with consistent results every time.

Available in Hookit™ Attachment System.


3M™ Blue Abrasives can be used with Hookit™ attachments.

Get the job ready for primer!

Use 3M™ Blue Abrasives to featheredge around the repair area to finish the body work and get ready for paint prep.



| 3M™ Hookit™ Attachment | | | | | | |
|--|--------------|--------------|--------------|--------------|--------------|--------------|
| Grade | 40 | 80 | 120 | 150 | 180 | 220 |
| 150mm 50 Discs/Box 4 Boxes/Case | 36170 | 36172 | 36174 | 36175 | 36176 | 36177 |




150mm 3M™ Hookit™ Blue
Abrasive Disc

3M Blue Abrasives are your go-to workhorse for the entire shop.

3M's engineered ceramic mineral blend delivers best-in-class cut and life. An anti-loading design and the available universal multi-hole pattern extend the life of the abrasive for consistent performance. A full line of discs is available in an array of grades for use throughout the repair process. Available in the 3M™ Hookit™ attachment system — from body repair to paint prep, BLUE is all you need.

Designed for performance:

- **Engineered ceramic mineral blend** provides best-in-class performance using exactly the right balance of ceramic grain and premium aluminum oxide
- **Anti-loading coating** improves disc life
- **Upgraded resins** improve durability and finish



Alignment line to quickly place disc on backup pad

150mm 3M™ Hookit™ Blue Abrasive Disc

Go Blue for Paint Prep.

Great performance and finish in finer grades.


3M™ Blue Abrasives are engineered to deliver great performance and finish in the finer grades to make paint prepping fast and consistent every time.

Available in discs.

3M™ Blue Abrasives discs available in 150mm in a range of grades for primer sanding.

Complete line of abrasives for all your paint prep needs.

Use the full range of 3M™ Blue Abrasive discs to prepare for the paint booth. Whether primer sanding or blend prepping, hand or machine sanding, 3M Blue Abrasives will get the job done!



Use 3M™ Masking Products to prepare the sanding area for primer.

233+



Reduce chance of burn through on edges, blends and bumpers with 3M™ Flexible Abrasive Sheets.

PN 34337 PN 34340



3M™ Accuspray™ Spray Gun and 3M™ PPS™ cover all your coating and painting needs.

HG14


| | 3M™ Hookit™ Attachment | | | | | |
|---------------------------------------|------------------------|-------|-------|-------|-------|-------|
| Grade | 240 | 320 | 400 | 500 | 600 | 800 |
| 150mm 50 Discs/Box 4 Boxes/Case | 36178 | 36180 | 36181 | 36182 | 36183 | 36184 |

3M Abrasive Disc Range.

3M™ Cubitron™ II Abrasives: For the Body Shop

3M™ Cubitron™ II 150mm Discs are 3M's highest performing abrasives and have a revolutionary advancement in automotive abrasive technology featuring triangular shaped ceramic mineral. As the triangular shaped grain wears, it continually fractures to form sharp points that slice through the substrate, wear evenly and provide extra-long life and consistency.


- Cuts 30% faster than premium abrasives
- Lasts up to twice as long
- Delivers finer, more uniform finish
- Requires less pressure



3M™ Clean Sand™ Abrasives: For the Paint Shop

3M™ Purple abrasives are 3M's best performing class of abrasives. Power packed with 3M innovation these discs sand faster to improve technician productivity and reduce cycle time. The consistent finish you can count on, results in higher-quality repairs reducing rework.

These long-lasting abrasives reduce material consumption. The reusable 3M™ Hookit™ attachment system allows technicians to utilize the entire life of the disc, resulting in less shop waste.




3M™ Blue Abrasives

3M™ Blue Abrasives are 3M's newest edition to the mid/high performance tier and are designed to deliver best-in-class performance every day. 3M's engineered ceramic mineral blend delivers best in class cut and life specifically designed to improve anti-loading and boost dust extraction.

- Engineered ceramic mineral blend
- Anti-loading coating
- Upgraded resins

With a full range of grades designed to meet the modern body shop's needs, 3M Blue abrasives are the upgrade you've been waiting for.




3M™ Gold Abrasives

3M™ Gold Abrasives are the standard that shops have turned to for quality, performance and durability for over 25 years.

Our Gold Abrasives are precision coated with high quality minerals and resins to deliver longer-lasting discs that cut through a variety of surfaces - including paint, primer, fiberglass, metal and SMC.

3M™ Gold Abrasives produce uniform, consistent finishes and are available in the Hookit™ attachment system for convenience and reuse. When job quality and productivity matter most, turn to the abrasives that shops have relied on year after year.



Best

Better

Good

3M Blue Abrasive. Upgrade your old abrasive today.

With optimized abrasive technology, best-in-class cut performance and durability, and a complete abrasive line offering, Blue abrasives are the upgrade you've been waiting for.

3M gives you exactly what you need to simplify the repair process, achieve consistent results and improve your bottom line, every day.



Learn more about our complete system of collision repair solutions — abrasives, fillers, adhesives, coatings, paint and masking solutions at **3M.com.au/AAD**



**3M Automotive
Aftermarket Division**
Building A, 1 Rivett Rd
North Ryde, NSW, 2113

Phone 136-136
Web www.3M.com.au/aad



Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

3M, Accuspray, Hookit and PPS are trademarks of 3M Company. Please recycle. © 3M 2016. All rights reserved. 60-4402-7927-5