

Are you protecting your repairs against corrosion?

With today's ever evolving substrates being used in automotive construction, industry organisations and OEMs alike specify the use of cavity wax to prevent corrosion.

3M™ Cavity Wax Plus 08852 is a simple and effective way to ensure corrosion protection, one of the most important parts of automotive repairs.

1,500 hours salt spray results

Actual panel test results ASTM B117 1,500 hours.



Without protection



**3M™ Cavity Wax Plus 08852
(3 coats)**



Are you taking the steps to prevent corrosion today?



According to leading industry bodies the use of cavity wax is recommended post repair. In addition, numerous OEMs call for the use of a corrosion protection product during vehicle repair.

3M™ Cavity Wax Plus 08852

Non-hardening corrosion protection for internal cavities in a convenient aerosol can.

- Self-healing, corrosion protection for inner body panels, frame rails and structural enclosures.
- When used according to directions 3M™ Cavity Wax Plus delivers the right amount of flow and wicking, providing consistent and uniform protection for your repair.
- Eliminates the need for using antiquated and messy bulk spray technology to apply corrosion protection to a vehicle.
- Provides access to inner body structures with tight tolerances.



3M™ Cavity Wax Plus

Part No.	Size	Product	Case Qty.
08852	511g aerosol	3M™ Cavity Wax Plus	4

3M™ Cavity Wax Plus Applicator Wand Kit 08851

Protect hard-to-reach places.

- 3M™ Cavity Wax Plus Applicator Wand Kits provide three great options (203mm, 610mm and 864mm) to access hard-to-reach places when applying corrosion protection coatings (inner rocker panels, dog legs, unside constructions, frame rails, etc.).
- 610mm and 864mm wands provide a uniform 360 degree spray pattern to ensure that you are maximising coverage with each application.
- 203mm tube delivers a powerful stream of material to flood joints and seal them from corrosive elements.

3M™ Cavity Wax Plus Applicator Wand Kit

Part No.	Size	Product
08851	203mm, 610mm & 864mm tubes	3M™ Cavity Wax Plus Applicator Wand Kit

3m.co.nz/aad



3M Automotive
Aftermarket Division
94 Apollo Drive
Rosedale, Auckland, 0632

Phone 0800 362 886
Web www.3m.co.nz/aad

Learn more about our complete system of body repair solutions at 3m.co.nz/aad

