



3M™ Paint Application

# Part Number Reference Guide

Solutions for every paint job.



## Experience a high-performance finish with *paint savings.*

As every painter knows, once paint has been mixed, it's sold. You either use it or lose it, which can cut into your bottom line. What if we told you mixing less paint yet getting the same or better coverage was possible? With the 3M™ Performance Spray Gun, that possibility can become reality. It's superior transfer efficiency in the palm of your hand. Don't cut down on your efficiency – start spraying the smart way.



### Precision Performance

Third-party tested, painter approved. It's everything you expect from your best spray gun — just smarter. Spray a full range of high-performance automotive coatings with one of the highest transfer efficiencies for industry leading spray guns.



### Cleans in Seconds

Innovative quick-change replaceable nozzle technology means cleanup can be as simple as a twist and a wipe. And every time you put on a fresh nozzle, it's like getting a brand-new spray gun.



### Faster Cycle Times



Integrated system with 3M™ PPS™ Series 2.0 Spray Cups and replaceable nozzles delivers the fastest changeovers in the industry, which adds up to faster cycle times and more time in the zone.




### Lightest in the World


Made from an impact-resistant composite material, it's the lightest spray gun in the world. All to enhance your comfort without sacrificing performance or durability.





# 3M™ Performance Spray Gun

3M™ Performance Spray Gun System	UPC	Part #	Qty/Case	Description
<b>3M™ Performance Spray Gun System with 3M™ PPS™ Series 2.0 System</b> 	04054596831346	26778	1 Kit/Case	<div>For Gravity Application</div> <p><u>Kit includes:</u></p> <ul style="list-style-type: none"> <li>1 – Performance Spray Gun</li> <li>1 – Air Control Valve</li> <li>1 – Locking Collar</li> <li>15 – Gravity Atomizing Heads (5 each of 1.2, 1.3, 1.4)</li> <li>1 – 3M™ PPS™ Series 2.0 System</li> </ul>
<b>3M™ Performance Spray Gun</b> 	00051131268326	26832	4/Case	<p><u>Includes:</u></p> <ul style="list-style-type: none"> <li>1 – Performance Spray Gun</li> <li>1 – Air control valve</li> </ul> <p>Lightweight, impact-resistant body made from advanced composite material quickly converts between pressure-fed systems and gravity-fed 3M™ PPS™ Series 2.0 Spray Cup System. Easy to change, replaceable nozzles range from 1.1 – 2.0. Designed for comfort. The simple, innovative design means fewer parts to maintain or rebuild.</p>

H/O Products	UPC	Part #	Size	Qty/Case	Description
 <b>3M™ PPS™ Series 2.0 Type H/O Pressure Cup</b>	00051131261211	26121	Midi (13.5 fl. oz.)	2/Case	A pressurized (H/O) hard cup and collar set that supports and holds 3M™ PPS™ Series 2.0 lids and flexible liners. This product is intended for use in place of metal cups on most pressure spray guns.
	00051131261242	26124	Large (28 fl. oz.)		
<b>3M™ Performance Spray Gun H/O Conversion Pack</b>	00051131268371	26837	—	4/Case	Equips the 3M™ Performance Spray Gun to use 3M™ PPS™ Series 2.0 Type H/O Pressure Cups. This upgrade adds an air pressure port to the gun for spraying high-viscosity coatings.

# 3M™ Performance Spray Gun

3M™ Performance Gravity System	UPC	Part #	Color	Size	Qty/Case	Description
<b>3M™ Performance Gravity HVLP Atomizing Head Refill</b>  	00051131267091	26709	O White	0.9	25/Case	Used for spraying a wide range of industrial and automotive coatings, including high-viscosity coatings, sprayable fillers, high-build primers, primer surfacers, sealers, single-stage top coats, solvent-based paints, waterborne paints and clear coats.
	00051131267121	26712	Blue	1.2	25/Case	
	00051131267138	26713	Green	1.3	25/Case	
	00051131267145	26714	Orange	1.4	25/Case	
	00051131267169	26716	Purple	1.6	25/Case	
	00051131267183	26718	Ø Clear	1.8	25/Case	
	00051131267206	26720	Red	2.0	25/Case	
<b>3M™ Performance Gravity HVLP Atomizing Head Refill Kit</b>	00051131267305	26730	Blue Green Orange Red Purple Ø Clear	1.2 – 2.0	5 Kits/Case	<b>Kit includes:</b> Six Atomizing Heads One of each size: 1.2, 1.3, 1.4, 1.6, 1.8, 2.0

Accessories and Replacement Parts	UPC	Part #	Qty/Case	Description
 <b>O-Ring Kit</b>	00051131268418	26841	4/Case	3M™ Performance Spray Gun Replacement O-Ring Kit.
 <b>Locking Collar</b>	00051131268357	26835	20/Case	Ensures a solid connection between the 3M™ Performance Spray Gun and atomizing heads.
 <b>Spray Gun Needle</b>	00051131268388	26838	1/Case	Use replacement needle when spray gun needle is damaged, bent or leaks.
 <b>Rebuild Kit</b>	00051131268401	26840	4/Case	Includes exterior replacement parts, all required interior seals, springs, screws and parts. Instruction manual provides specific details on how to rebuild.





# 3M™ PPS™ Series 2.0 Spray Cup System

## Paint shop solutions for every painter.

A revolution in painting productivity and quality started when we invented the 3M™ PPS™ paint preparation system – the world's first disposable paint cup system. With a constant mission of improving our paint shop solutions in the market, we then invented 3M™ PPS™ Series 2.0 – all to make your painting process more efficient and cleaner, providing the conveniences you demand in a busy shop.

Now, we're bringing you another painter-approved solution – the 3M™ PPS™ Series 2.0 Vented Spray Cup System. A ready-to-use system that gives you the results you expect from a premium vented cup with a consistent material flow each time. Whether you use our lined or vented cup options, you can be confident in the quality of your paint job – no matter which system you choose.



3M™ PPS™ Series 2.0 Lined Spray Cup System		UPC	Part #	Size	Qty/Case	Description
 <b>3M™ PPS™ Series 2.0 Spray Cup System Kit 200 Micron</b> <div>Kit</div>		00051131260245	26024	Large (28 oz., 850mL)	1 Kit/Case	Highest performing disposable spray cup system for mixing/measuring, filtering, spraying in any direction (360° spray rotation) and protecting coatings not in use.  <u>Kit contains:</u> 50 lids and liners, 32 sealing plugs, 1 reusable hard cup.
		00051131260009	26000	Standard (22 oz., 650mL)		
		00051131261129	26112	Midi (13.5 oz., 400mL)		
		00051131261143	26114	Mini (6.8 oz., 200mL)		
		00051131260283	26028	Micro (3 fl. oz., 90mL)		
 <b>3M™ PPS™ Series 2.0 Spray Cup System Kit 125 Micron</b> <div>Kit</div>		00051131263253	26325	Large (28 oz., 850mL)		
		00051131263017	26301	Standard (22 oz., 650mL)		
		00051131263123	26312	Midi (13.5 oz., 400mL)		
		00051131263147	26314	Mini (6.8 oz., 200mL)		
		00051131260283	26328	Micro (3 fl. oz., 90mL)		

For Industrial/Occupational use only.




# 3M™ PPS™ Series 2.0 Spray Cup System

3M™ PPS™ Series 2.0 Spray Cup System		UPC	Part #	Size	Filter	Qty/Case	Description
	<b>3M™ PPS™ Series 2.0 Spray Cup System UV Kit</b>	4054596313415	26710	Standard (22 oz., 650mL)	200 Micron	1 Kit/Case	Protects daylight sensitive materials — like UV-curing primers, sealers, base and clear coats — and helps you measure, mix, filter and spray with ease.
	UV Kit	4054596313439	20730	Standard (22 oz., 650mL)	125 Micron		<u>UV Kit contains:</u> 50 black lids and liners, 32 black sealing plugs, 1 reusable hard cup.
	<b>3M™ PPS™ Series 2.0 Spray Cup System Starter Kit</b>	00051131261723	26172	Standard (22 oz., 650mL)	200 Micron	2 Kits/Case	Convenient way to get started with our 3M™ PPS™ Series 2.0 Spray Cup System. Kits are available in Midi and Standard sizes, excellent for most mid-range repairs.
	Starter Kit	00051131261709	26170	Midi (13.5 oz., 400mL)			<u>Starter Kit contains:</u> 6 lids and liners, 16 sealing plugs, 1 reusable hard cup.
	<b>3M™ PPS™ Series 2.0 Spray Cup System 12-Pack Refill Kit</b>	00051131261730	26173	Standard (22 oz., 650mL)	200 Micron	2 Kits/Case	Simple, cost-effective way to keep our 3M™ PPS™ Series 2.0 Spray Cup System stocked and ready. Kits are available in Midi and Standard sizes, excellent for most mid-range repairs.
	Refill Kit	00051131261716	26171	Midi (13.5 oz., 400mL)			<u>Refill Kit contains:</u> 12 lids and liners, 16 sealing plugs.
	<b>3M™ PPS™ Series 2.0 Lid</b>	00051131262003	26200	Large/Standard	200 Micron	25/Case	Features quarter-turn lid locking system, helping eliminate cross-threading and paint build-up. Full-diameter filters built into every lid maximize filtration and fluid flow. Domed design and wide spout allow up to 3 fl. oz. (90mL) to be held below the filter, reducing inconsistent spray due to air-entrapment and sputter.
		00051131262041	26204	Midi/Mini/Micro	125 Micron		
		00051131261990	26199	Large/Standard			
		00051131262058	26205	Midi/Mini/Micro			
		00051131261501	26150	Large/Standard Type H/O Pressure Lid	200 Micron		
	<b>3M™ PPS™ Series 2.0 Cup</b>	00051131260238	26023	Large (28 oz., 850mL)	—	8 Cups/Box	Hard cups designed specifically for 3M™ PPS™ Series 2.0. Mix ratios built into every hard cup — no need for separate inserts. ‘Max Fill’ notation allows users to fit maximum amount of fluid in cup.
		00051131260016	26001	Standard (22 oz., 650mL)			
		00051131261228	26122	Midi (13.5 oz., 400mL)			
		00051131261150	26115	Mini (6.8 oz., 200mL)			




For Industrial/Occupational use only.



# 3M™ PPS™ Series 2.0 Spray Cup System

3M™ PPS™ Series 2.0 Spray Cup System		UPC	Part #	Size	Filter	Qty/Case	Description
	<b>3M™ PPS™ Series 2.0 Universal Shaker Core</b>	0005113126458	26458	Fits all lid sizes of 3M™ PPS™ Series 2.0	—	12/Case	Fits on top of the domed lid and fits into the 1/4-turn lid locking system, creating a stable, durable and even surface for clamping cup tightly into paint shakers.
	<b>3M™ PPS™ Series 2.0 Shaker Core and Support Cup Kit</b>	00051131264595	26459	Fits standard and large sizes of 3M™ PPS™ Series 2.0	—	1/Case	Kit creates stable, durable and even surfaces for clamping 3M™ PPS™ Series 2.0 hard cups tightly into paint shakers. The support cup prevents bending or crushing of the hard cup when shaking by redirecting the force of the shaker clamp onto the support cup.
	<b>3M™ PPS™ Series 2.0 Sealing Plug</b>	00021200063084	26432	Fits all lid sizes of 3M™ PPS™ Series 2.0	—	576/Case	Wide, flat design makes a stable base when cups are turned upside down. Excellent for temporary sealing and protection of coatings. Keep filters wet for longer life, fewer lid replacements. Use to seal lid while mixing in paint shakers.

For Industrial/Occupational use only.

Accessories	UPC	Part #	Size / Description	Qty/Case	Description
	00051131162198	16219	Lid Dispenser Fits all sizes 3M™ PPS™ Series 2.0	1/Case	Dispenses all available liner sizes for 3M™ PPS™ Series 2.0. Offers exceptional convenience to access 3M™ PPS™ liners. Keeps liners clean, neat, organized and free from contamination. Top-loading access for reloading 3M™ PPS™ liners. Wall mountable.
	00051131162990	16299	Liner Dispenser Fits all sizes 3M™ PPS™ Series 2.0		
 <div>Low VOC</div>	00051131266896	26689	15 oz. (426g) Aerosol Can	6/Case	Specifically formulated for removing waterborne and solvent-based coatings from metals, plastic and composite surfaces. This low VOC spray gun cleaner meets the requirements of SCAQMD Rule 1171.
	00051131165502	16550	<u>Kit includes:</u> 3M™ SUN GUN™ light with 50 watt bulb, rechargeable battery and charger with power supply	1/Case	Replicate natural sunlight to better match automotive and industrial paint colors. Evaluate damage for better estimates of cost of repair. Locate defects prior to painting vehicle or substrate. Identify imperfections in paint quality. Improve the professionalism of automotive and industrial paint jobs.




# 3M™ PPS™ Series 2.0 Vented Spray Cup System

## Ready-to-go for painters on the go.

When high standards are the expectation, you need equipment that delivers consistent results. Introducing the 3M™ PPS™ Series 2.0 Vented Spray Cup System - bringing the advantages you expect from a premium vented cup with the proven technology of the first disposable spray cup system in the world.

Consistent material flow is a must in a world of demanding cycle times and high-quality finishes. It's a spray cup system that provides easy cleanup with the performance and trust 3M aims to deliver. With pre-installed valves and filters and a thoughtfully-formulated cup design, you can spend more time on the things that matter.





3M™ PPS™ Series 2.0 Vented Spray Cup System		UPC	Part #	Size	Qty/Case		Description		
	<b>3M™ PPS™ Series 2.0 Vented Spray Cup System Kit 200 Micron</b> <div>Kit</div>	04064035086152	26264	Large (32 oz., 950mL)	1 Kit/Case		Ready-to-use vented cup option for painters who prefer vented paint spray cups. These easy-to-use, cups deliver the consistent flow you expect from a vented cup. 3M™ PPS™ 2.0 Vented Cup Kits come with their valves and filters pre-installed. They're ready to start mixing right out of the box.		
		04064035086077	26263	Standard (23.7 oz., 700mL)					
		04064035086053	26262	Midi (13.5 oz., 400mL)					
		04064035085995	26261	Mini (7 oz., 250mL)					
	<b>3M™ PPS™ Series 2.0 Vented Spray Cup System Kit 125 Micron</b> <div>Kit</div>	04064035086176	26164	Large (32 oz., 950mL)					<u>Kit contains:</u> 50 cups and lids, and 32 sealing plugs.
		04064035086091	26163	Standard (23.7 oz., 700mL)					
		04064035086039	26162	Midi (13.5 oz., 400mL)					
		04064035086015	26161	Mini (7 oz., 250mL)					
	<b>3M™ PPS™ Series 2.0 Vented Spray Cup System UV Kit</b> <div>Kit</div>	04064035086114	26260	Standard (23.7 oz., 700mL)	200 Micron	1 Kit/Case	Ready-to-use vented cup option for painters who prefer vented paint spray cups for spraying light-cured coatings.		
		04064035086138	26160		125 Micron			<u>Kit contains:</u> 50 cups and lids, and 32 sealing plugs.	





# 3M™ PPS™ Series 2.0 Vented Spray Cup System



3M™ PPS™ Series 2.0 Vented Spray Cup System		UPC	Part #	Size	Filter	Qty/Case	Description
	<b>3M™ PPS™ Series 2.0 Vented Spray Cup Lid</b>	04064035085827	26265	Large/Standard	200 Micron	50 Lids/ Case	Ready-to-use with 3M™ PPS™ 2.0 Vented Paint Spray Cups. They come with their filters welded in place so there's no time spent assembling. The lids deliver a robust screw-fit connection to cups. The stable 3M™ PPS™ Series 2.0 four-point snap connection means there are no threads to wear out.
		04064035085773	26266	Midi/Mini			
		04064035085865	26165	Large/Standard	125 Micron		
		04064035087562	26166	Midi/Mini			
	<b>3M™ PPS™ Series 2.0 Vented Spray Cup</b>	04064035085940	26364	Large (32 oz., 950mL)	—	50 Cups/ Case	Comes with valves pre-installed so you can start mixing right out of the box. These firm-but-flexible disposable cups allow you to have a clean cup every time with no reused components.
		04064035085902	26363	Standard (23.7 oz., 750mL)			
		04064035085803	26362	Midi (13.5 oz., 400mL)			
		04064035085735	26361	Mini (8.5 oz., 250mL)			

For Industrial/Occupational use only.

Accessories	UPC	Part #	Size / Description	Qty/Case	Description
 <b>3M™ PPS™ Dispensing Rack</b>	00068060533678	26370	Kit Dispenser Fits all sizes of 3M™ PPS™ Series 2.0 Lined and Vented Spray Cup Kits	1/Case	Store up to three boxes of vented cup kits, cups, or lids for easy access. Built from coated steel tubing, this three-tier rack provides durable storage.
 <b>3M™ PPS™ Series 2.0 Vented Shaker Core</b>	00068060533647	26457	Fits all lid sizes of 3M™ PPS™ Series 2.0 Vented Spray Cups	12/Case	Engineered to fit on the dome of 3M™ PPS™ Series 2.0 Vented Spray Cup Lids. Forms a stable clamping surface when placing assembled PPS™ Series 2.0 Vented Cups and Lids in paint shakers.



# 3M™ PPS™, Accuspray™, and Accessories




Accuspray™ ONE Spray Gun System	UPC	Part #	Legacy Part #	Qty/Case	Description
<b>3M™ Accuspray™ ONE Professional Spray Gun Kit with 3M™ PPS™ Series 2.0</b> 	00051131265783	26578	16578	2 Boxes/Case	Combines the simplicity and easy maintenance of our Accuspray™ spray gun with the material-saving, rapid clean-up convenience of PPS™ Series 2.0, our next generation, highest performing disposable spray cup system. Replaceable atomizing heads afford the performance of a new gun, on demand and at a fraction of the cost.
<b>3M™ Accuspray™ ONE Spray Gun System with 3M™ PPS™ Series 2.0 Display Kit</b> 	00051131265806	26580	16580	2 Boxes/Case	This system features the Accuspray™ ONE Spray Gun - a lightweight, composite spray gun body designed to eliminate the complexity of a traditional spray gun. This gun body has been engineered for enhanced durability in automotive and industrial environments. The spray gun uses a series of replaceable, see-through atomizing heads which can be reused 5-10 times and then simply removed and replaced.

Accuspray™ ONE Spray Gun System	UPC	Part #	Color/Size	Legacy Part #	Qty/Case	Description
<b>3M™ Accuspray™ Atomizing Head Refill Pack for 3M™ PPS™ Series 2.0</b> 	00051131266124	26612	Blue, 1.2mm	16615	6 Packs/Case	Designed specifically for use with the 3M™ Accuspray™ ONE and PPS™ Series 2.0 Spray Cup systems. A selection of replaceable heads makes for the incredibly fast, efficient application of low-, medium- and high-viscosity materials from one gun. Technicians simply remove and replace the head for the performance of a new spray gun on demand.
	00051131266131	26613	Green, 1.3mm	16614	6 Packs/Case	
	00051131266148	26614	Orange, 1.4mm	16612	6 Packs/Case	
	00051131266186	26618	Clear, 1.8mm	16611	6 Packs/Case	
	00051131266209	26620	Red, 2.0mm	16609	6 Packs/Case	
<b>3M™ Accuspray™ Atomizing Head Single Blister Pack for 3M™ PPS™ Series 2.0</b> 	00051131265820	26582	Blue, 1.2mm	16582	6 Packs/Case	
	00051131265837	26583	Green, 1.3mm	16583	6 Packs/Case	
	00051131265844	26584	Orange, 1.4mm	16584	6 Packs/Case	
	00051131265851	26585	Clear, 1.8mm	16585	6 Packs/Case	
	00051131265868	26586	Red, 2.0mm	-	6 Packs/Case	



# 3M™ PPS™, Accuspray™, and Accessories

3M™ Accuspray™ HGP Spray Gun System	UPC	Part #	Size	Legacy Part #	Qty/Case	Description
<b>3M™ Accuspray™ Spray Gun System HGP</b> 	00051131165878	16587	-	16587	2 Boxes/Case	Features an HVLP gravity pressurized spray gun body built specifically for applying high viscosity fluids in collision repair. The kit includes an Accuspray™ HGP pressurized spray gun and two each of 1.8 mm and 2.0 mm atomizing heads that allow for full, consistent spray patterns and low overspray.
<b>3M™ PPS™ Type H/O Pressure Cup</b> 	00051131261242	26124	Large	16124	1 Box/Case	Pressurized hard cups and collars to be used with 3M™ PPS™ Series 2.0 spray system. Designed to efficiently spray thick, high viscosity liquids. The all-in-one solution reduces the chance of outside contamination and reduces paint consumption.
	00051131261211	26121	Midi	16121	6 Boxes/Case	

Accessories	UPC	Part #	Size / Description	Qty/Case	Description
<b>3M™ PPS™ Single Spray Gun Holder</b> 	00051131162365	16236	Rack for keeping spray guns used with 3M™ PPS™ Series 2.0 and 3M™ PPS™ (Legacy)	5/Case	An accessory for use with the 3M™ PPS™(Legacy) paint preparation system and 3M™ PPS™ Series 2.0. Our holder keeps spray guns conveniently accessible and in a safe location while in storage. Keeping spray guns in this holder safeguards them from potential damage that can occur from laying them on a table or the floor.
<b>3M™ PPS™ Quad Spray Gun Holder</b> 	00051131162389	16238		1/Case	
 <b>3M™ PPS™ Series 2.0 and 3M™ PPS™ Adapters</b> <div>Most Popular Sizes</div>	00051131260030	26003	Type 2   #S2 3M™ PPS™ 1.0 Legacy Part # 16003	4/Case	Specifically designed adapters allows painters to use the 3M™ PPS™ Series 2.0 with virtually any spray gun. Stainless steel adapter offers exceptional durability. Threaded adapter is easy to install.
	00051131260160	26016	Type 9   #S9 3M™ PPS™ 1.0 Legacy Part # 16016		
	00051131260467	26046	Type 15   #S15 3M™ PPS™ 1.0 Legacy Part # 160046		
	00051131261358	26135	Type 40   #S40 3M™ PPS™ 1.0 Legacy Part # 16135		
	00051131261396	26139	Type 43   #S43 3M™ PPS™ 1.0 Legacy Part # 16139		

Need a new 3M™ PPS™ Series 2.0 or 3M™ PPS™ Adapter for your spray gun? Find a complete list of adapters at [3MCollision.com/PPSAdapters](http://3MCollision.com/PPSAdapters)

# 3M™ PPS™ Series 2.0 Spray Cup System

Choose the cup that fits the job.

Five lined and four vented sizes. Two filter options. H/O pressure cups for high viscosity materials. And opaque kits for UV coatings. You can have an unrivaled selection at your fingertips. And with 3M™ PPS™ Series 2.0 Adapters, they're compatible with nearly every spray gun on the market.




## Spot Repairs

**Micro Cups** — Ideal for areas requiring 3 fl. oz. (90mL) or less of material. EPA 6H compliant.




## 1-Panel Repairs

**Mini Cups** — Ideal for areas requiring up to 6.8 fl. oz. (lined) or 8.5 fl. oz. (vented) of material.




## 2-Panel Repairs

**Midi Cups** — Ideal for areas requiring up to 13.5 fl. oz. (lined and vented) of material, such as bumpers.




## 3-Panel Repairs

**Standard Cups** — Ideal for areas requiring up to 22 fl. oz. (lined) or 23.7 fl. oz. (vented) of material.



## 4-Panel Repairs

**Large Cups** — Ideal for areas requiring up to 28 fl. oz. (lined) or 32.1 fl. oz. (vented) of material, including large, clear coat batches.



**3M Automotive Aftermarket Division**  
3M Center  
Building 223-6N-01  
St. Paul, MN 55144-1000  
USA

Web: [3MCollision.com](http://3MCollision.com)

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit 3M.com.