

3M™ DI-NOC™ Architectural Finishes

Declaration of Performance No. 3M DI-NOC-8

According to Annex III of Regulation (EU) No 305/2011

1. Unique identification code of the product type:

3M™ DI-NOC™ Architectural Finishes

Series: AE, AM, AR, BW, CA, CH, CN, DW, E, ET, FA, FE, FW, GN, GE, H, HG, HS, LE, LW, LZ, ME, MT, MW, NU, OM, PA, PC, PG, PO, PS, PT, PW, RC, RS, RT, SE, SI, ST, SU, TE, VM, WG, as identified by product number in Enclosure of DOP No. 3M DI-NOC-8.

Excluding all DI-NOC™ with EX suffix and DG suffix.

2. Intended use or uses:

3M™ DI-NOC™ Architectural Finishes are self-adhesive decorative surface finishes for interior applications.

3. Manufacturer:



**3M Japan Products Limited
6-7-29 Kitashinagawa | Shinagawa-ku | Tokyo | 141-8684 | Japan**

4. Authorized representative:



**Commercial Branding and Transportation Division
Europe, Middle East and Africa
3M Deutschland GmbH | Carl-Schurz-Str. 1 | 41453 Neuss | Germany**

5. System or systems of AVCP:

System 3

6. Harmonized standard:

**EN 15102: 2007 + A1 2011
Decorative wall coverings - Roll and panel form**

7. Declared performance/s:

Essential Characteristics	Performance	Test Standard	Harmonized Technical Specification
Reaction to Fire	Class B-s1,d0	EN 13501-1: 2019-05	EN 15102: 2007 + A1 2011
Release of Formaldehyde	passed	EN 12149:1997	
Release of Dangerous Substances: - Heavy metals and specific elements - Vinyl chloride	passed	EN 12149:1997	
	passed	EN 12149:1997	
Sound Absorption	No Performance Determined		
Thermal Resistance	No Performance Determined		

8. Appropriate Technical Documentation and/or Specific Technical Documentation:


The performance of the product identified above is in conformity with the set of declared performance/s. This declaration of performance is issued in accordance with Regulation (EU) No 305/2011, under the sole responsibility of the manufacturer identified above.

Signed for and on behalf of the manufacturer by:

Neuss, 5th March 2025

3M Deutschland GmbH

ppa.

Signed by:

 BC411C16D1B948B...
 05-Mar-2025 | 16:04 CET

Camila Cruz Durlacher
 Vice President
 3M R&D Operations
 3M Corporate Research Laboratories
 Europe, Middle East and Africa

Enclosure of DOP No. 3M DI-NOC-8

5th March 2025

3M™ DI-NOC™ Architectural Finishes						
AE	AE-2150	AE-2510	CN	DW-1992MT	DW-2470MT	FA-1531
AE-1632	AE-2151	AE-2511	CN-1621	DW-1993MT	DW-2471MT	FA-1531PO
AE-1632AR	AE-2152MT	AE-2513	CN-1621PO	DW-2197MT	DW-2472MT	FA-1678
AE-1633	AE-2152PO	AM	CN-1622	DW-2197PO	DW-2473MT	FA-1678AR
AE-1633AR	AE-2153AR	AM-1696	CN-1623	DW-2198MT	DW-2473PO	FA-1679
AE-1634	AE-2153MT	AM-1697	CN-1958	DW-2199MT	DW-2474MT	FA-1680
AE-1634AR	AE-2153PO	AM-1698	CN-1958PO	DW-2200MT	DW-2474PO	FA-1962
AE-1635	AE-2154	AM-1699	CN-2112PO	DW-2201MT	DW-2475MT	FA-1963
AE-1636	AE-2155	AM-1700	CN-2512	DW-2202MT	DW-2475PO	FA-2169
AE-1636AR	AE-2156	AM-1701	DW	DW-2202PO	DW-2476MT	FA-2543
AE-1637	AE-2157	AM-1702	DW-1871MT	DW-2203MT	DW-2476PO	FA-2544
AE-1638	AE-2158	AM-1720	DW-1872MT	DW-2204MT	DW-2477MT	FA-2544PO
AE-1639	AE-2159	AM-1721	DW-1873MT	DW-2205MT	DW-2477PO	FE
AE-1640	AE-2160	AM-1722	DW-1874MT	DW-2206MT	DW-2478MT	FE-801
AE-1641	AE-2161	BW	DW-1875MT	DW-2207MT	DW-2479MT	FE-804
AE-1642	AE-2162MT	BW-1310	DW-1875PO	DW-2207PO	DW-2479PO	FE-805
AE-1643	AE-2162PO	BW-1310AR	DW-1876MT	DW-2208MT	DW-2480MT	FE-813
AE-1644	AE-2163AR	BW-1311	DW-1876PO	DW-2208PO	DW-2481MT	FE-1727
AE-1645	AE-2163MT	BW-1312	DW-1877MT	DW-2209MT	ET	FE-1728
AE-1646	AE-2163PO	BW-1313	DW-1877PO	DW-2209PO	ET-1772	FE-1729
AE-1717	AE-2164MT	BW-1314	DW-1878MT	DW-2210MT	ET-1773	FE-1730
AE-1717PO	AE-2165MT	BW-1315	DW-1878PO	DW-2211MT	ET-1774	FE-1731
AE-1718	AE-2165PO	BW-1316	DW-1879MT	DW-2211PO	ET-1775	FE-1732
AE-1719	AE-2167AR	CA	DW-1881MT	DW-2212MT	ET-1776	FE-1733
AE-1719PO	AE-2167MT	CA-418	DW-1882MT	DW-2212PO	FA	FE-1964
AE-1880MT	AE-2168	CA-419	DW-1882PO	DW-2213MT	FA-592	FE-1966
AE-1913MT	AE-2500MT	CA-420	DW-1883MT	DW-2213PO	FA-688	FE-1967
AE-1917MT	AE-2501MT	CA-421	DW-1884MT	DW-2214MT	FA-690	FW
AE-1921MT	AE-2502	CA-422	DW-1885MT	DW-2215MT	FA-1094	FW-231
AE-1926MT	AE-2503	CA-1170	DW-1886MT	DW-2215PO	FA-1095	FW-232
AE-1928MT	AE-2504	CH	DW-1887MT	DW-2216MT	FA-1098	FW-233
AE-1929MT	AE-2505	CH-1627	DW-1888MT	DW-2216PO	FA-1099	FW-233AR
AE-1930MT	AE-2506	CH-1628	DW-1889MT	DW-2217MT	FA-1150	FW-234
AE-1930PO	AE-2507	CH-1628AR	DW-1889PO	DW-2217PO	FA-1153	FW-236
AE-1931MT	AE-2508	CH-1629	DW-1890MT	DW-2218MT	FA-1156	FW-236AR
AE-1932MT	AE-2508PO	CH-1629AR	DW-1891MT	DW-2219MT	FA-1161	FW-237
AE-1933MT	AE-2167AR	CH-1630	DW-1891PO	DW-2220MT	FA-1163	FW-240
AE-1944MT	AE-2167MT	CH-1630AR	DW-1892MT	DW-2221MT	FA-1164	FW-324
AE-1951	AE-2168	CH-1631	DW-1893MT	DW-2222MT	FA-1166	FW-327
AE-1952	AE-2500MT	CH-1631AR	DW-1894MT	DW-2222PO	FA-1167	FW-330
AE-1953	AE-2501MT	CH-1676	DW-1895MT	DW-2223MT	FA-1521	FW-330AR
AE-1954	AE-2502	CH-1677	DW-1896MT	DW-2223PO	FA-1526	FW-332
AE-1955	AE-2503	CH-2116	DW-1897MT	DW-2224MT	FA-1526AR	FW-334
AE-1956	AE-2504	CH-2117	DW-1898MT	DW-2225MT	FA-1527	FW-336
AE-1957	AE-2505	CH-2118	DW-1899MT	DW-2226MT	FA-1527AR	FW-337
AE-1959MT	AE-2506	CH-2119	DW-1900HMT	DW-2227MT	FA-1528	FW-337AR
AE-1959PO	AE-2507	CH-2120	DW-1901MT	DW-2228MT	FA-1530	FW-338
AE-1960MT	AE-2508		DW-1902MT	DW-2229MT	FA-1530AR	FW-338AR
AE-2149	AE-2509		DW-1903MT	DW-2229PO	FA-1530PO	FW-501

Enclosure of DOP No. 3M DI-NOC-8

5th March 2025

3M™ DI-NOC™ Architectural Finishes						
FW	FW-1121HAR	FW-1266	FW-1734H	FW-1976PO	LE	ME-433
FW-502	FW-1122	FW-1268	FW-1735H	FW-1977	LE-018	ME-433AR
FW-510	FW-1122AR	FW-1269	FW-1736H	FW-1977PO	LE-137	ME-486
FW-521	FW-1123	FW-1270	FW-1737	FW-1978	LE-517	ME-904
FW-522	FW-1124	FW-1271	FW-1738	FW-1979	LE-703	ME-904AR
FW-606H	FW-1125	FW-1272	FW-1740	FW-1980	LE-783	ME-1174
FW-607H	FW-1126	FW-1272PO	FW-1743	FW-1981	LE-1104	ME-1175
FW-608H	FW-1127	FW-1273	FW-1744	FW-1982	LE-1105	ME-1176
FW-609H	FW-1129	FW-1273PO	FW-1745	FW-1983	LE-1106	ME-1223
FW-612	FW-1129AR	FW-1274	FW-1746	FW-1984	LE-1108	ME-1224
FW-613	FW-1129PO	FW-1275	FW-1747	FW-1985	LE-1109	ME-1225
FW-614	FW-1130H	FW-1276	FW-1748	FW-1986	LE-1171	ME-1434
FW-616	FW-1130HAR	FW-1277	FW-1749	FW-1987	LE-1226	ME-1435
FW-618	FW-1130HPO	FW-1278	FW-1750	FW-1988	LE-1228	ME-1466
FW-619	FW-1133	FW-1279	FW-1751	FW-1988PO	LE-1229	ME-1466AR
FW-625	FW-1134	FW-1280	FW-1751AR	FW-2420	LE-1231	ME-1467
FW-625AR	FW-1135	FW-1280AR	FW-1752H	FW-2421	LE-1551	ME-1467AR
FW-627	FW-1136H	FW-1281	FW-1753H	FW-2422	LE-1552	ME-1468
FW-627AR	FW-1137	FW-1282	FW-1754	FW-2423	LE-1553	ME-1469
FW-640	FW-1138	FW-1283	FW-1755	FW-2424	LE-1555	ME-1684
FW-641	FW-1138AR	FW-1285	FW-1755PO	FW-2425	LE-2128	ME-1684AR
FW-643	FW-1138PO	FW-1286	FW-1756	FW-2425PO	LE-2367	ME-1685
FW-648	FW-1139H	FW-1287	FW-1757	FW-2426	LE-2703	ME-1685AR
FW-649	FW-1207	FW-1288	FW-1758	FW-2426PO	LE-2741	ME-1716
FW-650	FW-1208	FW-1289	FW-1759	FW-2427	LE-2742	ME-1778
FW-651	FW-1209	FW-1290	FW-1760	FW-2427PO	LE-2782	ME-1781
FW-653	FW-1210	FW-1291	FW-1761	FW-7001	LW	ME-1781AR
FW-655	FW-1211	FW-1292	FW-1762	FW-7006	LW-1081	ME-1961
FW-656	FW-1211PO	FW-1293	FW-1763	FW-7007	LW-1083	ME-1997
FW-677	FW-1212	FW-1293AR	FW-1764	FW-7008	LW-1084	ME-2020
FW-788	FW-1213	FW-1293PO	FW-1765	FW-7009	LW-1085	ME-2022
FW-789	FW-1214	FW-1294	FW-1766	FW-7011	LZ	ME-2023
FW-791	FW-1215	FW-1294AR	FW-1767	FW-7011AR	LZ-461	ME-2024
FW-795	FW-1216	FW-1294PO	FW-1768	FW-7013	LZ-462	ME-2025
FW-886	FW-1217	FW-1296	FW-1769	FW-7014	LZ-587	ME-2026
FW-887	FW-1218	FW-1296PO	FW-1770	FW-7015	ME	ME-2027
FW-888	FW-1255	FW-1297	FW-1770PO	FW-7016	ME-009AR	ME-2172
FW-889	FW-1255PO	FW-1300	FW-1771H	FW-7017	ME-147	ME-2173
FW-1020	FW-1256	FW-1301	FW-1801	FW-7017AR	ME-377	ME-2174
FW-1021	FW-1256PO	FW-1302	FW-1801PO	HG	ME-379	ME-2251MT
FW-1022	FW-1257	FW-1302PO	FW-1805	HG-1201	ME-380	ME-2252MT
FW-1022AR	FW-1257PO	FW-1304	FW-1810	HG-1205	ME-388	ME-2253MT
FW-1023	FW-1258	FW-1306	FW-1811	HG-1511	ME-391	ME-2254MT
FW-1036	FW-1259	FW-1306PO	FW-1970	HG-1994	ME-396	ME-2255MT
FW-1037	FW-1261	FW-1307	FW-1971	HG-1995	ME-396AR	ME-2261
FW-1039H	FW-1261PO	FW-1331	FW-1972	HG-1996	ME-431	ME-2262
FW-1040H	FW-1262	FW-1681	FW-1974	HS	ME-431AR	ME-2263
FW-1113	FW-1262PO	FW-1682	FW-1975	HS-1655	ME-432	ME-2264
FW-1121H	FW-1265	FW-1683	FW-1976	HS-1656	ME-432AR	ME-2265

Enclosure of DOP No. 3M DI-NOC-8

5th March 2025

3M™ DI-NOC™ Architectural Finishes						
ME	MW	NU-1941MT	PA-187	PS-106	PS-992	PS-1870MT
ME-2271	MW-776	NU-1942MT	PA-187AR	PS-107	PS-998	PS-1904MT
ME-2272	MW-777	NU-1943MT	PA-320	PS-110	PS-999	PS-1989MT
ME-2273	MW-1177	NU-2001	PA-389	PS-112	PS-1003	PS-2060
ME-2274	MW-1242	NU-2002	PA-389AR	PS-116	PS-1005	PS-2091MT
ME-2275	MW-1243	NU-2003	PA-390	PS-121	PS-1008	PS-2092MT
ME-2281AR	MW-1244	NU-2004	PA-683	PS-132	PS-1009	PS-2093MT
ME-2282AR	MW-1416	NU-2005	PA-683AR	PS-134	PS-1010	PS-2094MT
ME-2283AR	MW-1417	NU-2006	PC	PS-135	PS-1183	PS-2095MT
ME-2284AR	MW-1418	NU-2007	PC-491	PS-136	PS-1184	PS-2096MT
ME-2285AR	MW-1419	NU-2008	PC-672	PS-138	PS-1185	PS-2097MT
ME-2286AR	MW-1420	NU-2009	PC-758	PS-139	PS-1186	PS-2098MT
ME-2287AR	MW-1782	NU-2010	PC-760	PS-140	PS-1187	PS-2099MT
ME-2291AR	MW-1783	NU-2011	PC-1178	PS-141	PS-1188	PS-2100MT
ME-2292AR	MW-1832	NU-2012	PC-1179	PS-151	PS-1436	PS-2101MT
ME-2293AR	MW-1833	NU-2013	PC-1181	PS-281	PS-1437	PS-2400MTRC
ME-2294AR	MW-1834	NU-2014	PG	PS-292	PS-1438	PS-2401MTRC
ME-2295AR	NU	NU-2015	PG-189	PS-293	PS-1439	PS-2402MTRC
ME-2296AR	NU-1237	NU-2016	PG-190	PS-294	PS-1440	PS-2403MTRC
ME-2297AR	NU-1238	NU-2017	PG-193	PS-503	PS-1441	PS-2404MTRC
ME-2341	NU-1239	NU-2175MT	PG-194	PS-504	PS-1442	PS-2405MTRC
ME-2343	NU-1240	NU-2176MT	PG-195	PS-506	PS-1443	PS-2406MTRC
ME-2344	NU-1241	NU-2177	PG-197	PS-539	PS-1444	PS-3091MT
ME-2346	NU-1601	NU-2178	PS	PS-665	PS-1446	PS-3092MT
ME-2351	NU-1602	NU-2179	PS-001AR	PS-668	PS-1447	PS-3093MT
ME-2353	NU-1603	NU-6007	PS-002AR	PS-713	PS-1448	PS-3094MT
ME-2354	NU-1784	OM	PS-003AR	PS-719	PS-1449	PS-3095MT
ME-2356	NU-1785	OM-2393	PS-004AR	PS-721	PS-1450	PS-3096MT
ME-2357	NU-1786	OM-2394	PS-005AR	PS-885	PS-1451	PS-3097MT
ME-2381AR	NU-1787	OM-2396	PS-006AR	PS-900	PS-1452	PS-3098MT
ME-2383AR	NU-1788	PA	PS-007AR	PS-910	PS-1453	PS-3099MT
ME-2384AR	NU-1789	PA-036	PS-008AR	PS-912	PS-1454	PS-3100MT
ME-2386AR	NU-1790	PA-038	PS-022	PS-914	PS-1455	PS-3101MT
ME-2550	NU-1791	PA-039	PS-027	PS-917	PS-1457	PS-3863MT
ME-2551	NU-1792	PA-045	PS-031	PS-920	PS-1458	PS-3864MT
ME-2552	NU-1793	PA-045AR	PS-034	PS-948	PS-1459	PS-3865MT
ME-2553	NU-1794	PA-046	PS-042	PS-949	PS-1820	PS-3866MT
ME-2554	NU-1795	PA-175	PS-048	PS-950	PS-1821	PS-3867MT
ME-2555	NU-1796	PA-177	PS-051AR	PS-952	PS-1822	PS-3869MT
ME-2556	NU-1797	PA-178	PS-055AR	PS-954	PS-1823	PS-3870MT
ME-2557	NU-1798	PA-179	PS-057AR	PS-955	PS-1824	PS-3904MT
ME-2558	NU-1799	PA-180	PS-058AR	PS-957	PS-1825	PS-3989MT
ME-2559	NU-1934MT	PA-180AR	PS-073	PS-959	PS-1826	PS-5501
ME-2560	NU-1935MT	PA-181	PS-074	PS-971	PS-1863MT	PS-5821
ME-2561	NU-1936MT	PA-181AR	PS-075	PS-975	PS-1864MT	PS-5822
ME-2562	NU-1937MT	PA-183	PS-090	PS-976	PS-1865MT	PS-5836
ME-2563	NU-1938MT	PA-183AR	PS-091	PS-980	PS-1866MT	PS-5899
ME-2564	NU-1939MT	PA-184	PS-093	PS-982	PS-1867MT	PS-5977
ME-2565	NU-1940MT	PA-185	PS-096	PS-983	PS-1869MT	PS-5987

Enclosure of DOP No. 3M DI-NOC-8

5th March 2025

3M™ DI-NOC™ Architectural Finishes						
PS	SE-568AR	ST-2534PO	VM-1990MT	WG-693	WG-1070	WG-1369
PS-5989	SE-570	ST-2535MT	VM-1991MT	WG-694	WG-1071	WG-1370
PS-5992	SI	ST-2536MT	VM-2034	WG-695	WG-1140	WG-1371
PS-5993	SI-1232	ST-2537MT	VM-2035	WG-696	WG-1140PO	WG-1372
PS-5995	SI-1233	ST-2537PO	VM-2036	WG-697	WG-1141	WG-1372AR
PS-5997	SI-1234	ST-2538MT	VM-2037	WG-699	WG-1141PO	WG-1373
PT	SI-1235	ST-2539	VM-2038	WG-709	WG-1142	WG-1374
PT-345	SI-1611	ST-2540MT	VM-2039	WG-763	WG-1143	WG-1375
PT-345AR	SI-1612	ST-2540PO	VM-2090	WG-763GN	WG-1143PO	WG-1376
PT-346	SI-1613	ST-2541MT	VM-2121	WG-765	WG-1144	WG-1377
PT-347	SI-1686	ST-2542MT	VM-2122	WG-765GN	WG-1145H	WG-1378
PT-735	SI-1687	SU	VM-2360	WG-767	WG-1146	WG-1380
PW	SI-1688	SU-2231MT	VM-2361	WG-831	WG-1147	WG-1381
PW-2305MT	SI-1689	SU-2232MT	VM-2362	WG-832	WG-1196	WG-1382
PW-2306MT	ST	SU-2233MT	VM-2363	WG-833	WG-1219	WG-1383
PW-2307MT	ST-011AR	SU-2234MT	VM-2364	WG-835	WG-1220	WG-1384
PW-2308MT	ST-442	SU-2235MT	VM-2365	WG-836	WG-1221	WG-1386
PW-2309MT	ST-736	TE	VM-2366	WG-837	WG-1336	WG-1387
PW-2310MT	ST-736AR	TE-1650	WG	WG-841	WG-1337	WG-1388
PW-2311MT	ST-737	TE-1651	WG-156	WG-845	WG-1338	WG-1389
PW-2312MT	ST-1195	TE-1652	WG-157	WG-846	WG-1339	WG-1390
PW-2313MT	ST-1586	TE-1653	WG-159	WG-854	WG-1340	WG-1391
PW-2314MT	ST-1587	TE-1713	WG-166	WG-855	WG-1341	WG-1392H
PW-2315MT	ST-1588	TE-1714	WG-242	WG-856	WG-1342	WG-1703
PW-2316MT	ST-1828	TE-1715	WG-243	WG-857	WG-1343	WG-1704
PW-2317MT	ST-1829	VM	WG-247	WG-863	WG-1344	WG-1705
PW-2318MT	ST-1830	VM-168	WG-248	WG-865	WG-1345	WG-1706
PW-2319MT	ST-1831	VM-305	WG-250	WG-877	WG-1346	WG-1707
PW-2320MT	ST-1911MT	VM-306	WG-256	WG-878	WG-1347	WG-1708
PW-2321MT	ST-1912MT	VM-381	WG-364	WG-879	WG-1348	WG-1709
PW-2322MT	ST-1914AR	VM-383	WG-364GN	WG-940	WG-1349	WG-1710
PW-2323MT	ST-1914MT	VM-452	WG-376	WG-941	WG-1350	WG-1710PO
PW-2324MT	ST-1915MT	VM-800	WG-408	WG-943	WG-1351	WG-1711GN
PW-2325MT	ST-1916MT	VM-1486	WG-410	WG-946	WG-1353	WG-1712GN
PW-2326MT	ST-1918MT	VM-1487	WG-416	WG-947	WG-1354	WG-1812
PW-2327MT	ST-1919AR	VM-1488	WG-417	WG-960	WG-1355	WG-1814
PW-2328MT	ST-1919MT	VM-1489	WG-428	WG-962	WG-1356	WG-1815
RS	ST-1920MT	VM-1691	WG-430	WG-964	WG-1357	WG-1816
RS-1189	ST-1927MT	VM-1692	WG-453	WG-1044	WG-1358	WG-1818
RS-1190	ST-2170MT	VM-1693	WG-467	WG-1046	WG-1359	WG-1835
RT	ST-2171AR	VM-1694	WG-478	WG-1050	WG-1360	WG-1836
RT-1111	ST-2171MT	VM-1695	WG-624	WG-1052	WG-1361	WG-1837
RT-1112	ST-2171PO	VM-1855MT	WG-629	WG-1057	WG-1362	WG-1838
RT-1827	ST-2530MT	VM-1856MT	WG-657	WG-1058	WG-1363	WG-1839
SE	ST-2531MT	VM-1858MT	WG-658	WG-1063	WG-1364	WG-1840
SE-010AR	ST-2532MT	VM-1859MT	WG-659	WG-1064	WG-1365	WG-1841
SE-567	ST-2533MT	VM-1860MT	WG-662	WG-1066	WG-1366	WG-1845
SE-567AR	ST-2533PO	VM-1861MT	WG-663	WG-1067	WG-1367	WG-1846
SE-568	ST-2534MT	VM-1862MT	WG-664	WG-1069	WG-1368	WG-1847

3M™ DI-NOC™ Architectural Finishes			
WG	WG-2452PO		Description
WG-1848	WG-2453		AE* Abstract Earth
WG-2019	WG-2453PO		AM* Advanced Metallic
WG-2033	WG-2454		AR** Abrasion Resistant
WG-2041	WG-2454PO		BW* Big Wave
WG-2042	WG-2460		CA* Carbon
WG-2047	WG-2460PO		CH* Cross Hairline
WG-2048	WG-2461		CN* Concrete
WG-2049	WG-2461PO		DW* Dry Wood
WG-2056	WG-2462		E*** E-Series
WG-2070	WG-2462PO		ET* Effect
WG-2071	WG-2463		FA* Abstract/Rust
WG-2072	WG-2463PO		FE* Wave
WG-2073	WG-2464		FW* Fine Wood
WG-2073PO	WG-2464PO		GN** Gloss
WG-2074	WG-2705		GE* G-Emboss
WG-2075	WG-2707		H** <small>horizontal grain direction</small>
WG-2076	WG-2839		HG* High Glass
WG-2077	WG-2860		HS* Hide Seek
WG-2078	WG-2862		LE* Leather
WG-2079	WG-2944		LW* Little Wave
WG-2080H	WG-7022		LZ* Abstract
WG-2081H	WG-7023		ME* Metallic
WG-2082H	WG-7024		MT** Matte
WG-2083H	WG-7024AR		MW* Metallic Wood
WG-2084H			NU* Nuno
WG-2085			OM* Optical Mesh
WG-2086			PA* Metallic
WG-2087			PC* Sand
WG-2088			PG* Abstract
WG-2115			PO*** Polyolefin Film
WG-2244			PS* Single Color
WG-2246			PT* Abstract
WG-2304			PW* Premium Wood
WG-2430			RC*** Recycled Content Film
WG-2431			RS* Random Style
WG-2432			RT* Rust
WG-2433			SE* Abstract/Stucco
WG-2434			SI* Silk
WG-2440			ST* Stone
WG-2441			SU* Suede
WG-2442			TE* Tech Fiber
WG-2443			VM* Metallic
WG-2444			WG* Wood Grain
WG-2450			TE* Tech Fiber
WG-2450PO			VM* Metallic
WG-2451			WG* Wood Grain
WG-2451PO			
WG-2452			

*Series / **surface texture / ***special construction