



3M Science.
Applied to Life.™

Automotive Aftermarket Division Heavy Duty Truck

Products and Accessories



Heavy Duty Truck - Table of Contents



Sanding4



Welding8



Grinding9



Adhesives & Fillers..... 10



Masking 12



Spray Equipment..... 13



Compounds, Polishes & Pads..... 15



Professional Detailing..... 16

Sanding



36170



30700



31374



30667

Part No.	Product Description
30666	3M™ Purple Finishing Film Hookit™ Disc, 6 in, P2000, 50 discs per box, 4 boxes per case
30667	3M™ Purple Finishing Film Hookit™ Disc, 6 in, P1500, 50 discs per box, 4 boxes per case
30668	3M™ Purple Finishing Film Hookit™ Disc, 6 in, P1200, 50 discs per box, 4 boxes per case
30669	3M™ Purple Finishing Film Hookit™ Disc, 6 in, P1000, 50 discs per box, 4 boxes per case
30670	3M™ Purple Finishing Film Hookit™ Disc, 6 in, P800, 50 discs per box, 4 boxes per case
30671	3M™ Purple Finishing Film Hookit™ Disc, 6 in, P600, 50 discs per box, 4 boxes per case
02085	3M™ Trizact™ Hookit™ Foam Discs, 6 in, P3000, 15 discs per box, 4 boxes per case
02088	3M™ Trizact™ Hookit™ Clear Coat Sanding Disc, P1500, 6 in, 25 discs per box, 4 boxes per case
02095	3M™ Trizact™ Hookit™ Clear Coat Sanding Disc, P1500, 5 in, 25 discs per box, 4 boxes per case
30662	3M™ Hookit™ Foam Disc, 6 in, P5000, 15 discs per box, 4 boxes per case
02090	3M™ Trizact™ Hookit™ Blending Disc 443A, 6 in, P1000, 15 discs per box, 4 boxes per case
01870	3M™ Purple Hookit™ Sheet, 4-1/2 in x 30 in, P220, 10 sheets per box, 5 boxes per case
01868	3M™ Purple Hookit™ Sheet, 4-1/2 in x 30 in, P320, 10 sheets per box, 5 boxes per case
01810	3M™ Hookit™ Purple Clean Sanding Disc 334U, 6 in, P500C, 50 discs per box, 4 boxes per case
01811	3M™ Hookit™ Purple Clean Sanding Disc 334U, 6 in, P400C, 50 discs per box, 4 boxes per case
01812	3M™ Hookit™ Purple Clean Sanding Disc 334U, 6 in, P320C, 50 discs per box, 4 boxes per case
01813	3M™ Hookit™ Purple Clean Sanding Disc 334U, 6 in, P280C, 50 discs per box, 4 boxes per case
01814	3M™ Hookit™ Purple Clean Sanding Disc 334U, 6 in, P240C, 50 discs per box, 4 boxes per case
30700	3M™ Hookit™ Purple Clean Sanding Sheet Roll 334U, 70MM x 12M, P800, 5 boxes per case
30701	3M™ Hookit™ Purple Clean Sanding Sheet Roll 334U, 70MM x 12M, P600, 5 boxes per case
30702	3M™ Hookit™ Purple Clean Sanding Sheet Roll 334U, 70MM x 12M, P500, 5 boxes per case
30703	3M™ Hookit™ Purple Clean Sanding Sheet Roll 334U, 80 mm x 12 m, 5 boxes per case
30705	3M™ Hookit™ Purple Clean Sanding Sheet Roll 334U, 70 MM x 12 m, 5 boxes per case
30706	3M™ Hookit™ Purple Clean Sanding Sheet Roll 334U, 70MM x 12M, P280, 5 boxes per case
30707	3M™ Hookit™ Purple Clean Sanding Sheet Roll 334U, 70 MM x 12M, P240, 5 boxes per case

Sanding

Part No.	Product Description
30724	3M™ Hookit™ Purple Clean Sanding Roll 334U, 115MM x 12M, P800, 3 rolls per case
30725	3M™ Hookit™ Purple Clean Sanding Roll 334U, 115MM x 12M, P600, 3 rolls per case
30726	3M™ Hookit™ Purple Clean Sanding Roll 334U, 115MM x 12M, P500, 3 rolls per case
30727	3M™ Hookit™ Purple Clean Sanding Roll 334U, 115MM x 12M, P400, 3 rolls per case
30729	3M™ Hookit™ Purple Clean Sanding Roll 334U, 115MM x 12M, P320, 3 rolls per case
30730	3M™ Hookit™ Purple Clean Sanding Roll 334U, 115MM x 12M, P280, 3 rolls per case
30731	3M™ Hookit™ Purple Clean Sanding Roll 334U, 115MM x 12M, P240, 3 rolls per case
30760	3M™ Hookit™ Purple Clean Sanding Disc 334U, 6 in, P800C, 50 discs per box, 4 boxes per case
30761	3M™ Hookit™ Purple Clean Sanding Disc 334U, 6 in, P600C, 50 discs per box, 4 boxes per case
30666	3M™ Purple Finishing Film Hookit™ Disc, 6 in, P2000, 50 discs per box, 4 boxes per case
36170	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 40 grade, 50 discs per box, 4 boxes per case
36172	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 80 grade, 50 discs per box, 4 boxes per case
36174	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 120 grade, 50 discs per box, 4 boxes per case
36175	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 150 grade, 50 discs per box, 4 boxes per case
36176	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 180 grade, 50 discs per box, 4 boxes per case
36177	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 220 grade, 50 discs per box, 4 boxes per case
36178	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 240 grade, 50 discs per box, 4 boxes per case
36180	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 320 grade, 50 discs per box, 4 boxes per case
36181	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 400 grade, 50 discs per box, 4 boxes per case
36182	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 500 grade, 50 discs per box, 4 boxes per case
36183	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 600 grade, 50 discs per box, 4 boxes per case
36184	3M™ Hookit™ Blue Abrasive Disc Multi-hole, 6 in, 800 grade, 50 discs per box, 4 boxes per case
36187	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 80 grade, 4 boxes per case
36189	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 120 grade, 4 boxes per case
36190	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 150 grade, 4 boxes per case
36191	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 180 grade, 4 boxes per case
36192	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 220 grade, 4 boxes per case
36193	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 240 grade, 4 boxes per case
36195	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 320 grade, 4 boxes per case
36196	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 400 grade, 4 boxes per case
36197	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 500 grade, 4 boxes per case
36198	3M™ Hookit™ Blue Abrasive Sheet Roll Multi-hole, 2.75 in x13 yd, 600 grade, 4 boxes per case
36200	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 40 grade, 25 discs per roll, 5 rolls per case
36202	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 80 grade, 50 discs per roll, 5 rolls per case
36204	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 120 grade, 100 discs per roll, 5 rolls per case
36205	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 150 grade, 100 discs per roll, 5 rolls per case

Sanding



30684



36221



36174



30666

Part No.	Product Description
36206	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 180 grade, 100 discs per roll, 5 rolls per case
36207	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 220 grade, 100 discs per roll, 5 rolls per case
36208	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 240 grade, 100 discs per roll, 5 rolls per case
36210	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 320 grade, 100 discs per roll, 5 rolls per case
36211	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 400 grade, 100 discs per roll, 5 rolls per case
36212	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 500 grade, 100 discs per roll, 5 rolls per case
36213	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 600 grade, 100 discs per roll, 5 rolls per case
36214	3M™ Stikit™ Blue Abrasive Disc Roll, 6 in, 800 grade, 100 discs per roll, 5 rolls per case
36215	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 10 yd, 40 grade, 5 boxes per case
36217	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 20 yd, 80 grade, 5 boxes per case
36219	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 30 yd, 120 grade, 5 boxes per case
36220	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 30 yd, 150 grade, 5 boxes per case
36221	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 30 yd, 180 grade, 5 boxes per case
36222	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 30 yd, 220 grade, 5 boxes per case
36223	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 30 yd, 240 grade, 5 boxes per case
36225	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 45 yd, 320 grade, 5 boxes per case
36226	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 45 yd, 400 grade, 5 boxes per case
36227	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 45 yd, 500 grade, 5 boxes per case
36228	3M™ Stikit™ Blue Abrasive Sheet Roll, 2.75 in x 45 yd, 600 grade, 5 boxes per case
31370	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 6 in, 40+, 25 discs per box, 4 boxes per case
31375	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 8 in, 40+, 25 discs per box, 4 boxes per case
31361	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 3 in, 80+, 50 discs per box, 4 boxes per case
31366	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 5 in, 80+, 50 discs per box, 4 boxes per case
31371	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 6 in, 80+, 50 discs per box, 4 boxes per case
31376	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 8 in, 80+, 25 discs per box, 4 boxes per case
31362	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 3 in, 120+, 50 discs per box, 4 boxes per case

Sanding

Part No.	Product Description
31367	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 5 in, 120+, 50 discs per box, 4 boxes per case
31372	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 6 in, 120+, 50 discs per box, 4 boxes per case
31363	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 3 in, 150+, 50 discs per box, 4 boxes per case
31368	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 5 in, 150+, 50 discs per box, 4 boxes per case
31373	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 6 in, 150+, 50 discs per box, 4 boxes per case
31364	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 3 in, 180+, 50 discs per box, 4 boxes per case
31369	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 5 in, 180+, 50 discs per box, 4 boxes per case
31374	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 6 in, 180+, 50 discs per box, 4 boxes per case
31461	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 3 in, 220+, 50 discs per box, 4 boxes per case
31471	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 5 in, 220+, 50 discs per box, 4 boxes per case
31481	3M™ Cubitron™ II Clean Sanding Hookit™ Abrasive Disc, 6 in, 220+, 50 discs per box, 4 boxes per case
34490	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 40+ grade, 95 mm x 177 mm, 25 sheets per carton, 4 cartons per case
34492	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 80+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34494	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 120+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34495	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 150+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34496	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 180+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34497	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 220+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34440	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 40+, 70 mm x 8 m, 1 roll per box, 5 boxes per case
34442	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 80+, 70 mm x 12 m, 1 roll per box, 5 boxes per case
34445	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 150+, 70 mm x 12 m, 1 roll per box, 5 boxes per case
34446	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 180+, 70 mm x 12 m, 1 roll per box, 5 boxes per case
34447	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 220+, 70 mm x 12 m, 1 roll per box, 5 boxes per case

Welding



Part No.	Description
05912	3M™ Welding and Spark Deflection Paper Dispenser, 1 per case
05916	3M™ Welding and Spark Deflection Paper, 24 in x 150 ft, 2 per case
05919	3M™ High Performance Welding Drape, 57 in x 80 in, 1 per case
05917	3M™ Weld-Thru Coating II, 12.75 oz Net Wt/361 g, 6 per case
08733	3M™ Rocker Protector Pouch, 3 fl oz (US), 4 per case
08734	3M™ Rocker Protector Pouch, 5.5 fl oz (US), 4 per case
08744	3M™ Paintable Undercoating Waterbased Pouch, 5.5 fl. oz. (US), 4 per case
08747	3M™ Paintable Undercoating Pouch, 5.5 fl oz, 4 per case
08801	3M™ No Cleanup Applicator Gun, 8 per case
08804	3M™ No Cleanup Waterbased Undercoating, 18.5 fl oz, 6 per case
08840	3M™ Sound Deadening Pads, 500 mm x 500 mm, 1 pad, 10 pads per case
08864	3M™ Body Schutz Rubberized Coating Black, 1 Quart, 6 per case
08874	3M™ Rocker Schutz Coating, 1 Quart (US), 6 per case
08881	3M™ Undercoating, 16 oz Net Wt/453 g, 6 per case
08882	3M™ Undercoating, 17 oz Net Wt/481 gr, 6 per case
08883	3M™ Rubberized Undercoating, 19.7 oz Net Wt, 6 per case
08889	3M™ Rocker Panel Coating - Grey, 23 oz Net Wt / 650g, 6 per Case
08852	3M™ Cavity Wax Plus, 18 oz, 4 per Case
08851	3M™ Cavity Wax Plus Applicator Wand Kit, 12 per Case
08997	3M™ Body Schutz Applicator Gun, 1 per case
08964	3M™ No Cleanup High Coverage Body Schutz™ Coating, 22 fl oz, 6 per case
08966	3M™ No Cleanup Replacement Nozzles, 8 per bag, 4 bags per case
49950	3M™ Speedglas™ Boneyard Welding Helmet 100, Auto-Darkening Filter 100V 07-0012-31BY, Shades 8-12 1/Case
49952	3M™ Speedglas™ Ice Hot Welding Helmet 100, Auto-Darkening Filter 100V 07-0012-31IH, Shades 8-12 1/Case
49954	3M™ Speedglas™ Razor Dragon Welding Helmet 100, Auto-Darkening Filter 100V 07-0012-31RD, Shades 8-12 1/Case
49956	3M™ Speedglas™ Raging Skull Welding Helmet 100, Auto-Darkening Filter 100V 07-0012-31RS, Shades 8-12 1/Case
49958	3M™ Speedglas™ Xterminator Welding Helmet 100, Auto-Darkening Filter 100V 07-0012-31XT, Shades 8-12 1/Case

Grinding



33413



33456



33472



33437

Part No.	Description
33425	3M™ Cubitron™ II Abrasive Fibre Disc, 7 in x 7/8 in (180mm x 22mm), 36+, 5 discs per box, 5 boxes per case
33427	3M™ Cubitron™ II Abrasive Fibre Disc, 7 in x 7/8 in (180mm x 22mm), 60+, 5 discs per box, 5 boxes per case
33428	3M™ Cubitron™ II Abrasive Fibre Disc, 7 in x 7/8 in (180mm x 22mm), 80+, 5 discs per box, 5 boxes per case
33415	3M™ Cubitron™ II Abrasive Fibre Disc, 5 in x 7/8 in (125mm x 22mm), 60+, 5 discs per box, 5 boxes per case
33416	3M™ Cubitron™ II Abrasive Fibre Disc, 5 in x 7/8 in (125mm x 22mm), 80+, 5 discs per box, 5 boxes per case
33413	3M™ Cubitron™ II Abrasive Fibre Disc, 5 in x 7/8 in (125mm x 22mm), 36+, 5 discs per box, 5 boxes per case
33377	3M™ Cubitron™ II Fibre Roloc™ Disc, 2 in (50mm), 36+, 15 discs per box, 6 boxes per case
33379	3M™ Cubitron™ II Fibre Roloc™ Disc, 2 in. (50mm), 60+, 15 discs per box, 6 boxes per case
33380	3M™ Cubitron™ II Fibre Roloc™ Disc, 2 in (50mm), 80+, 15 discs per box, 6 boxes per case
33389	3M™ Cubitron™ II Fibre Roloc™ Disc, 3 in (75mm), 36+, 15 discs per box, 6 boxes per case
33391	3M™ Cubitron™ II Fibre Roloc™ Disc, 3 in (75mm), 60+, 15 discs per box, 6 boxes per case
33392	3M™ Cubitron™ II Fibre Roloc™ Disc, 3 in (75mm), 80+, 15 discs per box, 6 boxes per case
33437	3M™ Cubitron™ II File Belt, 10mm x 330mm (3/8 in X 13 in), 36+, 10 belts per box, 5 boxes per case
33439	3M™ Cubitron™ II File Belt, 10mm x 330mm (3/8 in X 13 in), 60+, 10 belts per box, 5 boxes per case
33440	3M™ Cubitron™ II File Belt, 10mm x 330mm (3/8 in X 13 in), 80+, 10 belts per box, 5 boxes per case
33443	3M™ Cubitron™ II File Belt, 1/2 in x 18 in (12.7mm X 457.2mm), 36+, 10 belts per box, 5 boxes per case
33445	3M™ Cubitron™ II File Belt, 1/2 in X 18 in (12.7mm x 457.2mm), 60+, 10 belts per box, 5 boxes per case
33446	3M™ Cubitron™ II File Belt, 1/2 in x 18 in (12.7mm X 457.2mm), 80+, 10 belts per box, 5 boxes per case
33456	3M™ Cubitron™ II Cut-Off Wheel, 75mm x 1mm x 9.53mm (3 in x .04 in x 3/8 in), 5 wheels per box, 6 boxes per case
33455	3M™ Cubitron™ II Cut-Off Wheel, 75mm x 1.6mm x 9.53mm (3 in x .0625 in x 3/8 in), 5 wheels per box, 6 boxes per case
33467	3M™ Cubitron™ II Cut-Off Wheel, 115mm x 1mm x 22.23mm (4.5 in x .04 in x 7/8 in), 5 wheels per box, 6 boxes per case
34490	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 40+ grade, 95 mm x 177 mm, 25 sheets per carton, 4 cartons per case
34492	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 80+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34494	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 120+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34495	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 150+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34496	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 180+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34497	3M™ Cubitron™ II Hookit™ File Sheet Dust Free 737U, 220+, 95 mm x 177 mm, 25 sheets per box, 4 boxes per case
34440	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 40+, 70 mm x 8 m, 1 roll per box, 5 boxes per case.
34442	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 80+, 70 mm x 12 m, 1 roll per box, 5 boxes per case
34445	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 150+, 70 mm x 12 m, 1 roll per box, 5 boxes per case
34446	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 180+, 70 mm x 12 m, 1 roll per box, 5 boxes per case
34447	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U, 220+, 70 mm x 12 m, 1 roll per box, 5 boxes per case

Adhesives & Fillers



05907



01171



08280



58115

Part No.	Description
Adhesives	
08368	3M™ Urethane Seam Sealer, White, 310mL Cartridge, 12 per case
04903	3M™ Plastic Contouring Sheet, 1 roll, 6 rolls per case
04904	3M™ Reinforcement Patch, 1 roll, 6 rolls per case
05888	3M™ EZ Fix Flexible Patch, 4 in x 8 in, 6 patches per box, 6 boxes per case
05907	3M™ Polyolefin Adhesion Promoter, 12 oz Net Wt, 6 per case
08063	3M™ Trim and Emblem Adhesive, 8 ounces 6 per case
08270	3M™ SMC/Fiberglass Repair Adhesive-1, 400 mL, 6 per case
08271	3M™ SMC/Fiberglass Repair Adhesive-3, 400 mL, 6 per case
08272	3M™ SMC/Fiberglass Repair Adhesive-10, 400 mL, 6 per case
08273	3M™ SMC/Fiberglass Repair Adhesive-35, 400 mL, 6 per case
08274	3M™ SMC/Fiberglass Repair Adhesive-90, 400 mL, 6 per case
08275	3M™ Rigid Parts Repair Adhesive, 400 mL, 6 per case
08277	3M™ Fiberglass Matting Adhesive, 400 mL, 6 per case
08280	3M™ Performance Pneumatic Applicator, 400 mL, 1 per case
08609	3M™ Windo-Weld™ Super Fast Urethane, Black, 10.5 fl oz Cartridge, 12 per case
08681	3M™ Single Step Primer, 125 mL, 6 per case
08682	3M™ Single Step Primer, 30 mL, 6 per case
08688	3M™ Urethane Primer Daubers, 100 per bag, 5 bags per case
08689	3M™ Fast Cure Auto Glass Urethane, 450 mL Flex Pack, 12 per case
08690	3M™ Fast Cure Auto Glass Urethane, 10.5 fl oz Cartridge, 12 per case
08984	3M™ General Purpose Adhesive Cleaner, 1 Quart (US), 6 per case
08987	3M™ General Purpose Adhesive Cleaner, 15 oz net wt, 12 per case
38984	3M™ Specialty Adhesive Remover, 1 Quart (US), 6 per case
38987	3M™ Specialty Adhesive Remover, 15oz Net Wt, 6 per case

Adhesives & Fillers

Part No.	Description
55887	3M™ EZ Sand Flexible Parts Repair Adhesive, 600 mL, 4 per case
058115	3M™ Panel Bonding Adhesive, 450 mL, 4 per case
57333	3M™ Impact Resistant Structural Adhesive, 450 ml, 2 per case
Fillers	
01131	3M™ Platinum™ Plus Filler, 1 Gallon (US), 4 per case
01132	3M™ Platinum™ Plus Filler, 3 Gallon (US) Cartridge, 2 per case
01171	3M™ Platinum™ Filler, 1 Gallon (US), 4 per case
01231	3M™ Platinum™ Filler, 3 Gallon (US) Pail, 1 per case
01271	3M™ Platinum™ Filler, 3 Gallon (US) Cartridge, 2 per case
05841	3M™ Premium Body Filler Gold QBA, 5 gallon air pail, 1 pail, 1 per case
31138	3M™ Platinum™ with Hardener, 5 Gallon (US) Pail, 1 per case
31139	3M™ Platinum™ Plus w/Hardener, 5-Gal Pail boxed, 1 per case
02576	3M™ Bulk Nozzle Rack, 1 per case
05846	3M™ Dynamic Mixing Applicator - Pneumatic, 1 per case
05847	3M™ Dynamic Mixing Nozzle, 50 nozzles per box, 6 boxes per case
05857	3M™ Dent Finishing Glaze for DMS, 276 mL, 6 per case
05862	3M™ Platinum™ Glaze, 276 mL, 6 per case
05863	3M™ Platinum™ Plus for DMS, 276 mL, 6 per case
05877	3M™ Reinforced Filler for DMS, 276 mL, 6 per case
05860	3M™ Dry Guide Coat Cartridge, 50 gr, 10 per case
05861	3M™ Dry Guide Coat, 50 gr Cartridge and Applicator Kit, 6 per case

Masking



06728



06293



06620



26334

Part No.	Description
26330	3M™ Scotch® Performance Automotive 233+ Masking Tape, 6mm x 55m Bulk - 96 rolls/case
26332	3M™ Scotch® Performance Automotive 233+ Masking Tape, 12mm x 55m Bulk - 48 rolls/case
26334	3M™ Scotch® Performance Automotive 233+ Masking Tape, 18mm x 55m Bulk - 48 rolls/case
26335	3M™ Scotch® Performance Automotive 233+ Masking Tape, 21mm x 55m Bulk - 40 rolls/case
26336	3M™ Scotch® Performance Automotive 233+ Masking Tape, 24mm x 55m Bulk - 24 rolls/case
26338	3M™ Scotch® Performance Automotive 233+ Masking Tape, 36mm x 55m Bulk - 16 rolls/case
26340	3M™ Scotch® Performance Automotive 233+ Masking Tape, 48mm x 55m Bulk - 12 rolls/case
26341	3M™ Scotch® Performance Automotive 233+ Masking Tape, 72mm x 55m Bulk - 8 rolls/case
26343	3M™ Scotch® Performance Automotive 233+ Masking Tape, 3mm x 55m Boxed - 12 rolls/case
26344	3M™ Scotch® Performance Automotive 233+ Masking Tape, 6mm x 55m Boxed - 12 rolls/case
46334	3M™ Scotch® Performance Automotive 233+ Masking Tape, 18mm x 55m Wrapped - 48 rolls/case
46338	3M™ Scotch® Performance Automotive 233+ Masking Tape, 36mm x 55m Wrapped - 24 rolls/case
06531	3M™ White Masking Paper, 60 in x 750 ft, 1 per case
06537	3M™ White Masking Paper, 6 in x 750 ft, 6 per case
06538	3M™ White Masking Paper, 12 in x 750 ft, 3 per case
06539	3M™ White Masking Paper, 18 in x 750 ft, 2 per case
06540	3M™ White Masking Paper, 36 in x 750 ft, 1 per case
06620	3M™ Precision Masking Tape, 1 in x 60 yds, 12 rolls per case
06725	3M™ High Temperature Moisture Resistant Protective Sheeting, 5 m x 75 m, 1 roll per case
06724	3M™ Plastic Sheeting with 388N Yellow Masking Tape (36mm), 16 ft x 400 ft, 1 roll per case
06727	3M™ Overspray Protective Sheeting, 12 ft x 400 ft, 1 per case
06728	3M™ Overspray Protective Sheeting, 16 feet x 350 feet, 1 roll per case
06742	3M™ Overspray Protective Sheeting, 20 ft x 250 ft, 1 per case
06780	3M™ Overspray Protective Sheeting Masker, 1 per case
06864	Scotch® Slimline Apron Taper
06865	Scotch® 18 Inch Apron Taper
06866	Scotch® 36 Inch Apron Taper
06781	Scotch® Cart Masker

Spray Equipment



16580



16122



16172



36866

Part No.	Description
3M™ PPS™ Series 2.0 Lid & Liner Kits	
26024	Large (28 fl oz, 850 mL), 200u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26325	Large (28 fl oz, 850 mL), 125u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26000	Standard (22 fl oz, 650 mL), 200u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26301	Standard (22 fl oz, 650 mL), 125u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26112	Midi (13.5 fl oz, 400 mL), 200u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26312	Midi (13.5 fl oz, 400 mL), 125u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26114	Mini (6.8 fl oz, 200 mL), 200u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26314	Mini (6.8 fl oz, 200 mL), 125u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26028	Micro (3 fl oz, 90 mL), 200u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26328	Micro (3 fl oz, 90 mL), 125u Micron Filter, 50 lids & liners, 32 sealing plugs, 1 hard cup per case
26042	Trial Kit, Standard (22 fl oz, 650 mL), 200u Micron Filter, 25 lids & liners, 32 sealing plugs, 2 hard cups, 1 per case
26342	Trial Kit, Standard (22 fl oz, 650 mL), 125u Micron Filter, 25 lids & liners, 32 sealing plugs, 2 hard cups, 1 per case
3M™ PPS™ Series 2.0 Lids Only	
26200	Standard/Large, 200u Micron Filter, 25 per pack, 1 pack per case
26199	Standard/Large, 125u Micron Filter, 25 per pack, 1 pack per case
26204	Midi/Mini/Micro, 200u Micron Filter, 25 per pack, 1 pack per case
26205	Midi/Mini/Micro, 125u Micron Filter, 25 per pack, 1 pack per case
3M™ PPS™ Series 2.0 Hard Cups (with mix ratios on cup!)	
26023	Large (28 fl oz, 850 mL), 2 cups per carton, 4 cartons per case
26001	Standard (22 fl oz, 650 mL), 2 cups per carton, 4 cartons per case
26122	Midi (13.5 fl oz, 400 mL), 2 cups per carton, 4 cartons per case
26115	Mini (6.8 fl oz, 200 mL), 2 cups per carton, 4 cartons per case
3M™ PPS™ Series 2.0 Accessories	
26432	3M™ PPS™ Series 2.0 Sealing Plugs, 96 plugs per pack, 6 packs per case

Spray Equipment



Part No.	Description
16432	3M™ PPS™ 1.0 + Type V Sealing Plugs, 96 plugs per pack, 6 packs per case
26010	3M™ PPS™ Series 2.0 Cup Carrier, 1 box per case *available January*
26610	3M™ Accuspray™ Atomizing Head Kit Rack, 1 box per case *available January*
16219	3M™ PPS™ Liner Dispenser, fits all (5) sizes, 1 per case
16299	3M™ PPS™ Lid Dispenser, fits both sizes lids, 1 per case
16236	3M™ PPS™ Single Magentic Spray Gun Holder, 5 per case
16238	3M™ PPS™ Quad Spray Gun Holder, 1 per case
26458	3M™ PPS™ Series 2.0 Universal Shaker Core, 1 per case
26689	3M™ High Power Spray Gun Cleaner, 6 cans per case *available January 2018*
3M™ Accuspray™ ONE Spray Gun System for 3M™ PPS™ Series 2.0	
26578	3M™ Accuspray™ ONE Professional Spray Gun Kit with 3M™ PPS™ Series 2.0, 2 per case *available January 2018*
26612	Atomizing Head Refill Pack for PPS™ Series 2.0, Blue, 1.2mm, 4 atomizing heads per pack, 6 packs per case *available December*
26613	Atomizing Head Refill Pack for PPS™ Series 2.0, Green, 1.3mm, 4 atomizing heads per pack, 6 packs per case *available December*
26614	Atomizing Head Refill Pack for PPS™ Series 2.0, Orange, 1.4mm, 4 atomizing heads per pack, 6 packs per case *available December*
26618	Atomizing Head Refill Pack for PPS™ Series 2.0, Clear Transparent, 1.8mm, 4 atomizing heads per pack, 6 packs per case *available December*
26620	Atomizing Head Refill Pack for PPS™ Series 2.0, Red Opaque, 2.0mm, 4 atomizing heads per pack, 6 packs per case *available December*
26580	3M™ Accuspray™ ONE Spray Gun System with PPS™ Series 2.0 Display Kit, 2 kits per case *available January*
26582	Atomizing Head Blister Pack for PPS™ Series 2.0, Blue, 1.2mm, 1 atomizing head per each, 5 each per case *available January*
26583	Atomizing Head Blister Pack for PPS™ Series 2.0, Green, 1.3mm, 1 atomizing head per each, 5 each per case *available January*
26584	Atomizing Head Blister Pack for PPS™ Series 2.0, Orange, 1.4mm, 1 atomizing head per each, 5 each per case *available January*
26585	Atomizing Head Blister Pack for PPS™ Series 2.0, Clear Transparent, 1.8mm, 1 atomizing head per each, 5 each per case *available January*
3M™ Accuspray™ HGP Pressure Spray Gun for 3M™ PPS™ Series 2.0 *available 2018*	
26587	3M™ Accuspray™ HGP Pressure Spray Gun, includes air flow control valve, (2) 2.0mm, (2) 1.8mm atomizing heads, 2 per case
26121	3M™ PPS™ Series 2.0 Pressure Cup, Midi/Mini/Micro, 1 cup per box, 4 boxes per case
26124	3M™ PPS™ Series 2.0 Pressure Cup, Large/Standard, 1 cup per box, 2 boxes per case
3M™ Dirt Trap Booth & Surface Protection Material	
36849	3M™ Dirt Trap Material, 4 in x 300 ft 1 Roll/Case
36850	3M™ Dirt Trap Material, 6 in x 300 ft 1 Roll/Case
36851	3M™ Dirt Trap Material, 14 in x 300 ft 1 Roll/Case
36852	3M™ Dirt Trap Material, 28 in x 300 ft 1 Roll/Case
36853	3M™ Dirt Trap Material, 56 in x 300 ft 1 Roll/Case
36864	3M™ Dirt Trap Material 56 in Floor Applicator, 1 per case
36865	3M™ Dirt Trap Material 28 in Floor Applicator, 1 per case
36866	3M™ Dirt Trap Material 28 in Roller Wall Applicator, 1 per case

Compounds, Polishes & Pads



36060



06068



05752



06094



33279

Part No.	Description
36060	3M™ Perfect-It™ EX Rubbing Compound, Quart, 6 per case
36061	3M™ Perfect-It™ EX Rubbing Compound, Gallon, 4 per case
06094	3M™ Perfect-It™ EX Machine Polish, Quart, 6 per case
06095	3M™ Perfect-It™ EX Machine Polish, Gallon, 4 per case
06068	3M™ Perfect-It™ EX Ultrafine Machine Polish, Quart, 6 per case
06069	3M™ Perfect-It™ EX Ultrafine Machine Polish, Gallon, 4 per case
36064	3M™ Perfect-It™ 1 Finishing Material, Quart, 6 per case
36065	3M™ Perfect-It™ 1 Finishing Material, Gallon, 4 per case
33287	3M™ Perfect-It™ Wool Compounding Pad, 6 inch, 6 per case
33288	3M™ Perfect-It™ Low Lint Compound Pad, 6 inch, 6 per case
33284	3M™ Perfect-It™ Foam Compound Pad, 6 inch, 6 per case
05753	3M™ Perfect-It™ Wool Compound Pad, 9 inch, 6 per case
33279	3M™ Perfect-It™ Low Lint Compound Pad, 9 inch, 6 per case
05706	3M™ Perfect-It™ Foam Compound Pad, 8 inch, 6 per case
33285	3M™ Perfect-It™ Foam Polishing Pad, 6 inch, 6 per case
05707	3M™ Perfect-It™ Foam Polishing Pad, 8 inch, 6 per case
33286	3M™ Perfect-It™ Ultrafine Foam Polishing Pad, 6 inch
05708	3M™ Perfect-It™ Ultrafine Foam Polishing Pad, 6 per case
33292	3M™ Perfect-It™ 1 Foam Finishing Pad, 6 in, Quick Connect, 6 per case
33291	3M™ Perfect-It™ 1 Foam Finishing Pad, 8 in, Quick Connect, 6 per case
05551	3M™ Hookit™ Clean Sand Painters Back Up Pad, 6 inch, 10/cs
05777	3M™ Hookit™ Soft Interface Pad, 6 × 1/2 × 3/4 inch, 10 pads per case
06016	3M™ Perfect-It™ Detailing Cloth Yellow, 6/pack
06020	3M™ Perfect-It® III Auto Detailing Cloth, Blue, 6/6, 6 pack
06082	3M™ Inspection Spray, Gallon, 4 per case
05752	3M™ Quick Connect Adaptor, 10 per case
33271	3M™ Quick Connect Adaptor, 14 mm, 10 per case
29940	Festool Rotary Polisher SHINEX RAP 150-14 FE, 1 per case

Professional Detailing



D12005



D20120



D11601

Part No.	Description
D10601	Meguiar's™ Pro Fiber Rinse And Tannin Stain Remover (1-Gallon), 4 per case
D11601	Meguiar's™ Pro Protein Stain Remover (1-Gallon), 4 per case
M10501	Meguiar's™ Ultra Cut Compound (Gallon), 4 Per Case
M10532	Meguiar's™ Ultra Cut Compound (Quart), 6 Per Case
M10508	Meguiar's™ Ultra Cut Compound (8 Oz), 12 Per Case
M10001	Meguiar's™ Pro Speed Compound (1- Gallon), 4 Per Case
M10032	Meguiar's™ Pro Speed Compound (Quart), 6 Per Case
M20501	Meguiar's™ Ultra Finishing Polish (1-Gallon), 4 Per Case
M20532	Meguiar's™ Ultra Finishing Polish (Quart), 6 Per Case
M20508	Meguiar's™ Ultra Finishing Polish (8 Oz), 12 Per Case
M30564	Meguiar's™ Ultra Finishing Durable Glaze (64 Oz), 4 Per Case
M30516	Meguiar's™ Ultra Finishing Durable Glaze (16 Oz), 6 Per Case
WRSBP	Meguiar's™ Soft Buff Rotary Soft Backing Plate, 6 Per Case
WRBP	Meguiar's™ Soft Buff Rotary Backing Plate, 6 Per Case
WRWC8	Meguiar's™ Soft Buff Rotary Wool Cutting Pad 8", 6 Per Case
WRWHC7	Meguiar's™ Soft Buff Rotary Wool Heavy Cutting Pad 7", 6 Per Case
WRFP7	Meguiar's™ Soft Buff Rotary Foam Polishing Pad 7", 6 Per Case
DFC6	Meguiar's™ Soft Buff Da Foam Cutting Disc 6", 6 Per Case
DFF6	Meguiar's™ Soft Buff Foam Finishing Disc 6", 6 Per Case
DFP6	Meguiar's™ Soft Buff Da Foam Polishing Disc 6", 6 Per Case
DBP6	Meguiar's™ Da Backing Plate 6", 6 Per Case
DBP5	Meguiar's™ Da Backing Plate 5", 6 Per Case
DFC5	Meguiar's™ Soft Buff Da Foam Cutting Disc 5", 6 Per Case
DFP5	Meguiar's™ Soft Buff Da Foam Polishing Disc 5", 6 Per Case
DFF5	Meguiar's™ Soft Buff Foam Finishing Disc 5", 6 Per Case
DMCKIT5	Meguiar's™ Da Microfiber Correction System Kit 5, 4 per case

Professional Detailing

Part No.	Description
DMCKIT6	Meguiar's™ Da Microfiber Correction System Kit 6, 4 per case
DMF5	Meguiar's™ Da Microfiber Finishing Disc 5" (2 Pack), 6 per case
DMF6	Meguiar's™ Da Microfiber Finishing Disc 6" (2 Pack), 6 per case
MT300	Meguiar's™ Professional Dual Action Polisher, 1 Per Case
M3416	Meguiar's™ Final Inspection, 6 Per Case
D11105	Meguiar's™ Shampoo Plus (5-Gallon), 1 Per Case
D12001	Meguiar's™ Glass Cleaner Concentrate (Gallon), 4 Per Case
D12005	Meguiar's™ Glass Cleaner Concentrate (5-Gallon), 1 Per Case
D20120PK12	Meguiar's™ Glass Cleaner Bottle (12 Pack), 12 Per Case
D10105	Meguiar's™ All Purpose Cleaner (5-Gallon), 1 Per Case
D20101PK12	Meguiar's™ All Purpose Cleaner Bottle (12 Pack), 12 Per Case
D10805	Meguiar's™ Super Degreaser (5-Gallon), 1 Per Case
D20108PK12	Meguiar's™ Super Degreaser Bottle (12 Pack), 12 Per Case
D14005	Meguiar's™ Wheel Brightener (5-Gallon), 1 Per Case
D20140PK12	Meguiar's™ Wheel Brightener Bottle (12 Pack), 12 Per Case
D14305	Meguiar's™ Non Acid Wheel And Tire Cleaner (5 Gallon), 1 Per Case
D20143PK12	Meguiar's™ Secondary Bottle - Non Acid Wheel And Tire Cleaner, 12 Per Case
D14901	Meguiar's™ Quick Interior Detailer - (1-Gallon), 4 Per Case
D20149PK12	Meguiar's™ Secondary Bottle - Quick Interior Detailer (12 Pack), 12 Per Case
D15505	Meguiar's™ Last Touch Detailing Spray (5-Gallon), 1 Per Case
D20155PK12	Meguiar's™ Last Touch Bottle (12 Pack), 12 Per Case
D16005	Meguiar's™ All Season Dressing (5-Gallon), 1 Per Case
D20160PK12	Meguiar's™ All Season Dressing Bottle (12 Pack), 12 Per Case
D16105	Meguiar's™ Silicone Free Dressing (5-Gallon), 1 Per Case
D20161PK12	Meguiar's™ Silicone-Free Dressing Bottle (12 Pack), 12 Per Case
D17005	Meguiar's™ Hyper Dressing (5-Gallon), 1 Per Case
D20170PK12	Meguiar's™ Hyper-Dressing Bottle (12 Pack), 12 Per Case
D17105	Meguiar's™ Water Based Dressing (5- Gallon), 1 Per Case
D20171PK12	Meguiar's™ Water Based Dressing Secondary Bottle (32 Oz) (12 Pack), 12 Per Case
D20100PK12	Meguiar's™ Generic Spray Bottle (12 Pack), 12 Per Case
D110542	Meguiar's™ Chemical Resistant Sprayer, 12 Per Case
D9916	Meguiar's™ Dispenser Bottle (16 Oz), 12 Per Case
MDFAUCET	Meguiar's™ Md Faucets For 5 Gallon Containers, 1 Per Case
C2000	Meguiar's™ Mirror Glaze Professional Detailing Clay (Mild), 12 Per Case
X3002	Meguiar's™ Microfiber Wash Mitt, 6 Per Case
X3003	Meguiar's™ Grit Guard, 12 Per Case
X2000	Meguiar's™ Water Magnet Microfiber Drying Towel (22"X30"), 6 Per Case
DMS6000	Meguiar's™ Professional Metering System, 1 Per Case

This image shows a single sheet of white paper with horizontal ruling lines. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.

Notes

This image shows a blank sheet of white paper with horizontal ruling lines. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.



Visit www.3MCollision.com/HDTruck for more SOPs & videos

Heavy Duty Trucks

3M Automotive Aftermarket Division Standard Operating Procedures (SOP)

From metal and plastic repair, to sanding, paint finishing and truck clean-up, 3M has the products and repair processes for you. Feel confident your repair is done professionally and efficiently using our Standard Operating Procedures. These procedures will help you consistently produce quality, time-proven solutions for any of your collision repair needs. For Standard Operating Procedures, visit our website at 3MCollision.com/HDTruck.



Automotive Aftermarket Division
3M Center, Building 223-6N-01
St. Paul, MN 55144 USA

Phone 1-877-666-2277
Web 3MCollision.com



/3MCollision



/3MCollision



/3M_Collision



/3MAutobodyRepair

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If the 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

3M, Accuspray, Cubitron, Hookit, PPS, Perfect-It, Platinum, Roloc, Scotch, Speedglas, Stikit and Trizact are trademarks of 3M Company. Please recycle. Printed in USA. © 3M 2017. All rights reserved. (Rev. 08/17)