

3M Versaflo" NIOSH

3M[™] Versaflo[™] TR-800 Intrinsically Safe Powered Air Purifying Respirator

The new standard in intrinsically safe respiratory protection.

#3MScienceOfSafety

3M Versaflo



Personal protection that helps minimize the risk of fire or explosion.

The TR-800 is a PAPR blower UL-certified with an intrinsically safe (IS) rating of Division 1: IS Class I, II, III; Division 1 (includes Division 2) Groups C, D, E, F, G; T4, under the most current standard (UL 60079, 6th Edition, 2013).

Whenever the job takes your people into a potentially explosive area – whether from flammable gases and liquids or combustible dust – ignition from an electrical source could trigger a disaster.

Now, with the introduction of the **3M[™] Versaflo[™] TR-800 Powered Air Purifying Respirator** (PAPR), you can give the people in your care a high level of respiratory protection and help minimize the risk of fire or explosion.

As part of the 3M Versaflo family, when the TR-800 is combined with Versaflo headtops, belts, and other accessories, it becomes part of a NIOSH-approved respirator system featuring: multiple speeds, audible and visual alarms and the ability to work with a wide variety of cartridges.

Advanced features that help make the 3M[™] Versaflo[™] TR-800 Powered Air Purifying Respirator stand above the rest.



Innovative Materials 3M-patent pending material capable of meeting current IEC/ UL 60079 material properties requirement while still meeting aging, conditioning and drop test requirements for IS products



Battery Protection / Battery features bumpers to help absorb impact

A truly global respirator platform

The TR-800 will be launched globally, which gives multinational customers the option to standardize on one product platform with both NIOSH and CE versions available.

Designed for improved worker comfort, convenience and control.

Keep the air flowing – Multi-speed blower functions at altitudes up to 16,000 feet. Battery offers long run time and charges quickly, achieving 90% charge in approximately 3.5 hours.

More options for more tasks – Choose from particulate filters or gas and vapor combination cartridges for protection in a variety of environments.

Work at your own speed - Multiple airflow rates put you in control of your comfort.

Battery:

- Approximately 750 full charge/discharge cycles.
- Built in charge level indicator.
- Mechanical attachment of battery to help prevent battery removal during use.



Work with ease – Intuitive, colored touchpoints plus visual and audible lowflow indicators help make the TR-800 easy to use.

Easy Identification

Bright yellow touchpoints to differentiate from non-IS versions of Versaflo Product Family

Secure Battery Attachment

Mechanical attachment of battery to help prevent battery removal and spark risk during use per IEC/UL 60079



3M[™] Versaflo[™] TR-800 Intrinsically Safe Powered Air Purifying Respirator

The new standard of protection for hazardous environments.

Interchangeable components enable you to build a customized PAPR system to help you meet the needs of your specific application.

Whether you're mixing and granulating compounds in a pharmaceutical facility or working with combustible gases in the oil and gas industry, the TR-800 motor blower is built for environments where intrinsically safe (IS) equipment is essential. These types of environments may be found in industries such as:

- Food production
- Chemical handling
- Oil and gas refining
- Automotive and industrial paint spraying
- Pharmaceutical manufacturing



- Fully submersible* product features a smooth design surface that's quick and easy to clean.
- Ergonomically designed for greater movement in tight work spaces, such as overhauling and/ or cleaning reactors and tanks.
- Designed for work areas requiring Intrinsically Safe (IS) rated equipment.

Oil and Gas



- Ergonomically designed for greater movement in tight work spaces during plant turnaround and maintenance activities.
- Simplifies PPE compatibility challenges for contractors with a solution designed to provide integrated respiratory, eye, face, and head protection.
- Designed for plant areas where work permits require Intrinsically Safe (IS) rated equipment.

Paint Spray



- Ergonomically designed for greater movement in paint booth. Unlike supplied air systems, a PAPR does not require that you be connected to your air source by an air line, leaving you free to go where you need to go.
- Multiple NIOSH-approved headgear options available with TR-800 to meet the needs of paint spray applications, including the Respiratory Faceshield Assembly M-206 and the Painter's Hood Assembly S-757.
- Fully submersible* product features a smooth design surface that's quick and easy to clean.



RECOMMENDED FOR:

Paint spray booths or other enviroments where IS equipment is required.

Complete PAPR kits available.

Painter's Kit TR-800-PSK

INCLUDES:

- M-206 Respiratory Faceshield Assembly
- BT-20L Breathing Tube
- TR-6510N (OV/HE) Cartridge
- TR-641N Single Station Battery Charger •
- BT-922 Breathing Tube Cover
- TR-802N Intrinsically Safe PAPR Unit
- TR-830 Intrinsically Safe Battery
- TR-838 Battery Attachment Tool
- TR-627 Easy Clean Belt
- TR-6500 Filter Cover •
- TR-971 Airflow Indicator
- TR-653 Storage and Cleaning Kit

RECOMMENDED FOR:

cleaning of the PAPR unit is necessary.

Pharmaceutical and other industries where frequent

RECOMMENDED FOR:

Oil and gas refineries, chemical manufacturing and other enviroments where IS equipment is required

Easy-Clean Kit TR-800-ECK

INCLUDES:

- S-433L Hood with Integrated Head Suspension
- BT-30 Length Adjusting Breathing Tube
- TR-6710N (HE) Filter
- TR-641N Single Station Battery Charger
- BT-922 Breathing Tube Cover
- TR-802N Intrinsically Safe PAPR Unit
- TR-830 Intrinsically Safe Battery
- TR-838 Battery Attachment Tool
- TR-627 Easy Clean Belt
- TR-6700 Filter Cover
- TR-6600 Prefilter (X2) •
- TR-662 Spark Arrestor (X2) •
- TR-653 Storage and Cleaning Kit
- TR-971 Airflow Indicator

Heavy Industry Kit TR-800-HIK

INCLUDES:

- M-307 Respiratory Hard Hat Assembly with Premium Visor and Faceseal
- TR-802N Intrinsically Safe PAPR Unit
- TR-830 Intrinsically Safe Battery ٠
- TR-838 Battery Attachment Tool •
- BT-30 Length Adjusting Breathing Tube
- TR-626 High Durability Belt
- TR-6530N OV/AG/HE Cartridge
- TR-6500 Filter Cover
- TR-641N Single Station Battery Charger Kit
- TR-971 Airflow Indicator
- BT-926 High Temperature Breathing Tube Cover
- TR-6600 Prefilter (x2)
- TR-662 Spark Arrestor (x2) •
- TR-653 Storage and Cleaning Kit

	Product	SKU	UPC
	3M™ Versaflo™ TR-802N PAPR Motor/Blower, Intrinsically Safe	70071730025	00076308942427
	3M™ Versaflo™ TR-830N Battery, Intrinsically Safe	70071697117	00076308942434
	3M™ Versaflo™ TR-838 Battery Attachment Tool	70071697125	00076308942441
	3M™ Versaflo™ TR-851 Filter Latch Assembly	70071697133	00076308942458
	3M™ Versaflo™ TR-813N Assembly, Heavy Duty	70071697141	00076308942465
	3M™ Versaflo™ TR-814N Assembly, Easy Clean	70071697158	00076308942472
PLAP	3M™ Versaflo™ TR-800-PSK Paint Spray Kit	70071697166	00076308942489
***	3M™ Versaflo™ TR-800-ECK Easy Clean Kit	70071697174	00076308942496
AND AND	3M™ Versaflo™ TR-800-HIK Heavy Industry Kit	70071697182	00076308942502

For more information, visit us at 3M.com/versaflo800



3M General Offices 3M Center, Building 235-2W-1000 St. Paul, MN 55144-1000 3M.com/versaflo



AWARNING

These respirators help reduce exposures to certain airborne particulates. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. Misuse may result in injury, illness or death. For correct use, consult supervisor and User Instructions, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.

3M Canada Company PSD P.O. Box 5757 London, Ontario N6A 4T1 Canada

For More Information

Technical Assistance in US 1-800-243-4630 Technical Assistance in Canada 1-800-267-4414 www.3M.com/workersafety

3M and Versaflo are trademarks of 3M Company, used under license in Canada. Please recycle. Printed in USA. © 2018 3M. All rights reserved. 70-0716-7274-8