



**3M** Science.  
Applied to Life.™

3M™ Automotive Aftermarket Division

# New 3M™ Power Tools for Body Repair

Powerful, lightweight tools,  
designed to improve comfort  
and maximise efficiency.

► 3M™ Pistol Grip Disc Sander

The 3M™ Pistol Grip Disc Sander is a light-weight tool with the power to grind welds and the size to access small and hard-to-reach areas. Perfect for grinding and sanding applications with our 3M™ Cubitron™ II Fibre Roloc™ Discs.

- ▶ Maximum grinding efficiency with discs
- ▶ 3M™ Roloc™ Cubitron™ II
- ▶ Adaptable to 3M™ Roloc™ 50 and 75 mm discs
- ▶ Variable speed drive for greater comfort and precision



► 3M™ Cut-Off Wheel Tool

The 3M™ Cut-Off Wheel Tools deliver the performance you need when working with tough automotive substrates. When paired with 3M™ Cubitron™ II Cut-Off Wheels, technicians can slice through even high-strength steel and aluminium with clean, straight lines and minimal effort.

- ▶ Compact design for easy handling
- ▶ Non-slip composite material to guarantee comfort and operator safety




► 3M™ Mini File Belt Sander and File Belt Sander

The 3M™ File Belt Sanders allow technicians to access hard-to-reach areas and are great for spot weld removal, deburring, cleaning, and finishing.

- ▶ Removal of fast and precise welding points 3M™ Cubitron™ II Strips
- ▶ Swivel arm for easy accessibility and best comfort
- ▶ Available in 330 and 457 mm lengths



Choose the right product for the right application



**A Sectioning**



**3M™ Cubitron™ II**  
Cut-Off Wheels



**Cut-Off Wheel**

- ▶ Cutting metal, frame rails, exhaust pipes and rusted bolts
- ▶ Heavy stock removal

**B Spot Weld Removal**



**3M™ Cubitron™ II**  
Abrasive Belts



**Abrasive Belt**

- ▶ Spot weld removal
- ▶ Deburring
- ▶ Stripping
- ▶ Clean-up

**C Weld Grinding**



**3M™ Cubitron™ II**  
3M™ Roloc™ Discs



**Roloc™ Disc**

- ▶ Weld grinding
- ▶ Stripping
- ▶ Clean-up

# 3M™ Pistol Grip Disc Sander

Part number	Type	Diameter (mm)	Tr/mn	Power motor CV (W)	Weight (kg)	Length (mm)
33577	Pneumatic	50 & 75	18,000	0.45 (336)	0.56	189

The grinder comes with a 50mm Roloc 3M™ tray and a 75mm tray

Speak to your local sales rep or 3M distributor and discover the most suitable solution for your needs

# 3M™ Cut-Off Wheel Tool

Part number	Type	Diameter (mm)	Tr/mn	Power motor CV (W)	Weight (kg)	Length (mm)
33579	Pneumatic	75	20,000	0.70 (522)	0.87	196

# 3M™ Mini File Belt Sander and File Belt Sander

Part number	Type	Diameter (mm)	Tr/mn	Power motor CV (W)	Weight (kg)	Length (mm)
33573	Pneumatic	10×330	17,000	0.65 (485)	0.94	320
33575	Pneumatic	13×457	17,000	0.65 (485)	0.98	385

3M offers you a wide range of products for your bodyshop.



Automotive Aftermarket Division  
3M United Kingdom PLC  
Tel: 0845 603 9714  
aadukenquiries@mmm.com  
www.3M.co.uk/bodyshop

Automotive Aftermarket Division  
3M Ireland  
Tel: (00) 353 1 216 0301  
Fax: (00) 353 1 280 3509

Please recycle. Printed in the UK. © 3M 2017. 3M, 3M Science. Applied to Life., Cubitron, Hookit and Precision-Shaped Grain are trademarks of the 3M company. All rights reserved. J367318. March 2017. AB004/17

