



WSS-M99P48-A3

Pressure Sensitive Adhesive Tape (Interior, Exterior and Underhood Applications)

Automotive Spec Testing

Technical Bulletin

November, 2016

3M tested the following adhesive tapes to the Automotive OEM Spec: WSS-M99P48-A3. The results of the testing are provided in the following information. Adhesives not listed on this document have not been tested to this spec.

3M™ Adhesive Transfer Tape 468MP
3M™ Scrim Reinforced Transfer Tape 97053

3M™ Adhesive Transfer Tape 6035PC
3M™ Low VOC Scrim Reinforced Transfer Tape 9801LVC

3M™ Adhesive Transfer Tape 9472LE
3M™ Double Coated Tape 99786

3M™ Double Coated Tape 9832 HL
3M™ Low VOC Double Coated Tissue Tape 99015LVC

Test	Test Condition / Environment	
180° Peel Adhesion 300mm / 12 inch per min	Initial	1 hour @ room temp 23°C / 73°F
	Heat Aged	168 hours @ 100°C / 212°F
	Environmental Cycle	10 cycles 4 hours @ 100°C / 212°F 4 hours @ 38°C / 100°F 16 hours @ -40°

Adhesive	Test	SS	PP	ABS
468MP	As received	P	F	P
	Heat	P	P	P
	Cycle	P	P	P
9472LE	As received	P	P	P
	Heat	P	P	P
	Cycle	P	P	P
6035PC	As received	P	P	P
	Heat	P	P	P
	Cycle	P	P	P
98010 LVC	As received	P	P	P
	Heat	P	F	P
	Cycle	P	P	P

Adhesive	Test	SS	PP	ABS
97053	As received	P	P	P
	Heat	P	P	P
	Cycle	P	P	P
9832HL	As received	P	P	P
	Heat	P	P	P
	Cycle	P	P	P
99786	As received	P	P	P
	Heat	P	P	P
	Cycle	P	P	P
99015 LVC	As received	P	P	P
	Heat	P	F	P
	Cycle	P	P	P

P = Pass, F = Fail

Note: Data reported in this technical bulletin, for all test methods, is the average of three replicates using one typical lot of adhesive.

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

468MP Adhesive

Initial – 1 hour @ 23°C / 73°F						
468MP	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	1.04	95.02	Clean Peel	Pass
	PP		.34	31.06	Clean Peel	Fail
	ABS		.84	76.74	Clean Peel	Pass

Heat Aged – 168 hours @ 100°C / 212°F						
468MP	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement Max 25% loss from initial
	SS	PET	2.01	183.64	Cohesive	Pass
	PP		.31	28.32	Clean Peel	Pass
	ABS		.99	90.45	Clean Peel	Pass

Environmental Cycle – 10 cycles						
468MP	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS		2.06	188.21	Cohesive	Pass
	PP		.36	32.89	Clean Peel	Pass
	ABS		.72	65.78	Clean Peel	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

9472LE Adhesive

Initial – 1 hour @ 23°C / 73°F						
9472LE	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	.91	83.14	Clean Peel	Pass
	PP		1.29	117.86	Clean Peel	Pass
	ABS		1.32	120.60	Clean Peel	Pass

Heat Aged – 168 hours @ 100°C / 212°F						
9472LE	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.55	141.61	Clean Peel	Pass
	PP		1.01	92.28	Clean Peel	Pass
	ABS		1.43	130.65	60% Clean Peel /40% cohesive	Pass

Environmental Cycle – 10 cycles						
9472LE	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.50	137.05	Cohesive	Pass
	PP		1.10	100.50	Clean Peel	Pass
	ABS		1.41	128.82	Cohesive	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

97053 Adhesive

Initial – 1 hour @ 23°C / 73°F						
97053	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	.72	65.78	Clean Peel	Pass
	PP		.78	71.26	Clean Peel	Pass
	ABS		.80	73.09	Clean Peel	Peel

Heat Aged – 168 hours @ 100°C / 212°F						
97053	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.38	126.08	Cohesive	Pass
	PP		1.15	105.07	Cohesive	Pass
	ABS		1.34	122.43	Cohesive	Pass

Environmental Cycle – 10 cycles						
97053	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.26	115.12	Cohesive	Pass
	PP		1.04	95.02	Cohesive	Pass
	ABS		1.06	96.84	Cohesive	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

6035PC Adhesive

Initial – 1 hour @ 23°C / 73°F						
6035PC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	1.94	177.25	Cohesive	Pass
	PP		1.25	114.20	Clean Peel	Pass
	ABS		1.69	154.40	Clean Peel	Pass

Heat Aged – 168 hours @ 100°C / 212°F						
6035PC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	2.19	200.09	Cohesive	Pass
	PP		1.00	91.36	Clean Peel	Pass
	ABS		1.73	158.06	80% Clean Peel / 20% Cohesive	Pass

Environmental Cycle – 10 cycles						
6035PC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	2.10	191.86	Cohesive	Pass
	PP		1.09	99.59	Clean Peel	Pass
	ABS		1.52	138.87	Cohesive	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

99786 Adhesive

Initial – 1 hour @ 23°C / 73°F						
99786	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	1.13	103.24	Cohesive	Pass
	PP		.53	48.42	Clean Peel	Pass
	ABS		.92	84.05	Clean Peel	Pass

Heat Aged – 168 hours @ 100°C / 212°F						
99786	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.79	163.54	Cohesive	Pass
	PP		.54	49.34	Clean Peel	Pass
	ABS		.79	72.18	Clean Peel	Pass

Environmental Cycle – 10 cycles						
99786	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.76	160.80	Cohesive	Pass
	PP		.57	52.08	Clean Peel	Pass
	ABS		1.19	108.72	Clean Peel	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

9832HL Adhesive

Initial – 1 hour @ 23°C / 73°F						
9832HL	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	.85	77.66	Cohesive	Pass
	PP		.64	58.47	Clean Peel	Pass
	ABS		.83	75.83	Clean Peel	Pass

Heat Aged – 168 hours @ 100°C / 212°F						
9832HL	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	.26	23.75	Cohesive	Pass
	PP		.55	50.25	Clean Peel	Pass
	ABS		.85	77.66	Clean Peel	Pass

Environmental Cycle – 10 cycles						
9832HL	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	1.16	105.98	Cohesive	Pass
	PP		.58	52.99	Clean Peel	Pass
	ABS		.95	86.79	Clean Peel	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

98010LVC Adhesive

Initial – 1 hour @ 23°C / 73°F						
98010LVC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	1.11	101.41	Cohesive	Pass
	PP		1.07	97.76	Cohesive	Pass
	ABS		1.08	98.67	Cohesive	Pass

Heat Aged – 168 hours @ 100°C / 212°F						
98010LVC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.09	99.59	Cohesive	Pass
	PP		.55	50.25	Clean Peel	Fail
	ABS		1.23	112.38	Cohesive	Pass

Environmental Cycle – 10 cycles						
98010LVC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.04	95.02	Cohesive	Pass
	PP		1.10	100.50	Cohesive	Pass
	ABS		.82	74.92	Cohesive	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

99015LVC Adhesive

Initial – 1 hour @ 23°C / 73°F						
99015LVC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement 0.48 N/mm or 43.85 oz/in or cohesive failure
	SS	PET	1.08	98.67	Cohesive	Pass
	PP		.99	90.45	Clean Peel	Pass
	ABS		1.15	105.07	Clean Peel	Pass

Heat Aged – 168 hours @ 100°C / 212°F						
99015LVC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.45	132.48	Cohesive	Pass
	PP		.69	63.04	Clean Peel	Fail
	ABS		1.30	118.77	Cohesive	Pass

Environmental Cycle – 10 cycles						
99015LVC	Substrate	Backing	AVG Peel N/mm	AVG Peel oz/in	Observation	Requirement max 25% loss from initial
	SS	PET	1.23	112.38	Cohesive	Pass
	PP		1.36	124.25	Cohesive	Pass
	ABS		1.15	105.07	Cohesive	Pass

WSS-M99P48-A3: Foam Performance, Pressure Sensitive Adhesive Tape, Automotive Spec Testing

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.

If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001: 2000 standards.



Industrial Adhesives and Tapes Division
Converter Markets
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-7427 • 651-778-4244 (Fax)
www.3M.com/converter

3M is a trademark of 3M Company..
© 3M 2016
E70-0713-4628-5 (11/16)