

**3M** Science.  
Applied to Life.™

# Energize your wrap options.

Meet the NEW 3M Print Wrap Film family: IJ180mC and 480mC films,  
featuring Comply™ Adhesive with micro technology (mC).

More options. More design flexibility. Faster installs. Give your portfolio a high-octane upgrade.





# We added micro technology. You add adrenaline.

The same amazing printability, conformability, lifting resistance, film handling and removability you love about IJ180 and 480 are experienced in IJ180mC and SV or LX480mC. And now, Comply™ Adhesive with micro technology provides an even easier, faster and better-looking installation. What a rush!



## Optimized initial tack.

It's not too high and not too low. It's just right.



## Non-visible Comply™ Adhesive pattern.

Prevents lines in your finished graphic so all you'll see are smooth results.



## Fine-tuned slideability.

Easily position and reposition panels — light pressure holds them in place.



## Easier liner release.

The liner comes off easier than ever — great for large panels and in warm temps.





# Accelerate installs.

## 3M™ Print Wrap Film IJ180mC-10

Turbocharge your performance with a wrap film that installs even faster and looks even better.

- ▶ Slideability and initial tack optimized for wraps
- ▶ Comply™ Adhesive with micro technology provides excellent air release for smooth results
- ▶ Optimized performance on vehicles with compound curves and corrugations
- ▶ Highly durable film with 10-year durability and backed with the 3M™ MCS™ Warranty



# Max design options.

## 3M™ Print Wrap Film IJ180mC-114

Mix printed images with clear areas to create ultra-cool, never-been-done-before designs by letting the original vehicle color show through.

- ▶ Transparent wrapping film
- ▶ Design options multiplied
- ▶ Combine different designs into one graphic
- ▶ Comply™ Adhesive with micro technology provides excellent air release for smooth results



▲ Green vehicle colour shows through film and is part of the design.





▲ Make waves with a high-tech, metallic sheen.

## Add wow factor.

### 3M™ Print Wrap Film IJ180mC-120

Introducing the FIRST printable metallic wrap film to give vehicles a high-tech, attention-grabbing finish.

- ▶ Give graphics a shimmer not possible with inks or overlaminates
- ▶ Metallic finish adds a unique effect to your customer's design
- ▶ Comply™ Adhesive with micro technology provides excellent air release for smooth results
- ▶ Optimized performance on vehicles with compound curves and corrugations



3M™ Print Wrap Films

# Elevate performance.


## 3M™ Envision™ Print Wrap Films SV480mC and LX480mC

This ultra-versatile, non-PVC film gives you excellent print quality, plus a breakthrough boost in attributes with a sustainability edge.

- ▶ Conformable on demand — even in deep corrugations and on textured surfaces
- ▶ Installs and removes even easier — in a broader range of ambient temperatures
- ▶ Comply™ Adhesive with micro technology provides excellent air release for smooth results
- ▶ Greater tensile strength — provides faster removals
- ▶ Non-PVC for greener solution







## GREENGUARD Gold Certified

3M™ Envision™ Wrap Films and Overlaminates have earned the prestigious GREENGUARD Gold Certification. You can offer a greener graphic solution that will contribute to healthier indoor air quality.

### LX480mC

Designed for use with latex and UV printers.

### SV480mC

Designed for use with solvent/eco-solvent and UV printers.

Available now in 1.52m width.

## 3M™ Print Wrap Films

### All your portfolio needs fulfilled.

3M™ Print Wrap Films	What Makes It Awesome	Film Type	Applications	Conformability and Lifting Resistance	Max Durability
IJ180mC-10	<ul style="list-style-type: none"> <li>▶ Optimised initial tack</li> <li>▶ Non-visible Comply™ Adhesive pattern</li> <li>▶ Fine-tuned slideability</li> <li>▶ Easier liner release</li> <li>▶ Faster installs</li> </ul>	Cast vinyl film	General vehicle and boat wrap film	Compound curves, rivets and corrugations	10 years
IJ180mC-114	<ul style="list-style-type: none"> <li>▶ Printable transparent wrapping film</li> <li>▶ Combine different designs into one graphic</li> <li>▶ Create subtle designs that let vehicle colour show through</li> <li>▶ Design options multiplied</li> </ul>	Cast vinyl film	General vehicle and boat wrap film	Compound curves, rivets and corrugations	10 years
IJ180mC-120	<ul style="list-style-type: none"> <li>▶ Printable metallic wrap film for an edgier look</li> <li>▶ Adding a shiny effect on a printed metallic graphic for the WOW factor</li> <li>▶ Unique film offering many more possibilities for your customer</li> </ul>	Cast vinyl film	General vehicle and boat wrap film	Compound curves, rivets and corrugations	10 years
SV480mC and LX480mC	<ul style="list-style-type: none"> <li>▶ Highly conformable on demand</li> <li>▶ Installs and removes even easier — in a broader range of ambient temperatures</li> <li>▶ Greater tensile strength — provides faster removals</li> <li>▶ 100% printer compatible</li> <li>▶ Non-PVC for greener solution</li> </ul>	High-performance non-PVC	Vehicle and boat wrap film including the most challenging and extreme wraps	Compound curves, rivets and corrugations, deep channels	12 years

All above mentioned products come with Comply™ Adhesive with micro technology for excellent air release and Controltac™ technology for easy slideability.



3M™ MCS™ Warranty

All our premium films come with the 3M™ MCS™ Warranty — the most comprehensive finished graphic warranty in the industry.

For warranty information, visit [3M.com/GraphicsWarranties](http://3M.com/GraphicsWarranties).



**3M United Kingdom PLC**  
Commercial Solutions  
3M Centre, Cain Road  
Bracknell, Berkshire RG12 8HT

E-mail: [commgraphics.uk@mmm.com](mailto:commgraphics.uk@mmm.com)  
Internet: [www.3M.com/uk/graphicsolutions](http://www.3M.com/uk/graphicsolutions)

**3M United Kingdom PLC**  
Commercial Solutions  
Customer Office  
3M House, 28 Great Jackson Street  
Manchester M15 4PA

E-mail: [commgraphics.uk@mmm.com](mailto:commgraphics.uk@mmm.com)  
Internet: [www.3M.com/uk/graphicsolutions](http://www.3M.com/uk/graphicsolutions)

**3M Ireland Limited**  
Commercial Solutions  
The Iveagh Building, The Park  
Carrickmines  
Dublin 18

E-mail: [commgraphics.uk@mmm.com](mailto:commgraphics.uk@mmm.com)  
Internet: [www.3M.com/uk/graphicsolutions](http://www.3M.com/uk/graphicsolutions)

Protect your wraps with 3M Overlaminates, engineered and tested to help provide the performance and beauty you create with 3M™ Print Wrap Films.

- ▶ 3M™ Scotchcal™ Gloss or Matte Overlaminates (8518, 8520)
- ▶ 3M™ Envision™ Gloss Wrap Overlaminates 8548G or Luster 8549L

For more information, visit [3M.eu/IJ180mC](http://3M.eu/IJ180mC).

© 3M 2017. All rights reserved. 3M, Comply, Controltac, Envision, Scotchcal and MCS are trademarks of 3M. Please recycle. MAR 2017

FRESCA-WE-UK/1