

3M Science.
Applied to Life.™



3M™ Cavity Wax Plus and Applicator Wand Kit



With today's ever evolving substrates being used in automotive construction, industry organisations and OEMs alike specify the use of cavity wax to prevent corrosion.

3M™ Cavity Wax Plus 08852

Non-hardening corrosion protection for internal cavities in a convenient aerosol can.

- ▶ Corrosion protection for inner body panels, frame rails and structural enclosures.
- ▶ Provides consistent and uniform protection for your repair by delivering the right amount of flow and wicking.
- ▶ Eliminates the inconvenience of decanting into dispensers.
- ▶ Provides access to inner body structures with tight tolerances.

3M™ Cavity Wax Plus Applicator Wand Kit 8851WK


Protect hard-to-reach places.

- ▶ Comes with three lengths to access hard-to-reach places.
- ▶ The 360-degree tip provides a uniform spray pattern to maximise coverage with each application.
- ▶ 20cm tube delivers a powerful stream of material to flood joints and seal them from corrosive elements.

| Part no. | Size | Product | Case qty. |
|----------|---------------------------|---|-----------|
| 8851WK | 20cm, 61cm and 86cm tubes | 3M™ Cavity Wax Plus Applicator Wand Kit | 12 |
| 08852 | 532ml aerosol | 3M™ Cavity Wax Plus 08852 | 4 |

1,500 hours salt spray results

Actual panel test results ASTM B117 1,500 hours.



Without protection



3M™ Cavity Wax Plus 08852 (3 coats)

Learn more about our complete system of body repair solutions at www.3M.co.uk/bodyshop



Automotive Aftermarket Division

3M United Kingdom PLC
0845 603 9714
aadenquiries@mmm.com
www.3M.co.uk/bodyshop

3M Ireland
Tel: (00) 353 1 216 0301
Fax: (00) 353 1 280 3509

Please recycle. Printed in the UK. © 3M 2017.
3M is a trademark of the 3M company.
All rights reserved. J387214. AB011/17

