



# 3M™ Semi-Tight Buffer Clamp Tech Tip

## For use with 3M™ Crimplok™+ Connectors, 3M™ Fibrlok™ Splices, 3M™ Hot Melt Connectors and 3M™ No Polish Connectors


1. Fiber preparation: for 3M™ Crimplok™+ Connectors, 3M™ Fibrlok™ Splices, 3M™ Hot Melt Connectors, and 3M™ No Polish Connectors, the buffer extends 300 mm ± 50 mm from exit edge of Semi-Tight Buffer Clamp (prior to stripping & cleaving).



2. Remove 40–45 mm of semi-tight outer tube.



3. Strip 250 µm acrylate coating as close to the outer tube as possible.



4. Follow standard buffer position and cleave length requirements for each connector or splice.

**\*Note: For 3M Fibrlok Splices use 2 clamps, one for each side of the splice.**

**\*Note: Photos not to scale.**

3M, Fiblok, and Crimplok are trademarks of 3M Company.

**Important Notice**

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

**Warranty; Limited Remedy; Limited Liability.**

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



**Communication Markets Division**

6801 River Place Blvd.  
Austin, TX 78726-9000

Phone 1-800-426-8688  
Web [www.3M.com/Telecom](http://www.3M.com/Telecom)

Please recycle. Printed in USA © 3M 2017.  
All rights reserved. 78-0015-4356-6