



Double Coated Tapes with Adhesive 300MP

9687C • 9693

Technical Data

July, 2011

Product Description

3M™ Double Coated Tapes with 3M™ Adhesive 300MP feature a thin polyester film for dimensional stability and improved handling with ease of die cutting and laminating. 3M adhesive 300MP offers excellent adhesion to many plastics and good shear strength and provides exceptional temperature and chemical resistance that withstands tough application environments. For information on storage and usage tips regarding the 3M adhesive 300MP products, please refer to technical bulletin, *3M™ Laminating Adhesives 300MP – Tips for storing, handling and slitting in roll form* (70-0709-3905-6).

Construction

Product Number	Faceside ¹ Adhesive Type/ Thickness	Carrier Type/ Thickness	Backside ¹ Adhesive Type/ Thickness	Liner Color, Type, Print	Liner Caliper	Total Tape Thickness (w/o liner)
3M™ Double Coated Tape 9687C	300MP/ 0.0023" (0.058mm)	Clear PET ² 0.002" (0.051mm)	300MP/ 0.0077" (0.20mm)	Clear, PET, no print	0.002" (0.051mm)	0.012" (0.30mm)
3M™ Double Coated Tape 9693	300MP/ 0.0015" (0.038mm)	Clear PET 0.0005" (0.013mm)	300MP/ 0.0015" (0.038mm)	Clear, PET, no print	0.002" (0.051mm)	0.0035" (0.089mm)

Note 1: Faceside adhesive is on the interior of the roll.

The caliper listed is based on a calculation from manufacturing controlled adhesion coat weights using a density of 1.012 g/cc.

Backside adhesive is on the exterior of the roll.

Note 2: PET (Polyester).

3M™ Double Coated Tapes with Adhesive 300MP

9687C • 9693

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product Number	3M™ Double Coated Tape 9687C	3M™ Double Coated Tape 9693
Adhesion to stainless steel ASTM D3330 - 90 degree	Oz/in (N/100mm)	Oz/in (N/100mm)
- 15 minute RT	50 (55)	37 (40)
- 72 hour RT	53 (58)	61 (67)
- 72 hour 158°F (70°C)	104 (114)	67 (73)
ASTM D3330 - 180 degree, 2 mil Al foil		
- 72 hour RT	50 (55)	-
ASTM D3330 - 180 degree, 2 mil polyester, stainless steel		
- 72 hour RT	-	70 (77)
ASTM D3330 - 90 degree, 2 mil Al foil, 72 hour RT		
ABS	51 (56)	51 (56)
Polyester	51 (56)	61 (67)
Polycarbonate	62 (68)	-
Shear Strength - ASTM D3654 modified - (.5 inch ² sample size)		
1000 grams at 72°F (22°C)	4770 minutes	10,000 minutes
500 grams at 158°F (70°C)	—	7076 minutes
Less Bonding -	Push out test using 500N load cell with 15mm diameter pusher. Test Results - Average load (N) 106.24975 for 3M tape 9693.	
Relative High Temperature Operating Ranges:		
Long Term (days, weeks)	200°F (93°C)	200°F (93°C)
Short Term (minutes, hours)	300°F (149°C)	(149°C)

Available Sizes

Roll length, width, slitting tolerance, core size.		
Available Lengths (Subject to minimum order requirements)		
Maximum Length		
1/2" to 63/64"	-	180 yd. (164 m)
3" to 48"	-	-
1" to 54"	360 yd. (329 m)	360 yd. (329 m)
Available Widths		
Minimum	4" (102 mm)	1/2" (12.7 mm)
Maximum	54" (1372 mm)	54" (1372 mm)
Normal Slitting Tolerance	±1/32" (0.8 mm)	±1/32" (0.8 mm)
Core Size	6.0" (152.4 mm)	3.0" (76.2 mm)

3M™ Double Coated Tapes with Adhesive 300MP 9687C • 9693

Features

- 3M™ Double Coated Tape 9693 clear polyester carrier provides dimensional stability and improved handling with ease of die cutting and lamination compared to adhesive transfer tapes.

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improves bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.*

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

*Carefully read and follow the manufacturer’s precautions and directions for use when working with solvents. These cleaning recommendations may not be compliant with the rules of certain Air Quality Management Districts in California; consult applicable rules before use.

Application Ideas

- Cellular phone lens attachment
- Foam Lamination
- Nameplates
- Appliques
- Decorate Trim
- Thermal and sound dampening applications in the electronics and appliance industry.

Liner Configure Guide	General purpose steel rule die cutting	58# PCK (Polycoated Kraft)
	Steel rule cutting many nameplates on common sheet	83# PCK
	Kiss cutting, steel rule	83# PCK
	Rotary die-cutting	PET
	Selective die-cutting (cut adhesive before laminate)	Double-lined
	Thermoforming	HDPE (High density Polyethylene)
	Part inspection	HDPE, PET
	Embossed metal parts	White PP (polypropylene), HDPE
	Metal parts (punch press)	PET

Adding Liners to 3M™ Double Coated Tapes with 3M™ Adhesive 300MP

1. Rotary processing, tape only, on a densified (outside of #4994) kraft liner. In this process the tape waste will stay with the 83# PCK liner, leaving adhesive die-cuts dispensable from the #4994 (densified kraft) liner.
2. Rotary processing for finished parts. Current process limitations prevent the supply of 3M™ Adhesive 300MP on a DK liner.

3M™ Double Coated Tapes with Adhesive 300MP

9687C • 9693

Application Equipment To apply adhesives in a wide web format, lamination equipment is required to ensure acceptable quality. To learn more about working with pressure-sensitive adhesives please refer to technical bulletin, *Lamination Techniques for Converters of Laminating Adhesives* (70-0704-1430-8).

For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

Storage Store in original cartons at 70°F (21°C) and 50% relative humidity.

Shelf Life If stored under proper conditions, product retains its performance and properties for two years from date of manufacture.

Certification/ Recognition **MSDS:** 3M has not prepared a MSDS for these products which are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the products should not present a health and safety hazard. However, use or processing of the products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

TSCA: These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.

Technical Information The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2008

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2008 standards.



Industrial Adhesives and Tapes Division Converter Markets

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-223-7427 • 651-778-4244 (fax)
www.3M.com/converter



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2011 70070939254 (7/11)