



Learn how 3M's advanced technologies can help you weather all kinds of conditions.

Visit [3M.com/construction](https://www.3m.com/construction) or contact your 3M representative at 1-866-513-4026.

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-866-513-4026
www.3m.com/construction

© 3M 2022. All rights reserved.
70-0716-9845-3

**Protect your project
with all-weather acrylic
flashing and seaming tapes**


Let's Build Smarter.

Flexible solutions for Type 5 construction

Apply 3M acrylic flashing tapes in cold, hot and damp conditions. Thin, flexible material elongates up to 700% to seal tightly around uneven surfaces, even when penetrated with nails and staples.



High-tack acrylic adhesive sticks to damp surfaces



Application temperature of 0°F to 150°F (-18°C to 66°C) without a primer




Compatible with most sealants

3M™ Deck and Joist Flashing Tape 8047

Give decks a longer life

Waterproof membrane that helps prevent rotting by creating a moisture barrier for deck stringers, joists, posts and ledger boards. It also helps prevent corrosion of metal that is not designed to come in contact with treated lumber.

Available in 3" and 12" widths



3M™ All Weather Flashing Tape 8067

Protect windows, doors and other openings

Extremely flexible membrane seals around nails, staples and uneven surfaces. The thin design prevents tape buildup on overlaps and corners, making siding and window installation easier. Split liner allows easy tape positioning. Meets AAMA 711-05 and ICC Division 7, Evaluation ESR-2797.

Available in 2", 3", 4", 6", 9" and 12" widths



3M™ Sheathing Tape 8087CW

Seal house wrap seams and poly sheathing

Pressure-sensitive acrylic adhesive bonds to house wraps, poly sheathing and polystyrene in extremely cold, hot or humid conditions. Compliant with U.S. and Canadian building codes.

Red tape available in 1.88", 2.36", 2.83" and 3.89" widths

White tape available in 1.88" width



Extend the longevity of your residential building project with 3M's family of acrylic flashing tapes.

