



Double Coated Tape

93005LE

Technical Data

April 2015

Product Description 3M™ Double Coated Tape 93005LE is a double sided polyester tape featuring 3M™ High Strength Acrylic Adhesive 300LSE. Performance features include good resistance to consumer chemicals and excellent anti-lifting properties. The acrylic adhesive has a long history of successfully bonding a wide variety of similar and dissimilar materials such as metals, most plastics, glass, papers, and painted surfaces.

Product Construction A Double Coated Polyester Tape featuring 3M™ High Strength Acrylic Adhesive 300LSE and two Polycoated Kraft Release Liners.

Layer	Type	Thickness	
Release Liner 1	Polycoated Kraft	107 μ	4.2 mils
Adhesive - Faceside	300LSE Acrylic	19 μ	0.75 mils
Polyester Film	Transparent	12 μ	0.50 mils
Adhesive - Backside	300LSE Acrylic	19 μ	0.75 mils
Release Liner 2	Polycoated Kraft	157 μ	6.2 mils
Total Thickness: (including liners)		314 μ	12.4 mils
Total Thickness (without liners)		50 μ	1.97 mils

Notes: All tolerances +/- 10%

Typical Performance **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

Property	Substrate	Dwell/Rate	Value	Units	Value	Units
Faceside Adhesive Peel Adhesion @ 180° ASTM D3330	Stainless Steel Stainless Steel	20 min @ RT	0.618	N/mm	56.5	oz/in
		72 hrs @ RT	0.790	N/mm	72.2	oz/in
Backside Adhesive Peel Adhesion @ 180° ASTM D3330	Stainless Steel Stainless Steel	20 min @ RT	0.770	N/mm	70.4	oz/in
		72 hrs @ RT	0.824	N/mm	75.3	oz/in
		ABS Polypropylene HDPE	72 hrs @ RT 72 hrs @ RT 72 hrs @ RT	0.619 0.774 0.376	N/mm N/mm N/mm	56.6 70.7 34.4
Dynamic Shear ASTM D1002	Stainless Steel	10mm/min	1.084	N/mm ²	157.2	psi
Tensile Strength ASTM D897	Stainless Steel	10mm/min	1.099	N/mm ²	159.4	psi
Impact Shear Strength ASTM D950	25x25mm Puck	Pendulum Impact	1.545	J		

Notes: Adhesion is by ASTM D3330 method with exceptions as noted
 Stainless Steel substrate unless otherwise noted
 Adhesive backer is 2 mil Polyester Film

3M™ Double Coated Tape

93005LE

Technical Information

The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information..

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Waranty, Limited Remedy and Disclaimer

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M

Industrial Adhesives and Tapes Division

Converter Markets

3M Center, Building 225-3S-06

St. Paul, MN 55144-1000

800-362-3550

www.3M.com/converter

3M is a trademark of 3M Company.

©3M 2018 E70-0713-4677-2
(1/18)