

Energize your wrap options.

Print wrap film options for every preference,
style and application.



▲
**3M™ Print Wrap Film
IJ175Cv3**

For fast installation on:

1. Vehicle wraps
2. Trailers and box trucks

- ▶ Low initial tack: the easiest snap-up
- ▶ Featuring 3M™ Comply™ v3 Air Release for bubble-free graphics
- ▶ Moderate removal*
- ▶ Excellent slideability

* See Product Bulletin for details.



▲
**3M™ Print Wrap Film
IJ180mC-10**

For fast installation on:

1. Vehicle wraps
2. Trailers and box trucks

- ▶ Medium/low initial tack: a balance between easy snap-up and initial tack
- ▶ Featuring 3M™ Comply™ Air Release with micro technology for the smoothest appearance
- ▶ Excellent removal
- ▶ Excellent slideability



▲
**3M™ Controltac™ Graphic
Film with Comply™ v3
Adhesive IJ180Cv3**

For fast installation on:

1. Trailers and box trucks
2. Vehicle wraps

- ▶ Medium/high tack: requires less squeegee pressure speeding up installation and minimizing fatigue
- ▶ Featuring 3M™ Comply™ v3 Air Release for bubble-free graphics
- ▶ Excellent removal
- ▶ Good slideability
- ▶ Great film feel for easier management and alignment of panels

You have your own preference and style. We get that. And not all wrap jobs are the same. So, here's a suite of options to max your installation speed while delivering the best looking results.

These print wrap films are your reliable workhorse films for any job, any time. If your project needs more options, see our chart on the back to match your needs to the right wrap film.

See more at 3M.com/IJ180

3M™ Print Wrap Films

More options to fit the way you work.

3M™ Print Wrap Films	What Makes It Awesome	Film Type	Conformability and Lifting Resistance	Initial Tack	Slideability	Air Release Technology	Removability	Applications	
								Primary	Secondary
IJ180mC-10	A wrap film with medium/low initial tack, higher slideability, and the smoothest appearance.	Cast vinyl film	Stretches up to 130% and will not lift	Med/Low	High	Comply™ Adhesive with micro technology	Excellent	Vehicle and boat wraps	Trailers/box trucks, smooth walls
NEW IJ175Cv3	A wrap film with low initial tack, higher slideability, and bubble-free graphics.	Cast vinyl film	Stretches up to 130% and will not lift	Low	High	Comply™ v3 Adhesive	Moderate*	Vehicles and boat wraps	Trailers/box trucks
3M™ Controltac™ Graphic Film with Comply™ v3 Adhesive IJ180Cv3	The industry go-to film is optimal for trailer and box truck graphics using Comply™ v3 Adhesive.	Cast vinyl film	Stretches up to 130% and will not lift	Med/High	Medium	Comply™ v3 Adhesive	Excellent	Trailers/box trucks	Vehicle and boat wraps, smooth walls
3M™ Scotchlite™ Print Wrap Film 780mC-10R**	A reflective wrap film with big impact 24/7.	Cast vinyl film	Stretches up to 130% and will not lift	Med/Low	High	Comply™ Adhesive with micro technology	Excellent	Vehicle and boat wraps	Rough and smooth walls, trailers/box trucks
3M™ Envision™ Print Wrap Film SV480mC and LX480mC	These wrap films stretch 150% with no primer and no lifting. Even use on rough walls. Install in extreme temps with ease. Fine-tuned using Comply™ Adhesive with micro technology.	High performance non-PVC	Stretches up to 150% and will not lift	Med/Low	High	Comply™ Adhesive with micro technology	Excellent	Vehicle and boat wraps	Rough and smooth walls, trailers/box trucks
IJ180mC-114	Printable clear wrap film.	Cast vinyl film	Stretches up to 130% and will not lift	Med/Low	High	Comply™ Adhesive with micro technology	Excellent	Vehicle and boat wraps	Windows, trailers/box trucks, smooth walls
IJ180mC-120	Printable metallic wrap film for an edgier look.	Cast vinyl film	Stretches up to 130% and will not lift	Med/Low	High	Comply™ Adhesive with micro technology	Excellent	Vehicle and boat wraps	Trailers/box trucks, smooth walls
3M™ Controltac™ Graphic Film with Comply™ Adhesive IJ180C	The original go-to film is optimal for trailer and box truck graphics using Comply™ Adhesive.	Cast vinyl film	Stretches up to 130% and will not lift	Medium	Medium	Comply™ Adhesive	Excellent	Trailers/box trucks	Vehicle and boat wraps
IJ180mC-10UR	Ultra-removable adhesive removes cleanly without heat or chemicals.	Cast vinyl film	Stretches up to 130% and will not lift	Med/Low	High	Comply™ Adhesive with micro technology	Excellent	Promotional fleet, vehicles and signs	Trailers/box trucks, smooth walls
IJ180mC-10LSE	Wrap film for low surface energy plastics, such as motocross bikes and ATVs.	Cast vinyl film	Stretches up to 130% and will not lift	Medium	Medium	Comply™ Adhesive with micro technology	Difficult	Low Surface Energy Plastic Wraps (Motocross, ATV, etc)	Powder coated paints and other hard-to-stick surfaces
IJ180mC-10SLS	Wrap film for stainless steel applications.	Cast vinyl film	Stretches up to 130% and will not lift	Medium	Medium	Comply™ Adhesive with micro technology	Difficult	Stainless steel substrates	NA

*See Product Bulletin for details.

**This film is not yet intended for die-cut or plotter-cut applications.

For more information and to request a sample, visit 3M.com/Graphics
 To speak with 3M directly, call 1-800-328-3908.
 For warranty information, visit 3M.com/GraphicsWarranties.



Protect your wraps with 3M overlaminates, engineered and tested to help provide the performance and beauty you create with 3M™ Print Wrap Films.

- ▶ 3M™ Scotchcal™ Gloss, Luster, Matte or Ultra-Matte Overlaminates (8518, 8519, 8520, 8915)
- ▶ 3M™ Scotchcal™ Gloss Overlaminates 8528
- ▶ 3M™ Envision™ Gloss Wrap Overlaminates 8548G or Luster 8549L
- ▶ 3M™ Wrap Overlaminates Series 8900



Commercial Solutions

3M Center, Building 220-12E-04
 St. Paul, MN 55144 USA

Phone 1-800-328-3908
 Web 3M.com/Graphics