







3M™ PELTOR™ Level Dependent Earplug, LEP-200 EU

Small, Smart and Effective.

The 3M[™] PELTOR[™] Level Depdendent Earplug helps protect your hearing, and can help improve situational awareness and communications in challenging environments. Integrated with state-of-the-art level-dependent technology, the LEP-200 EU helps provide hearing protection

in noise and situational awareness in quiet environments. Ear pieces also include a small antenna to allow audio signals to be received wirelessly from a neckloop accessory (accessory sold separately).





3M[™] PELTOR[™] SportTac[™] Hearing Protection

A trusted companion.

The 3M™ PELTOR™ SportTac™ Hearing Protector is one of our most popular product, worn by thousands of hunters and shooters around the world. The unique digital sound circuit eliminates the sharp sound clip that is typical for many level dependent hearing protectors on the market. The electronics in

the 3M™ PELTOR™ SportTac™ Hearing Protector react instantaneously, and help protect your hearing from loud impulse noises. The system is designed and constructed to react so gently that you rarely hear the clip as the protection is activated.







3M™ PELTOR™ WS™ SportTac™ Hearing Protection

Instant communication.

The 3M™ PELTOR™ WS™ SportTac™ Hearing Protection is a level dependent hearing protector with built-in Bluetooth® technology, which allows for a complete wireless connection with your cell phone or other communication device with

Bluetooth® Technology. With the level dependent function, you can adjust the volume of surrounding sounds. And when time comes to take the shot it will help to protect against harmful noise levels.



Possibility for dual connections, wireless and wired.



Bluetooth® technology enables instant and discreet communication. With the well placed PTT/answer button on the left cup you can communicate over the communication radio or take/reject your calls from your cell phone.

3M™ PELTOR™ ProTac Shooter & Hunter Hearing Protector

Protection made easy.

The ProTac series offers a simple and user friendly range of products equipped with a digital level dependent function, specifically tuned for hunters and shooters. Large buttons for easy navigation and selection. A 3,5

mm input jack allows you to connect a hunting radio to the headset. Attenuation ratings range from SNR 26 dB for ProTac Shooter Hearing Protector, to SNR 32 dB for ProTac Hunter Hearing Protector.







3M™ PELTOR™ Tactical XP Hearing Protector

Extra Performance.

The 3M™ PELTOR™ Tactical™ XP helps to protect you from harmful noise and impulse sounds, while alowing and even amplifying ambient sounds such as conversation, barking of dogs and warning signals. The built-in functions of the Tactical

XP make it different from other active hearing protectors as the user can control and vary the volume function for the current situation. When neccessary ambient sounds can be amplified more than with any other 3M PLETOR hearing protector.





Comparison Chart of 3M™ PELTOR™ Hearing Protectors







	3M [™] PELTOR [™] SportTac [™]	3M [™] PELTOR [™] ProTac Hunter	3M [™] PELTOR [™] ProTac Shooter		
Max Amplification	HIGH	MEDIUM	MEDIUM		
Volume Steps	65	5	5		
Headband / cover	Foldable / Rubber	Non foldable / Plastic	Non foldable / Plastic		
Extra shells inc.	Yes	No	No		
App. with Gel Rings	Yes	No	No		
Operating time	~500h	~100h	~100h		
Charging time	N/A	N/A	N/A		
SNR	26 dB	26 dB	32 dB		
External Input	J22	3,5mm	3,5mm		
Bluetooth® Technology	No	No	No		
Adjustable balance	No	No	No		
Adjustable Equalizer	No	No	No		
Adjustable Release time	No	No	No		
Colour(s)	Red, Black, Green, Yellow,Pink	Green	Green		












3M [™] PELTOR [™] Tactical XP	3M™ PELTOR™ 3M™ PELTOR™ WS™ SportTac™ WS™ SportTac™ Lite		3M™ PELTOR™ LEP-200 EU
HIGH	MEDIUM	MEDIUM	MEDIUM
65	16	16	3
Foldable / Leather	Foldable / Leather	Foldable / Rubber	N/A
No	Yes, Orange	No	N/A
No	No	No	N/A
~1000h	~11h (bluetooth active)	~11h (bluetooth active)	~16h
N/A	8h	8h	90 min
31 dB	26 dB	26 dB	32/36/38 dB
J22	3,5mm	3,5mm	Wireless Listen only
No	Bluetooth 2.1	Bluetooth 2.1	No
Yes	Yes	Yes	No
Yes	Yes	Yes	No
Yes	No	No	No
Black	Green, Orange	Green	Yellow





3M™ PELTOR™ Bull's Eye™ Hearing Protector

3M™ PELTOR™ Bull's Eye I

The 3M™ PELTOR™ Bull's Eye™ I Hearing Protector was designed in collaboration with world-class sport shooters to develop a hearing protector that meets the need of different wearers. For example, a bevelled edge on the bottom of the shell helps prevent the unit from coming into contact with the barrel when sighting. The hearing protector has the necessary attenuation for most shooting application without being bulky so as not to interfere with the shooting process.

Wearer comfort is one of the critical determining factors when selecting appropriate hearing protector. The chosen hearing protector needs to be comfortable and offer adequate protection to help ensure the device is worn at all times during exposure to potentially hazardous noise. With its wide cushions filled with foam and fluid the 3M™ PELTOR™ Bull's Eye I Hearing Protector helps provide low pressure around the ears without compromising hearing protection. The foldable headband helps ensure that it takes up minimum space when not in use.

The 3M™ PELTOR™ Bull's Eye™ I Hearing Protector comes in red, green and black.



3M™ PELTOR™ Bull's Eye II Hearing Protector

A hearing protector specially designed for high noise exposure. Comfortable to wear even over long periods of time. Features a convenient low profile foldable headband. Available in red, green and black.





Weight: 230 g.



3M™ PELTOR™ Bull's Eye III Hearing Protector

A hearing protector with extremely high attenuation for very loud noise. The wide, soft, padded headband provide comfort even during prolonged period of use. Available in green.









Weight: 285 g.

3M™ PELTOR™ KID Hearing Protector

A range of hearing protectors are specially designed for little ones. Children have extremely sensitive hearing, and they also have more difficulty in protecting themselves from harmful noise. The 3M™ PELTOR™ KID Hearing Protector range comes in neon pink and neon green.







Weight: 180 g.











Hygiene Kit

Ear muffs, and in particular cushions, may deteriorate with use and should be examined at frequent intervals for cracking and leakage.



To replace ear cushions, slide your finger under the edge of the ear cushion and pull straight out.



Insert a new ear cushion by pressing until it snaps into place.

3M™ PELTOR™ Level Dependent Earplug, LEP-200 EU



Article Number	Description	3M ID
LEP-200 EU	3M™ PELTOR™, Level Dependent Ear Plug Kit, LEP-200 EU	70071677028

Accessories & Spare Parts

Article Number	Description	3M ID
LEP-CORD	3M™ PELTOR™, LEP-CORD, Replacement Cord	70071673795
LEP-200E	3M [™] PELTOR [™] , LEP-100E, Replacement Ear piece, Neon	70071677044
LEP-100C	3M™ PELTOR™, LEP-100C, Replacement Case, Neon	70071675139
370-TEPL-25	3M™ Ultrafit™ Ear tips, Large, Coyote Brown, 25 pairs	70071673746
370-TEPM-25	3M™ Ultrafit™ Ear tips,Medium, Desert Tan, 25 pairs	70071673738
370-TEPS-25	3M™ Ultrafit™ Ear tips, Small, OD Green, 25 pairs	70071673720
PELTIP5-01	3M [™] Torque [™] Ear tip, 50 pairs	7000108492
CCC-GRM-25	3M™ CCC-GRM-25, Triple C, 25 pairs	70071675212
TEP-WINDSCREEN	3M™ LEP/TEP Foam WINDSCREEN, 15 pairs	70071675907
TEP-LOOP-200	3M [™] PELTOR [™] Neckloop, 3,5mm Stereo plug	70071677036
TEP-LOOP-201	3M [™] PELTOR [™] Neckloop, 3,5mm Mono plug	70071730694

Ultrafit [™] Eartips							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	34,5	31,5	36,2	33,4	34,8	34,9	38,8
Standard deviation (dB)	6,0	5,4	5,6	4,3	3,8	5,0	4,0
Assumed Protection Value (dB)	28,5	26,1	30,6	29,1	31,0	29,9	34,8

SNR=32dB H=31dB M=30dB L=29dB

3M [™] CCC-GRM-25 Eartips							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	35,5	32,5	37,1	38,0	37,6	39,5	45,5
Standard deviation (dB)	4,5	4,0	4,4	3,7	2,9	4,6	4,2
Assumed Protection Value (dB)	30,9	28,4	32,7	34,3	34,6	34,9	41,3

SNR=36 dB H=35 dB M=34 dB L=32 dB

PELTIP5-01/Torque [™] Eartips							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	37,8	36,0	40,5	41,2	41,3	39,6	46,1
Standard deviation (dB)	4,3	5,5	4,2	4,7	3,2	4,3	3,6
Assumed Protection Value (dB)	33,5	30,5	36,3	36,5	38,0	35,3	42,5

SNR=38dB H=37dB M=36dB L=34dB

3M™ PELTOR™ SportTac™ Hearing Protection



Article Number	Description	3M ID
MT16H210F-478-RE	3M™ PELTOR™ SportTac™, pink and green cups inc.	7100090955
MT16H210F- 478GN945	3M™ PELTOR™ SportTac™, yellow and green cups inc.	7000108339
MT16H210F-478-RD	3M™ PELTOR™ SportTac™, black and red cups inc.	7000039607
MT16H210F-478-GN	3M™ PELTOR™ SportTac™, orange and green cups inc.	7100004420

Accessories & Spare Parts

Article Number	Description	3M ID
HY21	Hygine Kit	7000039686
HY80S-EU	Gel Rings	7100121710
210100-478-GN	One pair of replacement shells, green	7000107841
210100-478-OR	One pair of replacement shells, orange	7000107842
210100-478-SV	One pair of replacement shells, black	7000107843
210100-478-RD	One pair of replacement shells, red	7000107844
210100-478-VI	One pair of replacement shells, white	7000107845
FL6H	Cable 3.5-mm mono jack	7000107805
FL6M	Cable 2.5-mm mono jack	7000107806
FL6N	Cable 3.5-mm stereo jack	7100064600

MT16H210F-478-GN							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	21.1	17.9	27.0	26.8	30.5	38.3	36.4
Standard deviation (dB)	4.3	3.1	3.8	3.0	3.0	3.7	5.4
Assumed Protection Value (dB)	7.8	14.8	23.2	23.8	27.5	34.6	31.0

SNR=26dB H=29dB M=23dB L=16dB

MT16H210F-478* with HY80S-EU GEL RING							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	13.8	17.6	24.7	29.8	29.9	39.3	40.7
Standard deviation (dB)	2.9	2.7	3.0	2.2	3.7	4.2	3.8
Assumed Protection Value (dB)	10.9	14.9	21.7	27.6	26.1	35.2	36.9

SNR = 27 dB H=29 dB M=24 dB L=17 dB

3M[™] PELTOR[™] ProTac Shooter Hearing Protection 3M[™] PELTOR[™] ProTac Hunter Hearing Protection



Article Number	3M ID			
MT13H222A	3M™ PELTOR™ ProTac Hunter	7100088458		
MT13H223A	3M™ PELTOR™ ProTac Shooter	7100088425		

Accessories & Spare Parts

Article Number	3M ID	
HY220	Hygine Kit	7100101874
FL6CE	Cable 3.5-mm stereo jack	7000108359

MT13H222A							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	13.3	17.4	22.3	28.0	30.8	37.6	37.0
Standard deviation (dB)	3.2	1.8	2.3	3.2	3.4	2.8	4.8
Assumed Protection Value (dB)	10.1	15.6	20.0	24.8	27.4	34.8	32.2

M113H223A							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	17.0	24.0	29.5	36.9	37.3	39.3	35.4
Standard deviation (dB)	3.2	2.0	2.6	3.3	4.9	3.2	3.9
Assumed Protection Value (dB)	13.8	22.0	26.9	33.6	32.4	36.1	31.5

SNR=26dB H=29dB M=23dB L=17dB SNR=32dB H=34 M=29db L=22dB

3M[™] PELTOR[™] WS[™] SportTac[™] Hearing Protection



Article Number	Description	3M ID
MT16H21FWS5E-584GN	3M™ PELTOR™ WS™ SportTac™	7000108343
MT16H21FWS5L-584GN	3M™ PELTOR™ WS™ SportTac™Lite	7000108532

Accessories & Spare Parts

Article Number	Description	3M ID
HY68 SV	Hygine Kit	7000108023
FL6CE	Cable 3.5-mm stereo jack	7000108359
FL6H	J22 to 3,5 mm cord	7000107805
FL6M	J22 to 2,5 mm cord	7000107806
TAMT06	J22 to two pin with PTT/mic	7000108141
TAMT06V	J22 to two pin with PTT/mic/ang.	7000043765
MT53N-11-A44	Boom microphone	4000013209
210200-584-OR	Orange shells	7000108383

MT16H21FWS5E-584GN, MT16H21FWS5L-584GN								
Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	11.1	18.2	27.0	23.8	33.4	37.7	38.9	
Standard deviation (dB)	2.6	2.3	2.2	2.1	3.6	2.2	3.3	
Assumed Protection Value (dB)	8.5	15.8	24.8	21.7	29.8	35.5	35.5	

SNR=26dB H=29dB M=23dB L=19dB

3M™ PELTOR™ Tactical XP Hearing Protection



Article Number	Description	3M ID
MT1H7F2	3M™ PELTOR™ Tactical XP	7000039608

Accessories & Spare Parts

Article Number	Description	3M ID
HY79	Hygine Kit	7100063118
FL6H	Cable 3.5-mm mono jack	7000107805
FL6M	Cable 2.5-mm mono jack	7000107806
FL6N	Cable 3.5-mm stereo jack	7100064600

MT1H7F2*							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	13.8	21.5	30.9	36.6	35.9	35.5	39.0
Standard deviation (dB)	1.8	0.9	1.3	1.5	5.5	3.1	2.3
Assumed Protection Value (dB)	12.0	20.6	29.6	35.1	30.4	34.4	36.7

SNR=31dB H=32dB M=25dB L=20dB

3M™ PELTOR™ Bull's Eye™ Hearing Protection



Hygiene kits

For hearing protectors	Article number
3M™ PELTOR™ Bull's Eye I hearing protector	HY51
3M™ PELTOR™ Bull's Eye II hearing protector	HY52
3M [™] PELTOR [™] Bull's Eye III hearing protector	HY54
3M™ PELTOR™ Kid hearing protector	HY51

3M™ PELTOR™ Bull's Eye™ I

H515FB***							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	10.9	17.2	26.6	28.3	33.5	37.8	37.9
Standard deviation (dB)	3.2	2.5	2.2	2.7	2.6	2.0	2.6
Assumed Protection Value (dB)	7.7	14.8	24.4	25.6	30.9	35.7	35.3

SNR=27dB H=32dB M=24dB L=15dB

3M™ PELTOR™ Bull's Eye™ III

H540A							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean A ttenuation (dB)	17.4	24.7	34.7	41.4	39.3	47.5	42.6
Standard deviation (dB)	2.1	2.6	2.0	2.1	1.5	4.5	2.5
Assumed Protection Value (dB)	15.3	22.1	32.7	39.3	37.8	43.0	40.0

SNR=35 dB H=40 dB M=32 dB L=23 dB

3M™ PELTOR™ Bull's Eye™ II

H520F							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	14.5	20.3	32.6	39.1	35.1	34.7	39.8
Standard deviation (dB)	1.8	2.6	2.4	2.5	2.3	2.7	2.5
Assumed Protection Value (dB)	12.7	17.7	30.2	36.6	32.8	32.0	37.3

SNR=31 dB H=34 dB M=26 dB L=20 dB

3M™ PELTOR™ KID

H510AK KID							
Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenua- tion (dB)	11.6	18.7	27.5	32.9	33.6	36.1	35.8
Standard devia- tion (dB)	4.3	3.6	2.5	2.7	3.4	3.0	3.8
Assumed Pro- tection Value (dB)	7.3	15.1	25.0	30.1	30.2	33.2	32.0

SNR=27 dB H=32 dB M=25 dB L=15 dB







3M Personal Safety Division 3M Svenska AB Box 2341 SE-331 02 Värnamo, Sweden

www.3M.com/PELTOR

Please recycle. Printed in Sweden. © 3M 2018. All rights reserved. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by 3M Company is under license. 3M, SportTac and WS are trademarks of 3M Company, used under license in Canada. PELTOR is a trademark of 3M Svenska AB, used under license in Canada.