


3M™ Versaflo™ TR-800 Series

Parts and Accessories



Part Number	General Description	Description	Replace when maximum life is reached or when/if:	SAP ID#
System Kits				
TR-800-ECK	3M™ Versaflo™ Easy Clean PAPR Kit	Kit includes: S-433L Hood with Integrated Head Suspension, BT-30 Length Adjusting Breathing Tube, BT-922 Breathing Tube Cover, TR-6710N HE Filter, TR-6700FC Filter Cover, TR-6600 Prefilter (x2), TR-802N Intrinsically Safe PAPR Unit, TR-627 Easy-Clean Belt, TR-830 Intrinsically Safe Battery, TR-838 Battery Attachment Tool, TR-642N Single Station Battery Charger Kit, TR-971 Airflow Indicator, TR-653 Cleaning and Storage Kit	replace component(s) in kit based on guidance in table below, and/or reference component user instructions	7100150926

TR-800-HIK	3M™ Versaflo™ Heavy Industry PAPR Kit	Kit includes: M-307 Respiratory hard hat assembly with premium visor and faceseal, BT-30 Length Adjusting Breathing Tube, BT-926 High Temperature Breathing Tube Cover, TR-6530N OV/AG/HE Cartridge, TR-6500FC Filter Cover, TR-6600 Prefilter (x2), TR-662 Spark Arrestor (x2), TR-802N Intrinsically Safe PAPR Unit, TR-626 High Durability Belt, TR-830 Intrinsically Safe Battery, TR-838 Battery Attachment Tool, TR-642N Single Station Battery Charger Kit, TR-971 Airflow Indicator, TR-653 Cleaning and Storage Kit	replace component(s) in kit based on guidance in table below, and/or reference component user instructions	7100150927
TR-800-PSK	3M™ Versaflo™ Paint Spray Kit	Kit includes: M-206 Respiratory Faceshield Assembly, BT-20L Breathing Tube, BT-922 Breathing Tube Cover, TR-6510N OV/HE Cartridge, TR-6500FC Filter Cover, TR-6600 Prefilter (x2), TR-662 Spark Arrestor (x2), TR-802N Intrinsically Safe PAPR Unit, TR-627 Easy Clean Belt, TR-830 Intrinsically Safe Battery, TR-838 Battery Attachment Tool, TR-642N Single Station Battery Charger Kit, TR-971 Airflow Indicator, TR-653 Cleaning and Storage Kit	replace component(s) in kit based on guidance in table below, and/or reference component user instructions	7100150922
TR-800-IHK	Industrial Hard Hat with Hood Kit PAPR Kit	Kit includes: S-707 Premium Replacement Painter's Hood with Inner Shroud, S-960 Premium S-Series Hood and Hard Hat Adapter Assembly, H-701SFR-UV Hard Hat, White, Ratchet Suspension, with Uvicator, BT-30 Length Adjusting Breathing Tube, BT-922 Breathing Tube Cover, TR-6510N OV/HE Cartridge, TR-6500FC Filter Cover, TR-6600 Prefilter (x2), TR-802N Intrinsically Safe PAPR Unit, TR-626 Heavy Duty Belt, TR-830 Intrinsically Safe Battery, TR-838 Battery Attachment Tool, TR-642N Single Station Battery Charger Kit, TR-971 Airflow Indicator, TR-681 PAPR cover, TR-653 Cleaning and Storage Kit, BT-957 Breathing Tube Storage Plug	replace component(s) in kit based on guidance in table below, and/or reference component user instructions	7100307702
Series Assemblies				
TR-813N	Heavy-Duty PAPR Assembly	Assembly includes: BT-30 Length Adjusting Breathing Tube, TR-802N Intrinsically Safe PAPR Unit, TR-626 High Durability Belt, TR-830 Intrinsically Safe Battery, TR-838 Battery Attachment Tool, TR-971 Airflow Indicator	replace component(s) in assembly based on guidance in table below, and/or reference component user instructions	7100150924
TR-814N	Easy-Clean PAPR Assembly	Assembly includes: BT-30 Length Adjusting Breathing Tube, TR-802N Intrinsically Safe PAPR Unit, TR-627 Easy Clean Belt, TR-830 Intrinsically Safe Battery, TR-838 Battery Attachment Tool, TR-971 Airflow Indicator	replace component(s) in assembly based on guidance in table below, and/or reference component user instructions	7100150923
Component Parts and Accessories				
TR-802N	Blower	Intrinsically Safe Replacement Blower for Versaflo™ TR-800	damaged or unable to resolve alarms	7100150821
TR-830	Battery	Intrinsically Safe Battery for Versaflo™ TR-800 PAPR	damaged or no longer achieving desired run-time	7100150925
TR-838	Battery Attachment Tool	Battery attachment tool for Versaflo™ TR-800 PAPR and TR-800 battery (includes 2 replacement screws)	damaged	7100150921
TR-851	Filter Latch	Replacement filter latch assembly for TR-802N blower	damaged	7100150941

TR-642N	Single Charger	Single Station Battery Charger Kit TR-642N	damaged, broken, or unable to charge battery	7100342637
TR-642-3	3-StationCharger add-on	3-Station Battery Charger Pack Only TR-642-3, (cable not included)	damaged, broken, or unable to charge battery	7100342637
TR-626	HD Belt	High Durability belt for Versaflo™ TR-600/TR-800 PAPR	damaged	7100035831
TR-626X	HD Belt Extender	Belt extender for TR-626 High Durability Belt	damaged	7100035832
TR-627	EC Belt	Easy Clean belt for Versaflo™ TR-600/TR-800 PAPR	damaged	7100035833
TR-627X	EC Belt Extender	Belt extender for TR-627 Easy Clean Belt	damaged	7100035834
TR-927	Backpack	Easy Clean Backpack, TR-927	damaged	7100300071
BPK-HD	Backpack	Heavy Duty Backpack BPK-HD	damaged	7100282441
TR-655	Backpack Adapter	Backpack Adaptor to connect TR-602N to BPK-01 or alternate belts TR-325, TR-326 or TR-327 (not shown)	damaged	7100035843
BT-20S	Breathing Tube	Breathing Tube, BT-20S, Small/Medium	damaged, broken, holes, cuts or tears	7100296066
BT-20L	Breathing Tube	Breathing Tube BT-20L, Medium/Large	damaged, broken, holes, cuts or tears	7100296133
BT-30	Breathing Tube	Length Adjusting Breathing Tube, BT-30	damaged, broken, holes, cuts or tears	7100009685
BT-40	Breathing Tube	Heavy-Duty Breathing Tube, BT-40	damaged, broken, holes, cuts or tears	7100105845
BT-63	Breathing Tube	Length Adjusting Tight-Fitting Breathing Tube BT-63	damaged, broken, holes, cuts or tears	7100170023
BT-64	Breathing Tube	Heavy-Duty Tight-Fitting Breathing Tube, BT-64	damaged, broken, holes, cuts or tears	7100167214
BT-922	Breathing tube cover	Breathing Tube Cover BT-922	damaged	7100077588
BT-926	Breathing tube cover	Breathing Tube Cover BT-926 (high temperature)	damaged	7000042907
TR-6600	Prefilter	Prefilter for Versaflo™ TR-600/TR-800 PAPR	damaged or clogged	7100021255
TR-662	Spark Arrester/Prefilter	Spark arrester/Prefilter for Versaflo™ TR-600/TR-800 PAPR	damaged or unable to clean	7100035845
TR-6710N-5	HE Filter	Filter for Versaflo™ TR-600/TR-800 PAPR (5-pack)	damaged or when change is indicated by the PAPR low flow alarm	7100028247
TR-6710N-40	HE Filter	HE Filter for Versaflo™ TR-600/TR-800 PAPR (40-pack)	damaged or when change is indicated by the PAPR low flow alarm	7100019288

TR-6320N	Filter/Cartridge	Acid Gas/HE Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	7100021254
TR-6350N	Filter/Cartridge	Formaldehyde/HE Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	7100027551
TR-6360N	Filter/Cartridge	Ammonia/Methylamine/HE Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	7100027408
TR-6510N	Filter/Cartridge	Organic Vapor/HE Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	7100021253
TR-6530N	Filter/Cartridge	Organic Vapor/Acid Gas/HE Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	7100021007
TR-6590N	Filter/Cartridge	Multi-Gas/HE Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	7100035844
TR-6700FC	Filter Cover	Filter CoverFilter cover for 6700 series filters for Versaflo™ TR-600/TR-800 PAPR	damaged or broken. No longer securely attaches to filter/cartridge	7100021251
TR-6300FC	Filter Cover	Filter cover for 6300 series filter/cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged or broken. No longer securely attaches to filter/cartridge	7100021336

TR-6500FC	Filter Cover	Filter cover for 6500 series filter/cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged or broken. No longer securely attaches to filter/cartridge	7100021252
TR-971	Flow Indicator	Flow indicator for Versaflo™ TR-600/TR-800 PAPR (for loose fitting headgear)	damaged	7100035846
TR-973	Flow Indicator	Flow indicator for Versaflo™ TR-600/TR-800 PAPR (for tight fitting facepieces)	damaged	7100167216
TR-653	Cleaning/Storage Kit	Cleaning and Storage Kit for TR-602N/TR-802N PAPR, and TR-630/TR-632/TR-830 batteries	damaged, broken, gaskets changed after 30 washings	7100035841
TR-654	Cleaning/Storage Kit Gasket	Replacement gaskets for TR-653 cleaning and storage kit	damaged, broken, gaskets changed after 30 washings	7100134768
BT-953	Cleaning/Storage Kit	Cleaning and Storage Kit BT-953 for BT-60 Breathing Tubes	damaged	7100176699
BT-957	Breathing tube Storage Plug	Breathing Tube Storage Plugs BT-957	damaged	7100176778
TR-681	PAPR Cover	PAPR Cover TR-681	damaged	7100260718

WARNING



These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Improper use may result in injury, sickness or death.** For correct use, see supervisor and *User Instructions*, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.

For More Information

In U.S.

Technical Assistance: 1-800-243-4630, Hours of Operation: 8:00 a.m. – 4:30 p.m. CST

Customer Care Center: 1-800-328-1667, Hours of Operation: 7:00 a.m. – 5:00 p.m. CST



Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

3M PSD products are
occupational use only.

3M Canada

P.O. Box 5757
London, Ontario
N6A 4T1

In United States of America

Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/workersafety

In Canada:

Technical Service: 1-800-267-4414
Customer Service: 1-800-6880
3M.ca/Safety

3M is a trademark of 3M. Used under
license in Canada. © 2026, 3M.
All rights reserved. Please recycle.