



PROTECTA

Fall Protection

3M™ Protecta® Sliding Beam Anchor

Work confidently with the 3M™ Protecta® Sliding Beam Anchor. This durable solution provides a high-strength anchorage point that follows you while you work. Once you secure it to the beam using the integrated adjustment buttons, simply connect your Self-Retracting Lifeline (SRL)* or lanyard to the rotating D-ring and you're ready to work.

*Use 3M™ DBI-SALA® Nano-Lok™ edge Twin-Leg Quick-Connect Self-Retracting Lifeline – Cable when tying off at feet.

Model shown
2104703



Applications:

- ▶ Bridge work
- ▶ Buildings
- ▶ Warehouses
- ▶ Arenas
- ▶ Parking ramps

3M™ Protecta® Sliding Beam Anchor



Model shown
2104703

- ▶ Versatile size ranges to fit a variety of beams
- ▶ Replaceable wear pads
- ▶ Centered, D-ring anchor point
- ▶ Integrated dual ratcheting system
- ▶ 5,000 lb. (22 kN) strength and up to 420 lb. (189 kg) capacity

Versatile size range

Fits beam flanges 3-1/2 in. to 14 in. (9 cm-35.5 cm) wide and up to 1-1/4 in. (3.2 cm) thick.

Built to last

Rugged, corrosion resistant construction enhances longevity.

Fully adjustable

Integrated dual ratcheting adjustment system slides to fit snugly against the beam.

Guarded locking mechanism

Located on the bottom to reduce chance of accidental disengagement.

Replaceable wear pads


Eliminate metal-to-metal contact and extend the usability of the product.

Compliant

Meets ANSI Z359.18 and OSHA 1910.140, 1926.502 Anchorage Connector standards.

Ordering Information

Part #	Beam Width	Flange Thickness	Description
2104703	3.5-14 in.	1.25 in.	Sliding Beam Anchor (ANSI)



For foot level tie-off, use 3M™ DBI-SALA® Nano-Lok™ edge Twin-Leg Quick-Connect Self-Retracting Lifeline – Cable, 8 ft. (2.4 m)

Model shown
3500225

Find these products and more at [3M.com/FallProtection](https://www.3m.com/FallProtection).



3M Fall Protection
3833 SALA Way
Red Wing, MN 55066 USA

Phone 800.328.6146
Email 3mfallprotection@mmm.com
Web [3M.com/FallProtection](https://www.3m.com/FallProtection)

3M, DBI-SALA, Protecta and Nano-Lok are trademarks of 3M Company and its affiliates.
© 3M 2018. All rights reserved.