



3M | **PELTOR™**

3M™ PELTOR™ WS™ ALERT™ XPI Headset



Don't stop communicating. And don't stop working.

Don't miss a call. Don't stop your
work to run to a quiet location to talk.
Keep working on the job at hand.

#3MScienceOfSafety

3M Science. Applied to life.™

Protect your ears, protect your profits. You can't afford to stand around talking – or worse yet, leave the work area to find a quiet area to make or receive phone calls. Think how much more productive you could be with the new 3M™ PELTOR™ WS™ ALERT™ XPI Hearing Protection Headset.



Stay connected. Stay working. Stay engaged.

Turn your hearing protection into a communications centre. Connect one or two devices via Bluetooth® Multipoint technology and speak in normal volume even in noisy environments with the noise-cancelling microphone.

Big buttons and voice-guided menus

Large, push buttons are glove-friendly. Get immediate voice feedback after every setting adjustment. No need to remove the headset for any adjustments.

Hearing protection with situational awareness

Ambient microphones help you hear oncoming vehicles, alerts, and other warning signals while providing hearing protection to AS/NZS 1270 SLC80 Class 5 hearing protection when you need it. The Push-to-listen feature instantly decreases your Bluetooth® or FM radio volume while increasing your ambient volume while increasing your ambient listening ability.

Durable, practical electronics

The dual-shell design helps protect the electronics from moisture, impact, etc. Auto-OFF after 4 hours of non-use. "Low battery" voice message. Uses two AA alkaline batteries or the optional rechargeable batteries.

Talk normally, even in noisy work environments

Stop shouting. With this noise-cancelling microphone you can talk in normal volume.

Bluetooth® MultiPoint connectivity & flexibility

Always stay connected! Simultaneous, seamless connection to two Bluetooth® devices, for example, two mobile phones, a mobile and a DECT phone, or a mobile and a two-way radio.

Built in FM-Radio with vocalized channel selection

Two models: headset or helmet attachment

Both feature long-lasting, stainless steel wire bands for consistent, comfortable wear.



Bluetooth® MultiPoint technology for connection to one or two external devices for hands-free talk and streaming



Level-dependent function for ambient listening to help improve situational awareness



Built-in FM-Radio



Noise cancelling boom microphone for clear speech transmission in noisy environments



“I bring two mobile phones to work: one’s for work, the other is personal. With this headset, I can connect to both. So I can talk to my customers and family – or listen to Spotify™ and audio-books – while running a chainsaw the entire time! This is a must-have for any contractor like me.”

Martin Lindahl, Independent Excavator.

Technical data specifications

Headset models

Product Number	Description	3M Order Code
MRX21AWS6-AZ	3M™ PELTOR™ WS™ ALERT™ XPI Headset, yellow, headband	UU009152602
MRX21P3EWS6-AZ	3M™ PELTOR™ WS™ ALERT™ XPI Headset, yellow, helmet attachment	UU009153311

Accessories

Product Number	Description	3M Order Code
HY82	3M™ PELTOR™ HY82 Hygiene kit: 2 foam liners, 2 snap-in cushions	UU008567388
HYM1000	3M™ PELTOR™ HYM1000 Microphone protection, 5 metres	XH001651328
HY100A	3M™ PELTOR™ HY100A Clean hygiene pads, single-use “gasket” protectors for ear cushions, self-adhesive, 100 ea/case	XH001651351

Attenuation

Headband model: Meets the performance standard of AS/NZS 1270 30dB (Class 5)

Helmet attachment model: Meets the performance standard of AS/NZS 1270 29dB (Class 5)



Personal Safety Division

3M Australia Pty Ltd

Bldg A, 1 Rivett Road,
North Ryde, NSW 2113
TechAssist Helpline: 1800 024 464
Customer Services: 1300 363 565
Email: techassist@mmm.com
3M.com/au/ppesafety

3M New Zealand Limited

94 Apollo Drive, Rosedale,
Auckland 0632
TechAssist Helpline: 0800 364 357
Customer Services: 0800 252 627
3M.com/nz/ppesafety