



Fall Protection

The versatility you need when working at-height.

Stay on top of projects with 3M™ DBI-SALA® Roof Anchors.

Whether your roof is flat or sloped, wood, metal or concrete, there's a 3M™ DBI-SALA® Roof Anchor to help you get the job done efficiently and securely. They're easy to install and rugged enough to handle tough environments.



Pair these roof anchors with the 3M™ DBI-SALA® Smart Lock Self-Retracting Lifeline (SRL) for comfort and productivity with reduced unintentional lockups.*



Swiveling Self-Retracting Lifeline Bracket

Provides freedom of movement around the anchor.

Compact and Lightweight Design

Features fast and easy attachment for added productivity.

Durable Construction

Stands up to tough work environments.

*Compared to our previous generation SRLs.

2190073

3M™ DBI-SALA® Standing Seam Roof Anchor

- ▶ **Installs to Flat or Sloped Standing Seam Roofs**
System clamps to standing seams without special tools, providing an anchorage point for an SRL, including the 3M™ DBI-SALA® Smart Lock Self-Retracting Lifeline.
- ▶ **Built-in Non-Penetrating Clamp Design**
Four seam clamps allow for quick attachment without damaging the roof.
- ▶ **Slide on the Tube**
Legs fit a variety of seam spacings up to 36 in.
- ▶ **Portable and Reusable**
Anchor can be removed and simply reinstalled in a new location for added jobsite flexibility.



2190071

3M™ DBI-SALA® Swiveling Roof Anchor

- ▶ **Installs to Sloped or Flat Wood and Metal Decking Roofs**
Anchor can be installed to a variety of roofing materials to provide an anchorage point for an SRL or a tie-off point.
- ▶ **Fast and Easy Installation**
Fastener kit included—includes 16 ea. ¼-14 × 2-1/2 in. self-tapping screws for steel installation and 8 ea. ¼ × 2-1/2 in. lag screws for wood.
- ▶ **Secondary D-Ring Anchor Point**
Secondary D-ring allows user to tie-off to anchor with lanyard or install a 3M™ DBI-SALA® Horizontal Lifeline between two anchors.
- ▶ **Portable and Reusable**
Anchor can be removed and simply reinstalled in a new location for added jobsite flexibility.



2190074

3M™ DBI-SALA® Construction Roof Anchor

- ▶ **Installs to Rebar Ring During Pre-Cast Concrete Work**
Installs in seconds utilizing built-in ratcheting securement system.
- ▶ **Built-in Ratcheting Securement System**
Allows user to secure anchor in place quickly without special tools.
- ▶ **Dual-Use Design**
Can also be used as end anchors for a 2-person temporary 3M™ DBI-SALA® Horizontal Lifeline System.
- ▶ **For Use with 3M™ DBI-SALA® Smart Lock SRL (Sold Separately)**
Smart Lock Horizontal (Leading Edge) SRL knows the difference between regular movement and a fall—reducing unintentional lockups.*
- ▶ **Portable and Reusable**
Anchor can be removed and simply reinstalled in a new location for added jobsite flexibility.



*Compared to our previous generation SRLs.

Raise your roofing versatility at
3M.com/FallProtection.



3M Fall Protection
3833 SALA Way
Red Wing, MN 55066 USA

Phone 800.328.6146
Email 3mfallprotection@mmm.com
Web 3M.com/FallProtection

3M and DBI-SALA are trademarks of
3M Company and its affiliates.
© 3M 2018. All rights reserved.