

**3M** Science.  
Applied to Life.™

# 3M™ Perfect-It™ Fast Cut Plus Extreme.

Getting the perfect finish  
is even quicker.



# New Generation of Compound : 3M Fast Cut Plus Extreme

Fast Cut Plus Extreme is 3M's new and improved performance Green Top abrasive compound. Scratch removal time is typically reduced by 25%.

Customers will save time and benefit from improved quality along with improved confidence in the scratch removal compounding step.

The higher cutting performance of this compound is delivered with excellent gloss results providing a compound suitable for a wide range of systems.

Customers report excellent results following the use of 3M™ Trizact™ discs 3000 or 6000. Customers also report excellent scratch removal following dry sanding with 260L P1200 and P1500 and Wet or Dry P1500 and 2000.


Customers appreciate the improved working time of this product and our customer trials clearly indicated the product has a reduced tendency to dry out in application.

New Fast Cut Plus Extreme is designed to be used with our range of green foam pads for maximum efficiency to the product, either with flat foam pad that work faster with quick movements or convoluted foam which heat less the paint.

- Remove Scratches faster
- Excellent results on all paints
- Minimal Sling
- High gloss obtained even faster

Use 3M™ Extra Fine Plus in conjunction with a yellow high gloss pad as a second step to maximize the gloss.


In order to achieve the ultimate flawless finish or for critical colors that exhibit holograms, use 3M™ Ultra Fina SE in conjunction with a blue high gloss foam pad.



# 3M™ Quick Connect™ Adapter Benefits



## Foam Pad Construction



Cost saving due to 3M Quick Connect System allow usage of foam on both side.

The 3M™ Perfect-it™ III Quick Connect™ System consists of a unique adapter and a wide range of double-sided foams in 150 mm and 216 mm diameter.

- ▶ Allows for easy and fast pad changes.
- ▶ Ensures a perfect centering of all 3M™ double sided foams to reduce vibration and deliver working comfort.
- ▶ Adapters available for pneumatic or electric polishers.
- ▶ For cost & time optimization, pads of 216 mm can be used for large area.



Format	Description	Packaging	Part Number
M14	Adapter 3M Quick Connect M14 mainly for Electrical Polisher	Bag of 1 adapter	33271
5/8	Adapter 3M Quick Connect 5/8 mainly for Pneumatic Polisher	Bag of 1 adapter	05759
diam. 150 mm	Green Flat Foam Pad Double Side 3M Quick Connect	Bag of 1 Pad	50878
diam. 150 mm	Green Convuluted Foam Pad Double Side 3M Quick Connect	Bag of 1 Pad	50962
diam. 216 mm	Green Convuluted Foam Pad Double Side 3M Quick Connect	Bag of 1 Pad	50874
diam. 150 mm	Yellow Convuluted Foam Pad Double Side 3M Quick Connect	Bag of 1 Pad	50879
diam. 216 mm	Yellow Convuluted Foam Pad Double Side 3M Quick Connect	Bag of 1 Pad	50875
diam. 150 mm	Blue Convuluted Foam Pad Double Side 3M Quick Connect	Bag of 1 Pad	50880
diam. 216 mm	Blue Convuluted Foam Pad Double Side 3M Quick Connect	Bag of 1 Pad	50708

# Poster small area

## Denibbing

## Smart Repair

### Manual Wet Sanding

62 × 115 mm  
Stikit



Kit 5 grits  
4 accessories  
3 dimensions  
**PN° 33888**

Block  
**PN° 33912**

Sheet  
1500  
**PN° 33894**

Sheet  
2000  
**PN° 33897**

Sheet  
2500  
**PN° 33900**

Sheet  
3000  
**PN° 33903**

Ø 32 mm  
Stikit



Block  
**PN° 50199**

Circle  
1500 or Circle  
**PN° 33892** **PN° D2002**

Circle  
2000 or Circle  
**PN° 33895** **D2000**

Circle  
2500  
**PN° 33898**

Circle  
3000  
**PN° 33901**

### Machine sanding

Ø 32 mm  
Stikit



Pneumatic Machine  
**PN° 28737**

Circle  
1500 or Circle  
**PN° 33892** **PN° D2002**

Circle  
2000 or Circle  
**PN° 33895** **PN° D2000**

Circle  
2500  
**PN° 33898**

Circle  
3000  
**PN° 33901**

Ø 75 mm  
Hookit



Pneumatic Machine  
Festool\* LEX 3 77 2,5

Disc 260L  
P1500  
**PN° 00907**

3M™ Trizact™  
3000  
**PN° 50415**  
Optional  
3M™ Trizact™ 6000  
**PN° 51131**

### With a rotary Polisher

Ø 75 mm Back Up Pad  
**PN° 07652**



### With a Dual Action Polisher

Compound



Ø 75 mm  
3M™ Hookit™  
Convoluted Foam  
**PN° 50499**



Fast Cut Plus  
Extreme  
1 kilo  
**PN° 51815**  
0,5 kilo  
**PN° 51816**



Ø 75 mm  
3M™ Hookit™  
Convoluted Foam  
**PN° 50499**

Polish



Ø 75 mm  
3M™ Hookit™  
Convoluted Foam  
**PN° 50536**



Extra Fine Plus  
**PN° 80349**



Ø 75 mm  
3M™ Hookit™  
Convoluted Foam  
**PN° 50536**

If dark colour, to remove Holograms

Hologram  
Removal



Ø 75 mm  
3M™ Hookit™  
Convoluted Foam  
**PN° 50457**



Ultra Fine SE  
**PN° 50383**

**Not needed  
as Dual Action  
movement  
remove  
Holograms**

\*Festool Automotive Systems is a premium German manufacturer of system solutions for body shops.

# Poster large area

## Manual Wet Sanding

P1500  
PN° 09545  
2000  
PN° 09546




## Machine sanding

Ø 150 mm  
Interface  
5 mm : PN° 51126  
10 mm : PN° 51127



## Scratch Refinement Machine Sanding



Ø 150 mm Wet  
3M™ Trizact™ 3000  
PN° 50414  
Optional 3M™ Trizact™ 6000  
PN° 51130

Ø 150 mm  
260L P1500  
7 holes : PN° 50238  
9 holes : PN° 62011  
15 holes : PN° 51154

## With a rotary Polisher



Ø 127 mm  
3M™ Hookit™ Electrical M14  
PN° 09552  
Pneumatic 5/8 PN° 09553

Ø 150/216 mm  
3M™ Quick Connect™  
Electrical M14  
PN° 33271  
Pneumatic 5/8 PN° 05759



## With a Dual Action Polisher

Hookit Back Up Pad  
is supplied  
with the machine

### Compound

Ø 150 mm  
3M™ Hookit™  
Flat Foam  
PN° 50487

Ø 150 mm  
3M™ Quick Connect™ Double Side  
Flat Foam - PN° 50878  
Ø 150 mm  
3M™ Quick Connect™ Double Side  
Convuluted Foam - PN° 50962  
Ø 216 mm  
3M™ Quick Connect™ Double Side  
Convuluted Foam - PN° 50874



Fast Cut Plus  
Extreme  
PN° 51815

Ø 150 mm  
3M™ Hookit™  
Flat Foam  
PN° 50487

### Polish

Ø 150 mm  
3M™ Hookit™  
Convuluted Foam  
PN° 50488

Ø 150 mm  
3M™ Quick Connect™ Double Side  
Convuluted Foam  
PN° 50879  
Ø 216 mm  
3M™ Quick Connect™ Double Side  
Convuluted Foam  
PN° 50875



Extra Fine Plus  
PN° 80349

Ø 150 mm  
3M™ Hookit™  
Convuluted Foam  
PN° 50488

If dark colour, to remove Holograms

### Hologram Removal

Ø 150 mm  
3M™ Hookit™  
Convuluted Foam  
PN° 50388  
Ø 203 mm  
3M™ Hookit™  
Convuluted Foam  
PN° 50389

Ø 150 mm  
3M™ Quick Connect™ Double Side  
Convuluted Foam  
PN° 50880  
Ø 216 mm  
3M™ Quick Connect™ Double Side  
Convuluted Foam  
PN° 50708



Ultra Fine SE  
PN° 50383

**Not needed  
as Dual Action  
movement  
remove  
Holograms**

Abrasive	Format	Description	Fixation	Packaging	Part Number
Abrasives for Small Areas	Ø 32 mm	3M Finesse-it Hand sanding pad	3M Stikit	1 red Pad	50199
	Ø 32 mm	268L 3M Finesse-it Abrasive Disc P1500	3M Stikit	Sleeve of 100 discs	D2002
	Ø 32 mm	268L 3M Finesse-it abrasive disc 9 microns	3M Stikit	Sleeve of 100 discs	00127
	Ø 32 mm	466LA 3M Trizact A5 Adhesive discs P3000	3M Stikit	Sleeve of 100 discs	50079
	Ø 32 mm	Paint Defect Removal Cylinder		1 black Pad	33909
	Ø 32 mm	Sheet of 6 abrasive Circle 1500	3M Stikit	Box of 10 sheets of 6 circles	33892
	Ø 32 mm	Sheet of 6 abrasive Circle 2000	3M Stikit	Box of 10 sheets of 6 circles	33895
	Ø 32 mm	Mini Orbital Sander Air pressure		1 machine	28737
	Ø 25 mm	3M Roloc + Back Up Pad	3M Roloc	1 Back Up Pad	09884
	Ø 32 mm	3M Finesse-it Roloc Sanding Pad blue	3M Stikit	1 blue Pad	02345
	Ø 32 mm	Sheet of 6 abrasive circle 2500	3M Stikit	Box of 10 sheets of 6 circles	33898
	Ø 32 mm	Sheet of 6 abrasive circle 3000	3M Stikit	Box of 10 sheets of 6 circles	33901
	62 × 115 mm	Paint Defect Removal Foam Pad	3M Stikit	1 black Pad	33911
	62 × 115 mm	Paint Defect Removal Rubber Pad	3M Stikit	1 black Pad	33912
	62 × 115 mm	Paint Defect Removal Card 1500	3M Stikit	Box of 15 cards	33894
	62 × 115 mm	Paint Defect Removal Card 2000	3M Stikit	Box of 15 cards	33897
	62 × 115 mm	Paint Defect Removal Card 2500	3M Stikit	Box of 15 cards	33900
	62 × 115 mm	Paint Defect Removal Card 3000	3M Stikit	Box of 15 cards	33903
	Ø 75 mm	Back Up Pad yellow	3M Hookit	Bag od 1 pad	02700
	Ø 75 mm	Soft interface	3M Hookit	Bag of 1 Pad	05771
	Ø 75 mm	260L Abrasive disc plain P1200	3M Hookit	Box of 50 discs	00908
	Ø 75 mm	260L Abrasive disc plain P1500	3M Hookit	Box of 50 discs	00907
	Ø 75 mm	443SA 3M Trizact Abrasive Disc P1000	3M Hookit	Bag of 15 discs	50413
Ø 75 mm	443SA 3M Trizact Abrasive Disc 3000	3M Hookit	Bag of 15 discs	50415	
Ø 75 mm	443SA 3M Trizact Abrasive Disc 6000	3M Hookit	Bag of 15 discs	51131	
Abrasives for Large Areas	70 × 117 mm	WetOrDry Rubber Squeegee		1 squeegee	05517
	70 × 135 mm	Rubber Sanding Block		1 block	05519
	70 × 140 mm	WetOrDry Sponge Pad		Box of 5 pads	05526
	138 × 230 mm	401Q Abrasive Micro Fine 1500		Sleeve of 50 sheets	09545
	138 × 230 mm	401Q Abrasive Micro Fine 2000		Sleeve of 50 sheets	09546
	Ø 150 mm	Standard Sanding Pad Multiholes 5/16 or M8	3M Hookit	Bag of 1 pad	51122/3
	Ø 150 mm	Soft interface Multiholes 5mm	3M Hookit	Bag of 1 interface	51126
	Ø 150 mm	Soft interface Multiholes 10mm	3M Hookit	Bag of 1 interface	51127
	Ø 150 mm	260L Abrasive disc 7 holes P1500	3M Hookit	Box of 50 discs	50238
	Ø 150 mm	260L Abrasive disc 9 holes P1500	3M Hookit	Box of 50 discs	62011
	Ø 150 mm	260L Abrasive disc 15 holes P1500	3M Hookit	Box of 50 discs	51154
	Ø 150 mm	443SA 3M Trizact Abrasive disc Plain P3000	3M Hookit	Box of 15 discs	50414
	Ø 150 mm	443SA 3M Trizact Abrasive disc Plain P6000	3M Hookit	Box of 15 discs	51130
Clean & Control	500 ml	Finish Control Spray		1 Aerosol	55535
	370 × 380 mm	Polishing White Wipe		Roll of 275 wipes	34568
Accessories for Rotary Polisher	Ø 75 mm	Polishing Back Up Pad	3M Hookit	Bag of 1 Pad	07652
	Ø 127 mm	Red Back Up Pad for Electrical Polisher M14	3M Hookit	Bag of 1 Pad	09552
	Ø 127 mm	Red Back Up Pad for Pneumatic Polisher 5/8	3M Hookit	Bag of 1 Pad	09553
		Adapter QC for Electrical Polisher M14	3M Quick Connect	Bag of 1 adapter	33271
		Adapter QC for Pneumatic Polisher 5/8	3M Quick Connect	Bag of 1 adapter	05759

Compounding	0,5 kg	Fast Cut Plus Extreme Green Cap		Bottle of 0,5 Kilo	51816
	1 kg	Fast Cut Plus Extreme Green Cap		Bottle of 1 Kilo	51815
	Ø 75 mm	Green Convoluted Foam Pad	3M Hookit	Bag of 4 Pads	50499
	Ø 150 mm	Green Flat Foam Pad	3M Hookit	Bag of 2 Pads	50487
	Ø 150 mm	Green Flat Foam Pad Double Side	3M Quick Connect	Bag of 1 Pad	50878
	Ø 150 mm	Green Convoluted Foam Pad Double Side	3M Quick Connect	Bag of 1 Pad	50962
	Ø 216 mm	Green Convoluted Foam Pad Double Side	3M Quick Connect	Bag of 1 Pad	50874
320 × 360 mm	Green High Performance Ultra Soft Cloth		Bag of 5 clothes	10068	
Polishing	1 kg	Extra Fine Plus Polish Yellow Cap		Bottle of 1 Kilo	80349
	Ø 75 mm	Yellow Convoluted Foam pad	3M Hookit	Bag of 4 Pads	50536
	Ø 150 mm	Yellow Convoluted Foam pad	3M Hookit	Bag of 2 Pads	50488
	Ø 150 mm	Yellow Convoluted Foam pad Double Side	3M Quick Connect	Bag of 1 Pad	50879
	Ø 216 mm	Yellow Convoluted Foam pad Double Side	3M Quick Connect	Bag of 1 Pad	50875
	320 × 360 mm	Yellow High Performance Ultra Soft Cloth		Carton of 20 clothes	50400
Hologram Removal on dark colors	1 kg	Ultrafina SE polish Blue Cap		Bottle of 1 Kilo	50383
	Ø 75 mm	Blue Convoluted Foam Pad	3M Hookit	Bag of 4 Pads	50457
	Ø 150 mm	Blue Convoluted Foam Pad	3M Hookit	Bag of 2 Pads	50388
	Ø 203 mm	Blue Convoluted Foam Pad	3M Hookit	Bag of 1 Pad	50389
	Ø 150 mm	Blue Convoluted Foam Pad Double Side	3M Quick Connect	Bag of 1 Pad	50880
		Blue Convoluted Foam Pad Double Side	3M Quick Connect	Bag of 1 Pad	50708
	320 × 360 mm	Blue High Performance Ultra Soft Cloth		Carton of 20 clothes	50486
Finish Protection	1 liter	Finishing Glaze for Exhibition Hall Red Cap		Bottle of 1 Liter	09377
	1 liter	Polish Rosa for second hand cars		Bottle of 1 Liter	80345
	Ø 171 mm	Black Convoluted Foam Pad	3M Hookit	Bag of 2 Pads	05729
	320 × 360 mm	Pink/Red High Performance Ultra Soft Cloth		Carton of 20 Clothes	50489



**Automotive Aftermarket,  
3M United Kingdom PLC,**  
Tel: 016 1237 6391  
Fax: 016 1237 5911  
aadenquiries.uk@mmm.com

**Automotive Aftermarket,  
3M Ireland,**  
Tel: (01) 280 3555  
Fax: (01) 280 3509

Please recycle. Printed in France.  
© 3M 2018. All rights reserved.  
EL 77 AB 640  
3M, 3M Science. Applied to Life., Extra Fine,  
Quick Connect, 3M Ultrafina, Trizact, Perfect-it,  
Finesse-it, Wetordry, Hookit, Stikit, Roloc & Quick  
Connect are trademarks of the 3M Company.

www.3mbodyshop.co.uk