

3M™ Polyurethane Protective Tape

8663/8663DL

Product Description

3M™ Polyurethane Protective Tape 8663/8663DL (dual liner) is made from an exceptionally tough abrasion resistant polyurethane elastomer that resists punctures, tearing, abrasion and erosion. It is formulated for resistance to ultraviolet light. 3M 8663 Tape provides a simple, easy method of protecting a surface from corrosion, abrasion and minor impact damage. 3M 8663 Tape and 3M 8663DL Tape are constructed with a long-aging, solvent-resistant, pressure-sensitive acrylic adhesive that is protected with an easy-release plastic liner.

3M 8663 Tape is a transparent tape available in three liner configurations:

- Single polypropylene liner on the adhesive side.
- Single skip-slit polypropylene liner on the adhesive side.
- Dual liners, one on each side of the tape.

Typical Physical Properties and Performance Characteristics

Note: 1) The following technical information and data should be considered representative or typical only and should not be used for specification purposes. 2) ASTM = American Society for Testing and Materials. 3) Metric values are listed in parenthesis.

I. Dimensions:

Approximate Applied Thickness:*	0.016 inch (0.40 mm) Film 0.002 inch (0.06 mm) Adhesive Total thickness 0.018 inch (0.46 mm)
Standard Roll Length:	36 yd (32.9 m)
Available Widths:	1/2-inch min. 48-inch max. (1.25 cm to 122 cm)
Approximate Weight:*	1.04 lb./yd ² (516.7 g/m ²)

*Excludes the polyethylene liner that is removed from the tape prior to application.

II. Typical Physical Properties and Performance Characteristics

Property	Test Method	Units	Typical Value
Tensile Strength @ Break	ASTM D882	Lb./in. (N/100mm)	117 (2049)
Elongation % @ Break	ASTM D882	%	500
Peel Adhesion @ 70°F (21°C) to: Bare Aluminum Acrylic Enamel Paint ABS Plastic	ASTM D-1000	Oz./in. (N/100mm)	84 (92) 56 (61) 65 (71)
Maximum Service Temperature		°F (°C)	180°F (82°C)

General Information

- 3M™ Polyurethane Protective Tape 8663 and 8663DL have excellent environmental resistance properties and have been used to isolate and protect substrates from environmental damage and corrosive elements.
- 3M 8663 Tape can be used to provide a UV resistant surface coating for indoor and outdoor applications.
- 3M 8663 DL Tape comes with a protective polyethylene adhesive liner and a polyester top liner that stiffens the product and can serve as an application aid for some installations. Both liners are removed after final installation. Primary use of this product is for aircraft floor covering/ corrosion protection per Boeing Service Letters 737-SL-53-034 and 757-SL-53-018.
- 3M 8663 Tape may be painted per 3M Technical Bulletin Polyurethane Protective Tape, Painting Instructions.

Shipping and Storage

No special/hazardous labeling or packaging required or regulations for air, ground or water shipment for this product. Keep film in a clean area, away from excessive moisture and out of direct sunlight. Store rolls in the shipping carton. Return partially used rolls to the shipping carton. Shelf Life: Two (2) years from the date of manufacture or as expressly certified by 3M.

These products were manufacture under a 3M Quality Management System registered to the AS9100 standard

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. **Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. **Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive & Aerospace Solutions Division
3M Center
St. Paul, MN 55144-1000
Phone 1-800-328-1684
Web www.3M.com/aerospace

8663/8663DL
Issue date: 6/2018

3M is a trademark of 3M Company
© 3M 2018. All rights reserved.