

# 3M™ Versaflo™ TR-300+ Powered Air Turbo

## Technical Data Sheet



### Description

The 3M™ Versaflo™ TR-300+ Powered Air Turbo is a belt-mounted air purifying device. When combined with one of the 3M approved headtops, it forms a power-assisted system for respiratory protection against particles (and nuisance odour where applicable). The TR-300+ Powered Air Turbo can be used with the following 3M headtops: S-Series, M-Series, and 3M 6000 DIN full facemasks, Speedglas™ FX Air, Speedglas 9100.

### Features

- Two user selectable flow rates
- Controlled airflow delivers steady flow as battery discharges or filters loads with particulates
- Display shows battery charge status, selected airflow and particulate filter loading status during use
- Audible and LED alarm signals low battery charge or low airflow
- Three filter options available:
  - PAPR-P3 Particulate only
  - PAPR-P3 Particulate plus nuisance level organic vapours\*
  - PAPR-P3 Particulate only nuisance acid gas \* and offers protection against hydrogen fluoride up to 10 x Occupational Exposure Limit
- Lithium ion battery with LED to indicate charge status
- Three belt options (standard, easy-clean and leather) for a range of applications
- Suitable for use in decontamination shower (IP 53)

\* Nuisance level refers to concentrations below the Occupational Exposure Limit

### Approvals

The TR-300+ Powered Air Turbo, when used as part of an approved 3M Respiratory system has been shown to meet the Basic Safety Requirements under Article 10 and 11B of the European Directive 89/686/EEC and is CE marked. The product was examined at the design stage by: BSI, Kitemark Court, Davy Avenue, Knowlhill, Milton Keynes MK5 8PP, UK (Notified Body number 0086). The product complies with European EMC Directive 2014/30/EU.



### Standards

The TR-300+ Powered Air Turbo, in combination with 3M approved headtops, has been tested and is compliant with AS/NZS 1716:2012. The TR-300+ Powered Air Turbo also meets the following requirements:

- Dust protection and protection against spraying water to EN60529 IP 53.

## Applications

The TR-300+ Powered Air Turbo, when used as part of an approved system with appropriate filters, provides protection against:

- Particles e.g. fine dusts, mists and metal fume.
- Nuisance odour levels (below the Occupational Exposure Limit) of organic vapours
- Nuisance odour levels (below the Occupational Exposure Limit) of acid gases and up to 10 x Occupational Exposure Limit of hydrogen fluoride.

The TR-300+, when used with an appropriate 3M headtop and filters, may be used in various applications including:

- Agriculture
- Chemical Industry
- Construction and Building Renovation
- Demolition
- Food and Beverage
- Medical and Healthcare
- Metalworking
- Pharmaceutical Manufacturing
- Pulp and Paper Processing
- Smelting and Foundries
- Surface Preparation
- Woodworking

## Materials

Component	Material
Turbo body	Acrylonitrile butadiene styrene (ABS)
Filter cover	Acrylonitrile butadiene styrene (ABS)
Battery casing	Acrylonitrile butadiene styrene (ABS)
Belts	- Standard polyester web belt
	- Polyurethane coated polyester easy-clean belt
	- Leather belt

## Limitations

The TR-300+ Powered Air Turbo should not be used in the following conditions:

- In atmospheres containing less than 19,5 % oxygen
- Confined spaces (lack of ventilation)
- When the risk is considered to be Immediately Dangerous to Life or Health (IDLH).
- Where the contaminant concentration is above the Occupational Exposure Limit defined for the headtop used (see relevant User Instructions for the headtop)

## Product Range

TR-300+ Powered Air Turbo is available to buy as:

- TR-302E+ Turbo Unit (includes filter cover, airflow indicator and spark arrestors)
- TR-315A+ Starter Kit (includes TR-302E+ turbo unit, particulate filter, standard belt, high capacity battery pack, battery charger kit, self-adjusting breathing tube, airflow indicator and spark arrestors)

## Technical specifications

**Required Minimum Protection Factor (RMPF):** Depends on 3M headtop used.

### Protection Factors

- TR-300+ with 6000DIN full facemask 100+
- All other headtops 50

### Outlet Flow Characteristics

- Stated manufacturer's Minimum Design Flow (MMDF) 170l/min
- Standard Flow 185 l/min +/- 10 l/min
- High Flow 205 l/min +/- 10 l/min

### Battery Duration (with new filter and new battery)

- High-capacity battery Standard Flow 9-12 hours  
High Flow 9-10 hours

### Battery Charge Time

- High capacity battery pack = less than 3.5 hours

### Storage conditions

- -30°C to +50°C < 90 %RH

### Operating temperature

- -10°C to +55°C

### Shelf Life\*

- 5 years from date of manufacture

### Weight (including high capacity battery, belt and filter)

- Approx. 1135 g

\*The shelf life as defined above remains an indicative and maximum data, subject to many external and non controllable factors. It may never be interpreted as a warranty.

## Spare parts and accessories

Part No.	Description
TR-325	Standard belt
TR-326	Leather belt
TR-327	Easy-clean belt
022-25-10P4	Braces
BPK-01	Backpack
TR-332	High capacity battery pack
TR-340	Battery charger cradle
TR-341A	Battery charger kit
TR-344A	4-Station battery charger kit
TR-362	Spark Arrestor
TR-371+	Filter cover
TR-971	Airflow indicator
TR-3600	Pre-filter
TR-3712E	P3 Particulate filter
TR-3802E	P3 + Nuisance Level* Organic Vapour
TR-3822E	P3 + Nuisance Level* Acid Gas Filter (Hydrogen Fluoride up to 10 x Occupational Exposure Limit)
BT-20L	Lightweight breathing tube Large
BT-30	Self-adjusting breathing tube
BT-40	Heavy duty breathing tube
BT-922	Disposable breathing tube cover
BT-926	Flame resistant breathing tube cover

\* Nuisance level refers to concentrations below the occupational exposure limit (OEL).

## IMPORTANT NOTICE

The use of the 3M product described within this document assumes that the user has previous experience of this type of product and that it will be used by a competent professional. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application. All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user. Compliance to the information and specification relative to the 3M product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. The 3M group (which cannot verify or control those elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control.

Warranty conditions for 3M products are determined with the sales contract documents and with the mandatory and applicable clause, excluding any other warranty or compensation. Respiratory Protection is only effective if it is correctly selected, fitted and worn throughout the time when the wearer is exposed to respiratory contaminants.

For more information on 3M products and services please contact 3M.



**3M Australia Pty Ltd**  
**Personal Safety Division**  
Bldg A, 1 Rivett Road  
North Ryde NSW 2113  
TechAssist Helpline: 1800 024 464  
Customer Service: 1300 363 565  
Email: techassist@mmm.com  
Web: www.3M.com/au/ppesafety

**3M New Zealand Ltd**  
**Personal Safety Division**  
94 Apollo Drive, Rosedale  
Auckland 0632  
TechAssist Helpline: 0800 364 357  
Customer Service: 0800 252 627  
Email: techassist@mmm.com  
Web: www.3M.com/nz/ppesafety

3M and Versaflo are trademarks of 3M Company.  
Please recycle. Printed in Australia.  
© 3M 2018. All rights reserved.  
AV011467428