3M™ Aerospace Sealants Product Comparison

Class B Polysulfide Sealant Tack Free and Cure Times*

Specification	3M Product	Specific Gravity	Tack Free	Cure	Tack Free	Cure	Tack Free	Cure	Tack Free	Cure	Tack Free	Cure	Tack Free	Cure
			Class B-1/4		Class B-1/2		Class B-1		Class B-2		Class B-4		Class B-6	
AMS-S-8802 Fuel Tank and Fuselage	AC-350	1.4			2 - 3 hours	2 - 3 hours			7 - 8 hours	7 - 8 hours	32 - 36 hours	32 - 36 hours		
AMS3276 High Temp Fuel Tank and Fuselage	AC-350	1.4	1 - 2 hours	1 - 2 hours	2 - 3 hours	2 - 3 hours			7 - 8 hours	7 - 8 hours	32 - 36 hours	32 - 36 hours	48 hours	48 hours
AMS3281 Light Weight Fuel Tank and Fuselage	AC-370 (Type 1)	1.3			6 - 7 hours	6 - 7 hours			7 - 8 hours	8 - 10 hours				
	AC-380 (Type 2)	1.1			5 hours	5 hours			8 - 10 hours	8 - 10 hours				
AMS3265 Non-Chromated Corrosion Inhibitive	AC-730	1.5			4 hours	6 hours			16 hours	24 hours				
MIL-PRF-81733 Non-Chromated Corrosion Inhibitive	AC-735	1.1			5 hours	5 hours			10 - 12 hours	10 - 12 hours				
3M Standard Window & Canopy	AC-251 Black	1.6			4 hours	4 hours	5 hours	7 hours	8 hours	9 hours				

^{*}Measured at Standard Conditions (77°F / 25°C and 50% Relative humidity). These products were manufactured under a 3M Quality Management System registered to the AS9100 standard.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Automotive & Aerospace Solutions Division

3M Center

St. Paul, MN 55144-1000 Phone: 1-800-328-1684

Web: www.3M.com/aerospace

Issue date: 3/2019

3M is a trademark of 3M Company © 3M 2019. All rights reserved.