

**3M** Science.  
Applied to Life.™



# Airflow selection – delivering a world of comfort to you.

The new 3M™ Versaflo™ Powered Air Respirator System TR-600 provides protection against particles, gases or vapours, or against a combination of these depending on the type of filter used. The turbo has selectable multiple airflows through a simple, intuitive, easy to use two-button operation and the particulate filter and battery status indicators provide constant updates during use. The modern, low profile design keeps weight close to the back resulting in greater comfort.

#3MScienceOfSafety

# Introducing the New 3M™ Versaflor™ Powered Air Turbo TR-600

## Comfortable airflow

- Three user selectable flow rates to maximise comfort
- Controlled airflow delivers steady flow as battery discharges or filter loads with particulates

## Ease of use

- TR-600 display shows battery charge status and particulate filter loading status during use
- Charge status is also indicated by a useful LED display on the battery
- No user calibration of turbo required
- Electronic audible, visual and vibratory alarm in case of low battery and/or low air flow

## Multiple applications

- Easy clean belt – submersible belt with smooth surfaces allows easy, thorough cleaning
- High durability belt option for hot work or rugged environments provides greater durability and spark/flame resistance
- Suitable for shower decontamination and temporary submersion to aid cleaning

## Safety

- AS/NZS1716:2012 compliant Powered Air Purifying Respirator

Filters	Filter Covers
TR-6710ANZ P3	TR-6700FC
TR-6820ANZ P3 + Nuisance Odour* Organic Vapour Filter and Acid Gas (Hydrogen Fluoride up to 10 x Threshold Limit Value)	TR-6800FC
TR-6310ANZ A1P3	TR-6300FC
TR-6580ANZ, A1B1E1HgP3	TR-6500FC

\* "Nuisance Odour" refers to concentrations below the Exposure Standard

Belts
TR-626 High Durability Belt
TR-627 Easy-Clean Belt

Batteries
TR-630 Standard Battery
TR-632 High Capacity Battery



## Typical industries and applications

- Pharmaceutical manufacturing
- Painting
- Chemical processing
- Agriculture
- Demolition
- Pulp and paper processing
- Medical & healthcare
- Foundries

### 3M™ Versaflor™ Powered Air Turbo TR-602E

This turbo can be easily adapted to your type of environment – see options below. Includes Air Flow Indicator TR-971 and Spark Arrestor TR-662 (x2).

### 3M™ Versaflor™ Powered Air Turbo Starter Kit TR-619A

This Versaflor™ Starter Kit includes the TR-602E Turbo, PAPR-P3 filter, filter cover, prefilters (x10), spark arrestor (x2), easy clean belt, high capacity battery, single station battery charger kit, BT-30 length adjusting breathing tube and airflow indicator.

Spares and Accessories	
TR-6600 Pre-filter	TR-971 Air Flow Indicator
TR-662 Spark Arrestor	
TR-653 Cleaning & Storage Kit	TR-655 Backpack Adapter
TR-651 Filter Latch Assembly	TR-329 Braces
Chargers	
TR-641E Single Station Battery Charger Kit	
TR-644E 4-Station Battery Charger Kit	



Note: 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence or fraudulent misrepresentation.



## Personal Safety Division

### 3M Australia Pty Ltd

Bldg A, 1 Rivett Road,  
North Ryde, NSW 2113  
TechAssist Helpline: 1800 024 464  
Customer Services: 1300 363 565  
Email: techassist@mmm.com  
3M.com/au/ppesafety

### 3M New Zealand Limited

94 Apollo Drive, Rosedale,  
Auckland 0632  
TechAssist Helpline: 0800 364 357  
Customer Services: 0800 252 627  
3M.com/nz/ppesafety