



Accuspray nozzles available to match PPS series 2.0 cups

You can now upgrade your 3M™ Accuspray™ gun with new Accuspray™ Atomizing Heads to use with 3M™ PPS™ Series 2.0 cups.

They're designed to take advantage of PPS™ Series 2.0's improved material flow, and to deliver more-consistent atomization.

Also new, 3M™ High Power Spray Gun Cleaner, PN 26689. It blasts excess paint off spray gun surfaces - inside and out. It can be used for both solvent-base and waterborne paints and coatings.



PN	Description	Items/Box	Number/Case
26612	Blue, 1.2mm	4	6
26613	Green, 1.3mm	4	6
26614	Orange, 1.4mm	4	6
26618	Clear Transparent, 1.8mm	4	6
26620	Red Opaque, 2.0mm	4	6
26689	High Power Spray Gun Cleaner	-	6