

# 3M™ Strapping and Filament Tapes and Dispensers

Scotch® Clean Removal Strapping Tape 8899HP Blue

Scotch® Filament Tape 898 Clear

Tartan™ Filament Tape 8934 Clear

Scotch® Filament Tape Hand Dispenser H12


Tartan™ Hand-Held Filament Tape Dispenser HB901

## 3M Solutions

3M's line of filament-reinforced tapes and strapping tapes are high strength, reliable and affordable solutions that gives your product and package integrity. For closing boxes, stabilizing pallets, bundling and reinforcing; securing appliance components during transport and easy-open tear strips, our high strength tapes provide important benefits for manufacturers of piping, metal products, furniture, appliances, automotive parts, sporting goods, as well as food and beverage processors.

## Applications

- L-Clip closure
- Metal and pipe bundling
- High strength reinforcing
- Heavy duty strapping
- Secure racks, doors, shelves and other components in appliances
- Utility strapping
- Mounting protective packaging materials



## Where do I sell it?

- Small business
- Construction
- Consumer goods
- Food and beverage
- General industrial packaging
- Transportation
- Appliance
- Metalworking

## Who do I sell it to?

- Manufacturing entrepreneurs
- Small shop production supervisors
- Prototyping designers
- Shipping functions
- Custom woodworkers
- Packaging engineer

## Key Benefits:

### 8899HP

- Scotch® Clean Removal Strapping Tape 8899HP removes cleanly and resists stains on common surfaces, such as painted metal, plastic and glass.
- 3M pressure-sensitive rubber adhesive is specifically formulated to adhere evenly and bond firmly to long lasting hold.
- Designed to hold shelving, racks, doors, panels, cords and other parts in place.

### 898 and 8934

- High strength film backing resists breaking, abrasion, moisture and scuffs yet flexible enough for manual or semi-automatic dispensing.
- Industrial-strength, filament-reinforced tape resists nicks, abrasion and moisture.
- Secure L-clip closure for full overlap (FOL), tuck-type boxes or other non-standard boxes.
- Synthetic rubber adhesive bonds easily to most fiberboard, plastics and metal surfaces.
- Glass yarn filaments add strength for box closing, bundling and more.
- Able to withstand rough shipping and handling conditions.

**For distributors only.**

## How to open a call:

Can I share with you the strengths of 3M's different strapping and filament reinforced tapes?

## Recommended response:

Our Scotch® Filament Tape 898 is ideal for securing boxes, bundling pipe or reinforcing large bulk containers, i.e., Scotch® Clean Removal Strapping Tape 8899HP is a high performance tape formulated for use in many industries, including appliance and metalworking. Our Tartan™ Filament Tape 8934 is an economical general purpose clear fiberglass-reinforced tape with a synthetic rubber resin adhesive, ideal for light duty strapping, bundling and reinforcing.

## Ordering Information

UPC No.	3M ID	Description	Color	Size	Case quantity
0-00-21200-86520-6	70-0061-2003-7	Tartan™ Filament Tape 8934 is our general purpose clear fiberglass-reinforced tape with a synthetic rubber resin adhesive, ideal for light duty strapping, bundling and reinforcing. Our synthetic rubber resin adhesive provides good adhesion to most fiberboard surfaces, and a variety of plastics and metal surfaces.	Clear	24mm x 55m	36/Case Bulk
0-00-76308-98893-7	70-0075-0301-7	Our Scotch® Clean Removal Strapping Tape 8899HP is a high performance tape formulated for use in many industries, including appliance and metalworking. The tensilized polypropylene film backing features a pressure-sensitive natural rubber adhesive that provides high initial adhesion holding power and clean removal on a variety of metal, vinyl, plastic, fiberboard, powder coat and glass surfaces.	Blue	24mm x 55m	36/Case Bulk
0-00-51131-06898-8	70-0062-4858-0	With a polypropylene backing that resists abrasion, moisture, scuffing and breaks, try Scotch® Filament Tape 898. This filament reinforced tape is ideal for securing boxes, bundling pipe or reinforcing large bulk containers, Scotch® Filament Tape 898 is a high-strength, reliable and affordable solution for product and package integrity.	Clear	24mm x 55m	36/Case Bulk
0-00-21200-06953-6	78-8023-2207-9	Scotch® Filament Tape Hand Dispenser H12 features an interior core hand brake allowing the operator to add tension for tighter box reinforcement and secure sealing, as well as tighter tension for bundling applications. This dispenser is specifically designed for narrow width rolls of Scotch® Filament Tapes up to 1 inch wide.	Putty		6/Case Bulk
0-00-51131-06994-7	78-8114-0972-7	Our Tartan™ Hand-Held Filament Tape Dispenser HB901 gives you comfort and control in a lightweight hand-held dispenser specially designed to dispense Scotch® Filament Tapes. We manufacture this smooth operating dispenser using high-impact plastic.	Black		12/Case Bulk



**Industrial Adhesives and Tapes Division**  
3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
Phone 800-362-3550  
Web 3M.com/IATD

## For distributors only.

3M and Tartan are trademarks of 3M. Scotch is a registered trademark of 3M.  
© 3M 2017. All rights reserved. Please recycle. Printed in USA.