

Product Description

3M™ Automotive Window Films Color Stable Series are non-metallized polyester films with an acrylic pressure-sensitive adhesive and an abrasion-resistant coating.

Applications

3M™ Automotive Window Film Color Stable Series are intended for interior application on flat to complex curved glazing.

Typical Properties

Technical information provided consists of typical product data and should not be used for specification purposes. Unless otherwise noted, all tests are performed at room temperature.

- Colour stable, never fading technology
- Non-metallized, ensuring no interference with mobile phones, GPS and radio signals

Product construction	
Material base	Non-metallized, dyed polyester
Adhesive	Pressure sensitive acrylic
Protective liner	Heat shrinkable, siliconized PET

Typical Performance Properties according to EN 410								
Film Type	Visible Light			Total Solar Energy Rejected	Infrared Rejection*	Infrared Energy Rejection**	UV Block	Glare Reduction
	Reflected (interior)	Reflected (exterior)	Transmission					
	%	%	%	%	%	%	%	%
Clear Glass (6 mm)	8	9	89	19	NA	NA	40	NA
CS IR 5	5	5	8	64	40	49	99	91
CS IR 15	5	5	17	60	40	49	99	81
CS IR 25	5	5	27	57	40	49	99	70
CS IR 30	5	5	34	52	32	45	99	62
CS IR 35	6	6	38	51	32	45	99	57
CS IR 50	6	6	56	44	32	45	99	37
CS IR 70	7	7	70	39	32	45	99	21
Auto 75 glass (6 mm)	7	7	73	43	NA	NA	79	NA
CS IR 5	5	5	6	72	40	64	99	92
CS IR 15	5	5	14	69	40	64	99	80
CS IR 25	5	5	22	67	40	63	99	70
CS IR 30	5	5	28	64	32	62	99	62
CS IR 35	5	5	32	63	32	62	99	56
CS IR 50	6	6	46	58	32	62	99	37
CS IR 70	7	6	58	54	32	62	99	20

* IRR - IR Rejected over 900 – 1,000 nm wavelength range. Film with liner measurement.

** IRER – The percent of solar infrared energy rejection over the wavelength range from 780 – 2,500 nm. IRER takes into account the transmitted and absorbed IR energy that will be reradiated into a car. The film is applied to glass.

The values above are the results of illustrative lab test measurements and shall not be considered a commitment from 3M.

Shelf Life and Storage (prior to application)

The shelf life as defined below remains an indicative and maximum data, subject to many external and non-controllable factors. It may never be interpreted as a warranty.

Shelf life is 5 years from the manufacturing date. The material should be stored in its original packaging, laying in a horizontal orientation, away from direct sunlight. Heavy objects should not be placed on top of it to avoid damaging the product. Recommended storage conditions are +21°C and 40 – 50% relative humidity. Avoid extreme temperature ranges in storage.

Application

These are indicative values for 3M™ Automotive Window Film products.

Recommended surface	Flat to complex curved glazing
Application method	Wet application. Use a heat gun to shrink and fit the film to simple and complex curves when necessary.
Application temperature	From +4°C to +45°C
Service temperature	From -40°C to +70°C (not for extended periods of time at the extremes)
Edge sealing	Not necessary
Drying Time	Final adhesion is reached after approximately 15 - 20 days at +18°C and dry conditions. Please refer to local instructions for details.

3M Automotive Window Film is to be professionally applied by skilled, well-trained, and 3M authorized installers. Windows can be considered operational after 24 hours.

Maintenance and Cleaning

Use a cleaning agent designed for high-quality glass surfaces. The cleaning agent must be wet and non-abrasive with a pH value between 6 and 8 (neither strongly acidic nor strongly alkaline).

Health and Safety

When handling any chemical products, read the manufacturer's container labels and the Safety Data Sheets (SDS) for important health, safety, and environmental information.

Follow the link to obtain SDS sheets for 3M products on [3M.com/SDS](https://www.3m.com/SDS).

IMPORTANT! When using any equipment, always follow the manufacturer's instructions for safe operation.

Remarks

This bulletin provides technical information only.

To request additional product information, see the address below.

All questions of warranty and liability relating to this product are governed by the terms and conditions of the sale, subject, where applicable, to the prevailing law.

Before using, the user must determine the suitability of the product for its required or intended use, and the user assumes all risk and liability whatsoever in connection therewith.

3M is a trademark of 3M Company. All other trademarks are the property of their respective owners.

3M United Kingdom PLC
Commercial Branding and Transportation
Cain Road
Bracknell, RG12 8HT
UK
www.3m.co.uk/graphics-and-signage-uk/

© 3M 2025. All rights reserved.