

Kategorie	Media				
3M™ Envision™ Print Wrap Film LX480	LX480mC				
3M™ Envision™ Print Wrap Film SV480	SX480mC				
Gegossen glänzend	IJ70 Series	IJ180 Series	IJ680 Series	780mC	8150 Series
Kalandriert glänzend	IJ40 Series (gloss versions)		IJ20 Series (gloss versions)		
Kalandriert matt	IJ40 Series (matte versions)		IJ20 Series (matte versions)		
3M™ Envision™ Print Film 48	48 Series				
Transluzente Spanntücher	FS-1				