

Category	Media				
3M™ Envision™ Print Wrap Film LX480	LX480mC				
3M™ Envision™ Print Wrap Film SV480	SX480mC				
Gjuten glans	IJ70 Serien	IJ180 Serien	IJ680 Serien	780mC	8150 Serien
Kalendrerad glans	IJ40 Serien (glansig version)		IJ20 Serien (glansig version)		
Kalendrerad matt	IJ40 Serien (matt version)		IJ20 Serien (matt version)		
3M™ Envision™ Print Film 48	48 Serien				
Flexibla substrat	FS-1				