

January, 2011

3M™ Adhesive Transfer Tape 91022

Product Description

3M™ Adhesive Transfer Tape 91022 with 3M™ Silicone Adhesive provide high bond strength to most silicones and difficult-to-bond to substrates, including many low surface energy plastics and select varnished leathers.

Product Features

- Single liner tapes with a stable differential release.
- Good initial quick stick and adhesion build over time.
- Adhesion to silicone rubbers and silicone foams.
- Excellent solvent resistance.
- Superior temperature performance.



Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Property	Values	
Total Tape Thickness without liner	0.05 mm	2 mil
Adhesive Type	Silicone	
Liner Material	PET	
Liner Thickness	0.05 mm	2 mil
Liner Color	White	

Typical Performance Characteristics

90° Peel Adhesion		Substrate
4.4 N/cm	40 oz/in	Stainless Steel
4.4 N/cm	40 oz/in	ABS
4.4 N/cm	40 oz/in	Polycarbonate (PC)
3.8 N/cm	35 oz/in	Polypropylene (PP)
3.8 N/cm	35 oz/in	Silicone Rubber

Property: 90° Peel Adhesion
 Method: ASTM D3330
 Dwell/Cure Time: 24 hr @ Room Temperature

Property	Values		Method	Test Condition	Notes
Maximum Service Temperature	260 °C	500 °F			
Static Shear	>10,000 min		ASTM D3654	1000 g @ Room Temperature	1 in ² sample size
Static Shear	>10,000 min		ASTM D3654	500 g @ 70°C (158°F)	1 in ² sample size
Solvent Resistance	Excellent				

Available Sizes

Property	Values	
Note	Subject to Minimum Order Requirements	
Maximum Available Width	48 in	
Normal Slitting Tolerance	±0.8 mm	±1/32 in
Core Size (ID)	76.2 mm	3 in

Maximum Length		Width
66 m	72 yd	1/2 in to 1 in widths
329 m	360 yd	3 in and wider

Property: Maximum Length

Environmental Performance

Humidity Resistance: High humidity has minimal effect on adhesive performance.

No significant reduction in bond strength is observed after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

UV Resistance: When properly applied, nameplates and decorative trim parts are not adversely affected by exposure.

Water Resistance: Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

Temperature Cycling Resistance: High bond strength is maintained after cycling four times through:

- 8 hours at 194°F (90°C)
- 16 hours at -40°F (-40°C)
- 8 hours at 100.4°F (38°C/100% RH)
- 16 hours at -40°F (-40°C)

Chemical Resistance: When properly applied, nameplate and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids and alkalis.

Handling/Application Information

Application Ideas

- General purpose silicone bonding.
- Vibration damping.
- High temperature applications.
- Ideal for single liner applications.

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure and moderate heat, from 100°F (38°C) to 130°F (54°C), will assist the adhesive in developing intimate contact with the bonding surface.

To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.* Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

*Carefully read and follow the manufacturer's precautions and directions for use when working with solvents. These cleaning recommendations may not be compliant with the rules of certain Air Quality Management Districts in California; consult applicable rules before use.

3M™ Adhesive Transfer Tape 91022

Handling/Application Information (continued)

Application Equipment

To apply adhesives in a wide web format, lamination equipment is required to ensure acceptable quality. To learn more about working with pressure-sensitive adhesives please refer to technical bulletin, Lamination Techniques for Converters of Laminating Adhesives (70-0704-1430-8). For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

Storage and Shelf Life

Store in original cartons at 70°F (21°C) and 50% relative humidity.
If stored under proper conditions, product retains its performance and properties for one year from date of manufacture.

Family Group

	91022	96042
Total Tape Thickness without liner (mm)	0.05	0.13
Adhesive Type	Silicone	Silicone
Liner Material	PET	PET
Liner Thickness (mm)	0.05	0.05
Liner Color	White	White

References

1. 3m.com Product Page
Url: http://www.3m.com/3M/en_US/company-us/all-3m-products/~/3M-Adhesive-Transfer-Tape-91022?N=5002385+3293240965&rt=rud
2. Safety Data Sheet
Url: https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=91022

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

