



SCOTT™
Fire & Safety

3M™ Scott™ RIT-Pak Fast Attack

Emergency Air-Supply System





3M™ Scott™ RIT-Pak Fast Attack

A small, lightweight and compact solution for rapid intervention teams (RIT).

When a call comes in for a structure fire with possible entrapment, or a mayday is issued for a firefighter in distress, the last thing that should be on the minds of the RIT team is the equipment needed to perform the rescue. The RIT-Pak Fast Attack is another example of 3M Scott Fire & Safety listening to the fire services community to deliver a user-friendly and intuitive product solution that firefighters can rely on.

3M Scott's RIT-Pak Fast Attack offers a small, lightweight, and compact solution for rapid entry and air replenishment to a firefighter in distress. Developed with input from firefighters and RIT instructors across the country, the RIT-Pak Fast Attack provides an intuitive design enabling RIT teams to focus on locating and assessing the downed firefighter.

Carrying Device

- High-visibility orange fabric makes it easier to identify the bag in low visibility conditions, while also offering improved durability to meet the rigors of the fireground
- Two color-coded storage compartments provide separation and easy identification of low-pressure and high-pressure components
- Tactile pull handles offer easy identification of low-pressure and high-pressure compartments in low visibility conditions
- Low-pressure compartment sized to allow for facepiece and mask-mounted breathing regulator to remain pre-connected for storage
- 3M™ Scotchlite™ Reflective Material provides enhanced visibility in low light conditions, offers abrasion and water resistance, and is easy to clean
- An easy-to-remove and adjustable length shoulder strap allows for convenient carrying and provides supplementary use as a pick-off strap during RIT removal

- A fixed point carabiner on each end of the bag allows for easy attachment to the firefighter being rescued; captive bar design ensures proper orientation of the carabiner each and every time
- A reinforced protective bottom provides added durability and reduces friction when dragging

Pneumatics

- An external pressure gauge with photoluminescent display provides continuous monitoring of air pressure remaining
- A distinct, audible whistle alarm provides notification when the RIT-Pak Fast Attack has reached 25% of the rated cylinder pressure
- A universal high-pressure charging wand and a low-pressure hose with dual manifold offer maximum versatility for providing emergency breathing air to a firefighter in distress
- 3M™ Scotchlite™ Reflective Material makes it easier to locate the mask-mounted regulator, universal high-pressure charging wand, and low-pressure hose with dual manifold in low light conditions

- Multiple storage options for the universal high-pressure charging wand provide user flexibility

Facepiece

- The facepiece, a modified 3M™ Scott™ AV-3000 SureSeal Facepiece or 3M™ Scott™ Vision C5 Facepiece, has a simple-to-use donning handle, helping to strap onto a downed firefighter or victim





Features



Low-Pressure Hose and Dual Manifold (with Hansen or Rectus fittings)



Facepiece with Mask-Mounted Regulator



Pressure Gauge and Whistle



Shoulder Strap with Quick Adjustment Pull Handle



Carabiner with Captive Bar (Fixed)

High-Pressure Compartment includes:

- Universal Charging Wand
- Pressure Reducer
- Cylinder Valve

Low-Pressure Compartment includes:

- Facepiece
- Regulator
- Hose and Manifold

Bag Specifications:

Small Bag

- Length: ~22 in.
- Width: ~7 in.
- Height: ~7 in.
- Weight: 10.5 lbs (less cylinder)

Medium Bag

- Length: ~27 in.
- Width: ~7 in.
- Height: ~7 in.
- Weight: 10.8 lbs (less cylinder)

Cylinder Specifications:

Cylinder, 4.5, 15 min

- Weight: 7.16 lbs (full)

Cylinder, 4.5, 30 min

- Weight: 11.24 lbs (full)

Cylinder, 5.5, 30 min

- Weight: 10.44 lbs (full)

Cylinder, 5.5, 45 min

- Weight: 14.15 lbs (full)

3M™ Scott™ RIT-Pak Fast Attack

Specifications and Ordering Information.

RIT-Pak Fast Attack (Less Cylinder)								
Part Number	Bag Size	Pressure (psig)	Carrying Bag	6' EBSS Hose	5' RIC Hose	Facepiece Model	Regulator Model	Fixed Carabiner
201564-01	Medium	4500	•	Hansen	•	AV-3000 SureSeal	E-Z Flo	•
201564-02	Medium	5500	•	Hansen	•	AV-3000 SureSeal	E-Z Flo	•
201564-03	Small	4500	•	Hansen	•	AV-3000 SureSeal	E-Z Flo	•
201564-11	Medium	4500	•	Rectus	•	AV-3000 SureSeal	E-Z Flo	•
201564-12	Medium	5500	•	Rectus	•	AV-3000 SureSeal	E-Z Flo	•
201564-13	Small	4500	•	Rectus	•	AV-3000 SureSeal	E-Z Flo	•
201564-21	Medium	4500	•	Hansen	•	Vision C5	E-Z Flo C5	•
201564-22	Medium	5500	•	Hansen	•	Vision C5	E-Z Flo C5	•
201564-23	Small	4500	•	Hansen	•	Vision C5	E-Z Flo C5	•
201564-31	Medium	4500	•	Rectus	•	Vision C5	E-Z Flo C5	•
201564-32	Medium	5500	•	Rectus	•	Vision C5	E-Z Flo C5	•
201564-33	Small	4500	•	Rectus	•	Vision C5	E-Z Flo C5	•

Cylinders	
Part Number	Description
201561-01	4.5, 15 min, Cylinder and Valve (90°)
200870-01	4.5, 30 min, Cylinder and Valve (90°)
201567-01	5.5, 30 min, Cylinder and Valve (90°)
201568-01	5.5, 45 min, Cylinder and Valve (90°)

Replacement Parts (Spares)	
Part Number	Description
201558-01	RIT-Pak Fast Attack, Bag, Medium
201558-02	RIT-Pak Fast Attack, Bag, Small
201600-01	RIT-Pak Fast Attack, Shoulder Strap Assembly
201595-01	RIT-Pak Fast Attack, Facepiece
201605-02	RIT-Pak Fast Attack, E-Z Flo Regulator, Hansen
201605-03	RIT-Pak Fast Attack, E-Z Flo Regulator, Rectus
31003648	RIT-Pak Fast Attack, Carabiner
201825-01	Vision C5 Facepiece, RIT-Pak Variant
201673-03	RIT-Pak Fast Attack, E-Z Flo C5 Regulator, Hansen
201673-04	RIT-Pak Fast Attack, E-Z Flo C5 Regulator, Rectus



3M Scott Fire & Safety

Personal Safety Division
Monroe Center, P.O. Box 569
Monroe, NC 28111

Phone 1-800-247-7257
Email US-3M-ScottMonroeCSR@mmm.com
Web 3M.com/ScottFire
3M.ca/ScottFire

3M, Scott and Scotchlite are trademarks of 3M. Used under license in Canada.
© 2022, 3M. All rights reserved. 2112-22581 E