



## 3M™ Scott™ Airline Hose

### Description

3M Scott Fire & Safety Airline Hose and coupling assemblies must be used with Scott Airline Respirators as represented on the NIOSH approval label supplied with your Scott Respirator in order to maintain NIOSH/MSHA approvals of the respirator.



AIRLINE HOSE Specifications	
MATERIAL	BLACK NEOPRENE RUBBER
ID	1/4" ID
WORKING PRESSURE	300 PSI MAXIMUM
AIRLINE HOSE TEMPERATURE RANGE	-25° F TO 205° F

### Ordering Information

3M Scott Fire & Safety Airline Hose is available in designated segments with quick-disconnect couplings. A maximum of 12 segments totaling 300 feet is approved for use with Scott Airline Respirators.\*

Always refer to the 3M Scott Fire & Safety Operations and Maintenance Manual and NIOSH approval label supplied with your Scott Respirator to ensure you are using an approved assembly.

Part Number	Length	Coupling
26369-025	25 FEET	HANSEN HK
26369-050	50 FEET	HANSEN HK
26369-100	100 FEET	HANSEN HK
26370-025	25 FEET	FOSTER
26370-050	50 FEET	FOSTER
26370-100	100 FEET	FOSTER
30010-025	25 FEET	HANSEN
30010-050	50 FEET	HANSEN
30010-100	100 FEET	HANSEN
30020-025	25 FEET	SCHRADER
30020-050	50 FEET	SCHRADER
30020-100	100 FEET	SCHRADER
805659-025	25 FEET	CEJN
805659-050	50 FEET	CEJN
805659-100	100 FEET	CEJN

\* Exception: Hansen HK, maximum number of segments is 6, maximum length is 150 feet. Additional Airline Hose Length Part Numbers Available Upon Request



**3M Scott Fire & Safety**

Personal Safety Division  
Monroe Center, P.O. Box 569  
Monroe, NC 28111

Phone 1-800-247-7257  
E-Mail ScottMonroeCSR@scottsafety.com  
Web ScottSafety.com

H/S 7092\_EN 6/18 ISO 9001 Registered.  
Please recycle. Printed in USA © 3M 2018. All rights reserved.  
3M and Scott are trademarks of 3M.