



SCOTT
Fire & Safety

3M™ Scott™ Cylinders





3M™ Scott™ Cylinders

Over the years, breathing air cylinders have been providing SCBA users with a supply of fresh air. The original cylinders were made of steel and quite heavy. But today, advances in technology have enabled cylinders to become much lighter and less burdensome to the SCBA user. 3M Scott offers a complete assortment of cylinders to meet the needs and demands of all SCBA users – aluminum cylinders for infrequently used SCBA to carbon-wrapped cylinders for daily use. In addition, 3M Scott offers a variety of cylinders for its escape products.

5500 PSIG Cylinder:

One of the lightest and smallest cylinders used on self-contained breathing apparatus.

The best way to understand the needs of SCBA users is to simply listen. 3M Scott did just that by visiting SCBA users from across North America. The participants included fire chiefs, SCBA technicians, safety officers and firefighters. It was not exclusive to the fire service, as representatives from the military, general industry and law enforcement were also included. The overwhelming attribute that users requested was a reduction in weight, followed closely by a reduction in profile.

The engineers of 3M Scott determined the best manner to accomplish this was to increase the pressure of the cylinders to 5500 psig. The 5500 psig cylinder, an “industry first,” has approximately a 10% reduction in weight and profile as compared to a traditional 4500 psig cylinder and is available in 30-, 45-, 60- and 75-minute durations.

The construction maintains an aluminum liner wrapped with layers of carbon fibers and fiberglass, and sealed with a protective epoxy resin coating, which makes the cylinder easier to clean.


The overall result is a lighter “3M™ Scott™ Air-Pak™ SCBA that helps to reduce user fatigue, increase productivity and decrease injuries.

Accessory Items:

Custom Logo I.D. Bands

3M Scott offers its customers the ability to customize their new carbon cylinders by adding a personalized logo. This custom logo is printed on white paper, and protected by the fiberglass wrap and epoxy resin.

- Maltese cross or customer-provided graphic
- Greater visibility
- Easy to identify
- Reduces cylinders being misplaced in mutual aid scenarios
- Minimum order quantity of 25 cylinders



Cylinder Offerings

Aluminum Cylinder

- Aluminum cylinders are built to the Department of Transportation (DOT) and Transport Canada (TC) specifications
- 2216 psig working pressure
- Rated for 30-minute duration, based on NIOSH breathing rates
- Hydrostatic testing to be performed every five years
- Unlimited life expectancy

Carbon Cylinder

- Carbon cylinders are built to DOT and TC specifications
- 2216, 4500 and 5500 psig working pressures
- Lightweight, composite cylinder consisting of an aluminum alloy inner shell with a total overwrap of carbon fiber, fiberglass and epoxy resin
- Rated for 30-, 45-, 60- and 75-minute durations based on NIOSH breathing rates
- Luminescent band provides enhanced visibility
- 75-minute cylinder is ideal for Rapid Intervention Team (RIT) and extended-duration operations
- Hydrostatic testing to be performed every five years
- 15-year life expectancy

ST7 Tough Cylinder

- ST7 Tough cylinders are built to DOT and TC specifications
- Built extremely tough and durable
- Provides added protection against abrasion and abuse
- 4500 psig working pressure
- Rated for 30-, 45- and 60-minute durations based on NIOSH breathing rate
- Luminescent band provides enhanced visibility
- Hydrostatic testing to be performed every five years
- 15-year life expectancy

Escape Cylinder

- 2216 psig aluminum cylinders available in 3-minute or 5-minute durations with unlimited life expectancy
- Carbon cylinders available in 3000 psig (5-minute or 10-minute durations) and 4500 psig (15-minute duration)
- 15-year life expectancy for carbon cylinders

30-Year Life Cylinder

- 30-year cylinders (available in the US only) are built to DOT specifications
- 4500 psig working pressure
- Lightweight, composite cylinder consisting of an aluminum alloy inner shell with a total overwrap of carbon fiber, fiberglass and epoxy resin
- Rated for 30-, 45- and 60-minute durations based on NIOSH breathing rates
- Luminescent band provides enhanced visibility
- Hydrostatic testing to be performed every five years
- Up to a 30-year life expectancy

Accessory Items:

To help prevent damage and improve durability of the cylinder, 3M Scott offers several protective solutions.

Cylinder Sleeves

Protective sleeves are offered for 2216 psig, 4500 psig, and 5500 psig carbon cylinders, and will accommodate multiple cylinder sizes, to include 30-, 45- and 60-minute durations.

- Constructed of a specially-compounded fire-retardant-grade of clear, high-durometer, PVC/ Plastisol
- Easy to use and install over the cylinder, forming a protective barrier
- Approved by NIOSH and certified to NFPA 1981, as an accessory to the 3M™ Scott™ Air-Pak™ SCBA

Cylinder End Caps

Protective end caps are offered for 4500 psig carbon cylinders and will accommodate 30- and 45-minute rated durations.

- Protects the crown areas of carbon cylinders
- Easy to install and remains firmly adhered to cylinder
- Easily removed and reused as necessary (i.e. hydrostatic testing)
- Can be purchased individually or as a set
- Certified to NFPA 1981, as an accessory to the 3M™ Scott™ Air-Pak™ SCBA

Cylinder Valves



CGA Threaded Cylinders



Snap-Change Cylinders



ACSi Cylinders

Description		Duration	Air Capacity		Volume	Dimensions			Weight	
Part Number	Pressure (psig)	Minutes (at 40 LPM)	Cubic Feet (SCF)	Liters	H ₂ O (in ³)	Length less Valve (in)	Length with Valve (in)	External Diameter (in)	Empty Cylinder with Valve (lbs.)	Full Cylinder with Valve (lbs.)
Escape Cylinder (CGA Threaded)										
Aluminum										
801935-03	2216	5	7	203	83	9.3	12.4	4.4	4.7	5.3
805031-01	2216	3 or 5	7	203	83	9.3	12.4	4.4	4.9	5.4
Carbon-Wrapped										
200779-03	4500	15	24	666	148	14.3	17.4	4.7	5.3	7.0
805947-02	3000	5	8	219	68	9.2	12.3	4.0	3.3	3.9
805948-02	3000	10	17	488	151	13.9	17.0	4.5	4.4	5.7
200779-01	4500	15	24	666	148	14.5	17.6	4.8	5.5	7.2
ELSA Cylinder										
Aluminum										
8007200	2216	5	8	225	92	10.0	13.0	4.4	5.1	5.7
8007201	3000	10	15	432	134	14.7	17.8	4.4	7.9	9.0

Description		Duration	Air Capacity		Volume	Dimensions			Weight	
Part Number	Pressure (psig)	Minutes (at 40 LPM)	Cubic Feet (SCF)	Liters	H ₂ O (in')	Length less Valve (in)	Length with Valve (in)	External Diameter (in)	Empty Cylinder with Valve (lbs.)	Full Cylinder with Valve (lbs.)
CGA Threaded Cylinders										
Aluminum										
804101-01	2216	30	45	1267	517	21	24.0	6.8	18.1	21.4
Carbon-Wrapped										
804840-01	2216	30	45	1282	523	20.5	23.5	6.6	8.3	11.6
804721-01	4500	30	45	1285	285	18.5	21.6	5.5	7.7	11.1
804722-01	4500	45	67	1886	418	20.3	23.4	6.3	10.1	15.0
804723-01	4500	60	88	2482	550	21.5	24.6	6.9	12.7	19.2
200930-01	5500	30	43	1201	233	19.1	22.2	4.9	6.9	10.0
200969-01	5500	45	64	1800	349	19.1	22.2	6.0	9.1	13.8
200972-01	5500	60	85	2400	465	21.4	24.5	6.5	11.1	17.4
200975-01	5500	75	106	2999	581	22.4	25.5	7.2	13.8	21.6
Carbon-Wrapped Short and Stubby										
804722-01A	4500	45	66	1877	416	18.0	21.1	6.8	10.4	15.3
Carbon-Wrapped ST7										
804721-11	4500	30	45	1285	285	18.5	21.6	5.5	7.7	11.1
804722-11	4500	45	67	1886	418	20.3	23.4	6.3	10.1	15.0
804723-11	4500	60	88	2482	550	21.5	24.6	6.9	12.7	19.2
Carbon-Wrapped 30-Year										
804721-35	4500	30	45	1285	285	18.7	21.7	5.5	8.1	11.5
804722-35	4500	45	67	1886	418	20.7	23.7	6.4	10.9	15.8
804723-35	4500	60	88	2482	550	21.7	24.7	7.0	14.0	20.5
Snap-Change Cylinders										
Carbon-Wrapped										
200131-01	2216	30	45	1282	523	20.5	23.5	6.6	8.6	11.9
200128-01	4500	30	45	1285	285	18.5	21.6	5.5	8.1	11.4
200129-01	4500	45	67	1886	418	20.3	23.4	6.3	10.4	15.3
200130-01	4500	60	88	2482	550	21.5	24.6	6.9	13.1	19.5
200967-01	5500	30	43	1201	233	19.1	22.2	4.9	7.2	10.3
200970-01	5500	45	64	1800	349	19.1	22.2	6.0	9.4	14.1
200973-01	5500	60	85	2399	465	21.4	24.5	6.5	11.4	17.7
200976-01	5500	75	106	2999	581	22.4	25.5	7.2	14.2	22.0
Carbon-Wrapped Short and Stubby										
200129-01A	4500	45	66	1877	416	18.2	21.3	6.8	10.8	15.6
Carbon-Wrapped ST7										
200128-11	4500	30	45	1285	285	18.5	21.6	5.5	8.1	11.4
200129-11	4500	45	67	1886	418	20.3	23.4	6.3	10.4	15.3
200130-11	4500	60	88	2482	550	21.5	24.6	6.9	13.1	19.5
Carbon-Wrapped 30-Year										
200128-35	4500	30	45	1285	285	18.7	21.7	5.5	8.5	11.8
200129-35	4500	45	67	1886	418	20.7	23.7	6.4	11.3	16.2
200130-35	4500	60	88	2482	550	21.7	24.7	7.0	14.4	20.8
ACSi Cylinders (90-Degree CGA Threaded)										
Aluminum										
200874-01	2216	30	45	1267	517	20.9	24.0	6.8	18.1	21.4
Carbon-Wrapped										
200873-01	2216	30	45	1282	523	20.5	23.6	6.6	8.3	11.6
200870-01	4500	30	45	1285	285	18.5	21.7	5.5	7.8	11.2
200871-01	4500	45	67	1886	418	20.3	23.4	6.3	10.2	15.1
200872-01	4500	60	88	2482	550	21.5	24.6	6.9	12.8	19.3



Personal Safety Division
3M Scott Fire & Safety
 Monroe Center, P.O. Box 569
 Monroe, NC 28110

Phone 1-800-247-7257
 Email US-3M-ScottMonroeCSR@mmm.com
 Web 3M.com/ScottFire (US)
 3M.ca/ScottFire (Canada)

3M, Scott and Air-Pak are trademarks of 3M. Used under license in Canada. © 3M, 2025. All rights reserved. All other trademarks are property of their respective owners.