

3M[™] Polyurethane Protective Tape 8672

Technical Data Sheet

Product Description

3M™ Polyurethane Protective Tape 8672 is made from a tough abrasion resistant polyurethane elastomer that resists punctures, tearing, abrasion and erosion. It is formulated for resistance to ultraviolet light. 3M 8672 Tape provides a simple, easy method of protecting a surface from corrosion, abrasion and minor impact damage. It can be installed in a minimum amount of time with simple tools. It can be painted or applied over painted surfaces. 3M 8672 Tape is a transparent tape constructed with a pressure-sensitive acrylic adhesive that is protected with an easy-release polyester liner.

Typical Physical Properties and Performance Characteristics

Note: 1) The following technical information and data should be considered representative or typical only and should not be used for specification purposes. 2) ASTM = American Society for Testing and Materials. 3) Metric values are listed in parenthesis

Property	Test Method	Units	Typical Value
Tensile Strength @ Break	ASTM D882	lb/in (N/100 mm)	40 (700)
Elongation % @ Break	ASTM D882	%	500
Peel Adhesion @ 70°F (21°C) to:		oz/in (N/100 mm)	
Bare Aluminum	ASTM D-1000		60 (66)
Acrylic Enamel Paint			43 (48)
ABS Plastic			50 (55)
Max. Service Temperature		°F (°C)	180°F (82°C)

Dimensions

Approximate Applied Thickness*	0.006 inch (0.15 mm) Film	
	0.002 inch (0.06 mm) Adhesive	
	0.008 inch (0.21 mm) = Total thickness	
Standard Roll Length	36 yd (32.9 m)	
Available Widths	Minimum 1 inch	
	Maximum 48 inches	
	(2.54 cm to 122 cm)	
Approximate Weight*	0.47 lb/yd² (236.3 g/m²)	

^{*}Excludes the liner that is removed from the tape prior to application.

General Information

- 3M 8672 Tape has been used to isolate and protect substrates from environmental damage and corrosive elements
- 3M 8672 Tape can be used to provide a UV-resistant surface coating for indoor and outdoor applications
- 3M 8672 Tape may be painted per 3M[™] Technical Bulletin Polyurethane Protective Tape, Paint Instructions

Shipping and Storage

No special/hazardous labeling or packaging required or regulations for air, ground or water shipment for this product. Keep film in a clean area, away from excessive moisture and out of direct sunlight. Store rolls in the shipping carton. Return partially used rolls to the shipping carton. **Shelf life:** Two (2) years from date of manufacture

Precautionary Information

Refer to Product Label and Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501, and visit www.3m.com/3M/en_US/company-us/SDS-search/

Additional Information

In the U.S. call toll free 1-800-235-2376, or fax 1-800-435-3082 or 651-737-2171. For U.S. Military, call 1-866-556-5714. If you are outside of the U.S., please contact your nearest 3M representative.

Authorization to Use

Ensure products meet all applicable specifications, standards, and maintenance manual requirements for the platform being worked on and validate all aircraft approvals against current technical documentation.

*These products were manufacture under a 3M Quality Management System registered to the AS9100 standard

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive & Aerospace Solutions Division 3M Center St. Paul, MN 55144-1000 Phone 1-800-328-1684 Web www.3M.com/aerospace 8672

Issue date: 5/2021

3M is a trademark of 3M Company © 3M 2021. All rights reserved.