

April, 2014

3M™ Plasticizer Resistant Hook Fastener SJ3522

Product Description

3M™ Hook and Loop Fasteners offer advanced closure alternatives to zippers, screws, snaps, hooks and more. They offer greater design flexibility, faster product assembly, smoother and cleaner exterior surfaces and improved product performance in many applications. 3M hook and loop fasteners consist of hooks and loops which engage to form a quick fastening attachment. Simply pull the strips apart by hand to disengage.

Product Features

3M™ Plasticizer Resistant Hook Fastener SJ3522 is one part of a two-part fastener solution designed to provide great durability for thousands of closures. With its plasticizer resistant, acrylic-based pressure sensitive adhesive backing, this fastener allows for easy and convenient attachment to a variety of substrates, especially flexible vinyl's. Commonly paired with 3M™ Loop Fastener SJ3523, this hook fastener can also engage with other 3M™ Loop Fasteners.



3M™ Plasticizer Resistant Hook Fastener SJ3522

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Thickness		Test Condition
2.4 mm	91 mil	Unmated without liner
0.33 mm	140 mil	Mated without liner

Property: Thickness

notes: Using 1/2" pressure foot with 34 gram weight

Property	Values	
Material	Hook- Woven Nylon	
Backing	Plasticizer resistant acrylic PSA	
Liner	Non printed polyolefin film	
Liner Thickness	0.089 mm	3.5 mil
Liner Color	Clear	
Weight	0.063 g/cm ²	0.015 oz/in ²

Typical Performance Characteristics

Property	Values		Substrate	Notes
Dynamic Tensile	7.6 N/cm ²	11 lb/in ²	Nylon Hook to Nylon Loop	Run at 12 inches per minute
Dynamic Shear	15.2 N/cm ²	22 lb/in ²	Nylon Hook to Nylon Loop	Run at 12 inches per minute
Cleavage Strength	13.1 g/cm width	7.5 lb/in width	Nylon Hook to Nylon Loop	
T-Peel Adhesion	3.5 g/cm width	2 lb/in width	Nylon Hook to Nylon Loop	Run at 12 inches per minute
90° Peel Adhesion	3.9 g/cm width	2.2 lb/in width	Nylon Hook to Nylon Loop	Run at 12 inches per minute
Cycle Life	5000		Nylon Hook to Nylon Loop	Number of closures before losing 50% of original strength

3M™ Plasticizer Resistant Hook Fastener SJ3522

Typical Performance Characteristics (continued)

Product Performance:

Material Dynes mJ/m ²	Polypropylene 29	Polyethylene 31	EVA 33	Acrylic 38	PC 42	ABS 42	Aluminum 840	Stainless Steel 700-1100	Typical Temperature Resistance °F
	Low Surface Energy Plastics			Medium Surface Energy Plastics			High Surface Energy Materials		
SJ3401 SJ3402	Sew on			Sew on			Sew on		200
SJ3530 SJ3531	X	X	X	X	X	X	X	X	90
SJ3532N SJ3533N	X	X	X	X	X	X	X	X	110
SJ3526N SJ3527N	X	X	X	X	X	X	X	X	120
SJ3522 SJ3523				X	X	X	X	X	150
SJ3571 SJ3572				X	X	X	X	X	200
X - Typically good adhesion without the use of surface primer									

Additional Information

notes: This guide should assist you in determining which product will adhere best to your substrate for.

Handling/Application Information

Directions for Use

Attachment Techniques

The following information is intended to assist the designer considering the use of 3M hook and loop fasteners. System product performance depends upon a number of factors, including the fastener (material, adhesive and area), application method, surface characteristics (material, texture and cleanliness), environmental conditions (moisture, ultraviolet and temperature exposure) and the time it is expected to support a given load. Because many of these factors are uniquely within the user's knowledge and control, it is required that the user evaluate 3M products to determine whether they are fit for a particular purpose and are suitable for the user's substrates, method of application and desired end use.

Rounding the corners, slightly recessing the product into the substrate, or providing raised edges around the Reclosable fastener can reduce the possibility of edge lifting and improve the overall appearance of the fastener on the finished product. Mechanically securing the corners of the fastener with rivets, staples, screws, etc. may also reduce the possibility of edge lifting, but may reduce the closure performance.

The two most common techniques for attaching these 3M hook and loop fasteners to various surfaces are summarized below.

Pressure Sensitive Adhesive Attachment: The use of pressure sensitive adhesives eliminates or reduces the need for sewing, solvent activation, dielectric or ultrasonic bonding or bulk adhesive bonding. This can result in simplicity, improved safety and lower installation costs. Pressure sensitive adhesive products can be applied manually or automatically using a variety of equipment choices. Contact your 3M Sales Representative to discuss automated equipment options.

Surface Preparation: Highly textured surfaces may reduce the ultimate adhesion levels and care should be given to minimize the surface texture or roughness.

Adhesive backed fasteners should be applied to surfaces that are clean, dry and free of oil, grease, dust, mold release agents or surface contaminants that could reduce the adhesion. It is recommended to remove any surface contaminants that may reduce adhesion by using a method suited for the type and quantity of surface contaminants present. Isopropyl alcohol is a good general use solvent for cleaning contaminants from surfaces for example.

In exceptional cases, especially when removing silicone mold release agents or on rough, porous surfaces, it may be necessary to lightly abrade the surface, use an adhesion promoter, or surface sealer to optimize the adhesive bond to the substrate. The selection of abrasion, priming or sealing methods will depend upon the substrates and the environmental conditions the product will be exposed to during use.

Attachment Procedure: To obtain optimum bond to any surface, both the fasteners and the target surfaces should have equilibrated for a minimum of one hour at temperatures between 68°F (20°C) to 100°F (38°C) before application. The liner protecting the adhesive is removed and preferably without touching the adhesive, the fastener is applied to the substrate. Exposure of the adhesive to ambient conditions without the protective liner, before applying to the surface, should be minimized as initial adhesive tack may decrease. Flexible materials should be lying on a hard flat surface so as to permit uniform adhesive contact with the surface. Use of a rubber hand roller, press platen or similar device is recommended to ensure full adhesive contact or wet- out with the substrate surface. Approximately 4.5 pounds of force per square inch, (310 grams per square centimeter) is recommended to increase adhesive contact, improving bond strength. For all adhesive applications, it is important to ensure that the edges are rolled down to reduce the chance of edge lifting.

Plain backed

The plain backed 3M hook and loop fasteners are most commonly sewn into their applications. Liquid or hot melt adhesives and staples are other forms of attachment that can be utilized.

Sewing: Although the selvage edge was initially developed for stitching on, customers often find that they get better anchorage when stitching through the 3M hook and loop portions of the fastener – this may be application dependent. The type of thread and stitch type is also best determined based on individual application, however, the fastener should be stitched on all edges for the best seam strength. Typically, special machine adjustments are not necessary when using our 3M hook and loop fasteners

Storage and Shelf Life

Shelf Life when stored in original packaging at 72°F (22°C) and 50% RH is 24 months.

Trademarks

3M is a trademark of the 3M Company.

3M™ Plasticizer Resistant Hook Fastener SJ3522

Family Group

	SJ3401	SJ3522	SJ3523	SJ3526N	SJ3527N	SJ3402	SJ3531	SJ3571	SJ3572	SJ3532N	SJ3533N	SJ3530
Thickness (mm) Test Condition: Unmated without liner	2	2.4	3.2	2.4	3.2	2	3.2	3.2	2.4	2.03	3.05	2.4
Thickness (mm) Test Condition: Mated without liner	3.1	0.33	0.33	0.33	0.33	3.1	0.33	0.33	0.33	3.3	3.3	0.33
Material	Loop- Woven Nylon	Hook- Woven Nylon	Loop- Woven Nylon	Hook- Woven Nylon	Loop- Woven Nylon	Hook- Woven Nylon	Loop- Woven Nylon	Loop- Woven Nylon	Hook- Woven Nylon	Hook- Woven Nylon	Loop- Woven Nylon	Hook- Woven Nylon
Backing	No Adhesive Sewon	Plasticizer resistant acrylic PSA	Plasticizer resistant acrylic PSA	High Performance rubber based PSA	High Performance rubber based PSA	No Adhesive Sewon	General Purpose rubber based PSA	High Performance Acrylic PSA	High Performance Acrylic PSA	Rubber based PSA	Rubber based PSA	General Purpose rubber based PSA
Liner	None	Non printed polyolefin film	Non printed polyolefin film	Polyethylene with red printing	Polyethylene with red printing	None	Polyp ropyl ene	Polyole fin with embossed 3M logo	Polyole fin with embossed 3M logo	White Polypropylene	White Polypropylene	Polyp ropyl ene
Liner Thickness (mm)		0.089	0.089	0.08	0.08		0.08	0.1	0.1	0.08	0.08	0.08
Liner Color		Clear	Clear	White	White		White	Clear	Clear			White

References

- 3m.com Product Page
Url: https://www.3m.com/3M/en_US/company-us/all-3m-products/~/-/3M-Plasticizer-Resistant-Hook-Fastener-SJ3522?N=5002385+3293241237&rt=rud
- Safety Data Sheet
Url: https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=SJ3522

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001: 2000 and ISO/TS 16949:2002 standards.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

3M™ Plasticizer Resistant Hook Fastener SJ3522

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

