

## 3M Cleaning Chemical Usage Guide

3A

### 3M™ Neutral Cleaner Concentrate 3A

- Use for daily floor cleaning
- Use in mop bucket, auto scrubber, or 3M™ Easy Scrub Express
- Green Seal™ Certified



17A

### 3M™ Glass Cleaner and Protector 17A

- Non-streaking formula with Scotchgard™ Protection built to remove and protect against finger prints, water spots, etc.
- Also suitable as a general purpose cleaner
- Green Seal™ Certified



34A

### 3M™ Peroxide Cleaner Concentrate 34A

- Non-rinse, fragrance free formula
- Versatile for rest rooms, carpets and floors
- Use in mop bucket



42A

### 3M™ MBS Disinfectant Cleaner Concentrate 42A

- EPA registered, 5 minute contact time, hospital grade disinfectant
- Flexible applications: Mop bucket, flat mop tools, trigger sprayer, flip top cap, charge buckets, wipes, etc.
- No scent

