



3M™ Scott™ Ska-Pak Plus Supplied-Air Respirator



Supplied-Air Respirator

The Ska-Pak Plus supplied-air respirator (SAR) is a combination escape SCBA and SAR that offers emergency respiratory protection in hazardous atmospheres, including those identified as immediately dangerous to life or health (IDLH).

This respirator features either a padded nylon or padded Kevlar® harness for additional comfort in extended wear applications and the E-Z Klip cylinder retention mechanism for quick and easy cylinder change-out.

The Ska-Pak Plus respirator is versatile and can be used in numerous markets, including chemical, food processing, petrochemical, oil and gas, ship building and public utilities for applications like confined space entry, hazardous materials handling, general maintenance and turnarounds.

Product Highlights

- Includes E-Z Flo pressure-demand regulator with first-breath activation and low exhalation resistance for easy breathing and reduced user fatigue
- 5, 10, or 15-minute rated cylinder egress options for selection versatility based on the job at hand
- Optional “E-Z Fill” auxiliary fitting facilitates direct connection to high-pressure cylinder charging systems to enhance efficiency
- E-Z Klip cylinder retention system for quick and easy cylinder change-outs
- Three harness styles:
 - Padded Nylon that is designed to be comfortable and lightweight
 - Padded fire-resistant Kevlar® for high heat environments or when there is potential for sparking

3M™ Scott™ Ska-Pak Plus

Supplied-Air Respirator

SAR Model	Entry/Egress ¹	Pressure (psig)	Cylinder	Harness	Regulator	Air Line	Facepiece ²	Case ³	Packaging
3 Ska-Pak Plus SAR	2 Entry/Egress	2 2216	00 None	3 Nylon	1 E-Z Flo	0 None	0 None	0 None	1 One Per Box
	3 Egress Only	3 3000	01 2216 Aluminum, 5 min	4 Kevlar®	2 E-Z Flo Modulair	1 Hansen	3 AV-3000 SureSeal, Kevlar® (M)	1 Hard Case	
		4 4500	02 3000 Carbon, 5 min			2 Schrader	6 AV-3000 SureSeal, Polyester (M)		
		7 3000 E-Z Fill	03 3000 Carbon, 10 min			3 Cejn	9 AV-3000 SureSeal, Rubber (M)		
		8 4500 E-Z Fill	06 4500 Carbon, 15 min			4 Hansen HK Plug			
			Drained			5 Hansen HK Socket			
			AA 2216 Aluminum, 5 min						
			BB 3000 Carbon, 5 min						
			CC 3000 Carbon, 10 min						
			FF 4500 Carbon, 15 min						

Part Number

Select a one- or two-digit number per box from the chart above that corresponds to your choice.

SAR	3				0					1
-----	---	--	--	--	---	--	--	--	--	---

1. Must select Entry/Egress to select an air line option.
2. If you prefer an alternate facepiece style, head harness or size, choose "none" and order an approved facepiece as a separate line item.

Combination Air Line

As a Type C positive pressure respirator, the Ska-Pak Plus supplied-air respirator can be used with various lengths of 3M Scott supplied-air hose for a combination of up to 12 segments, totaling 300 feet*. Available with Hansen, Schrader, Cejn, Hansen HK plug or Hansen HK socket fittings.

Regulator

The benefits of the E-Z Flo pressure-demand regulator start with first-breath activation and its low exhalation resistance means less effort to breathe and less fatigue. Doffing is made simple with the E-Z Flo air-saver switch. Depressing the air-saver switch immediately stops the air flow into the mask. The Modulair offers quick disconnect to easily remove the regulator from the rest of the respirator.

Harness

The nylon and Kevlar® harness are lightweight with padded adjustable shoulder straps for maximum comfort. The harness includes web adjusters and quick release buckles. A strain relief location on the waist belt prevents the regulator's air hose from tugging on the regulator during operation.

Cylinder Options

The Ska-Pak Plus supplied-air respirator is available with the following rated cylinders, featuring the E-Z Klip cylinder retention system:

- 5-minute 2216 psi aluminum
- 5-minute 3000 psi carbon
- 10-minute 3000 psi carbon
- 15-minute 4500 psi carbon

E-Z Fill Cylinder Valve

Optional "E-Z Fill" auxiliary fitting facilitates direct connection to high-pressure cylinder charging systems to enhance efficiency (3000 and 4500 psi only)

Facepieces

The Ska-Pak Plus supplied-air respirator is used with the AV-series facepieces, which feature the 3M Scott Top-Down Convertibility platform, allowing one facepiece to be used in numerous respiratory protection applications, from supplied-air to air-purified. This one-facepiece concept reduces inventory and training costs and eliminates the need to fit-test multiple facepieces for each employee.

*Exception: Hansen HK, maximum number of segments is 6, maximum length is 150'.

Related Products:



3M™ Scott™ Ska-Pak AT
Supplied-Air Respirator



3M™ Scott™
Mobile Air Cart



3M™ Scott™
Air Line Hose



These respirators help to protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of applicable jurisdiction, as appropriate. Improper use may result in sickness or death. For correct use, see supervisor and User Instructions, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.



3M Scott Fire & Safety

Personal Safety Division
Monroe Center, P.O. Box 569
Monroe, NC 28110

3M PSD products are occupational use only.

1-800-247-7257
3M.com/ScottIndustrial (US)
3M.ca/ScottSafety (Canada)

Please recycle. Printed in USA. © 2023, 3M. All rights reserved.
3M, SCOTT and Ska-Pak are trademarks of 3M.
Used under license in Canada.
Kevlar® is a registered trademark of E.I. Du Pont de Nemours and Company.

HS 7082D_EN 11/23 2202-23290b-E