


CSH Series

ORDERING INFORMATION

Sample Part Number



6 = 600A (All Aluminum Components; Al/Cu rated)
 7 = 600A (Copper Components and Copper-Top Lug; Al/Cu rated)
 9 = 900A (All Copper Components)*

N = None
 T = W/ Capacitive Test-Point

Elbow Size
 Select **Elbow Size (O, P, or Q)** based on USE RANGE-CSH TABLE. Leave **Lug Code** blank.

Compression Lug Kit:
 Select **Elbow Size (O, P, or Q)** based on USE RANGE-CSH TABLE. Select **Lug Code** using TABLE X.

Range Taking Kit w/ Shear Bolt Lug:**
 Select **Elbow Size + Lug Code** using TABLE XRA-CSH.

1 = CSH Housing and Stud
 2 = CSH Housing, Stud, and Insulating Plug

Note: Leave blank if Shield Adapter is not needed.
 G = Tinned Copper Braid w/ Solder Block and Constant Force Spring
 Braid size is #6 for housing size "O" and #4 for housing sizes "P" and "Q".

2 = 15/25 kV

Table X - Compression Lug Selection

Conductor Size	Strd/Compr	Cmpt/Sol
	"X"	"X"
#2	7	6
#1	8	7
1/0 AWG	9	8
2/0 AWG	10	9
3/0 AWG	11	10
4/0 AWG	12	11
250 kcmil	13	12
300 kcmil	14	13
350 kcmil	15	14
400 kcmil	16	15
450 kcmil	17	16
500 kcmil	18	17
550 kcmil	20	18
600 kcmil	20	18
650 kcmil	211 [†]	20
700 kcmil	22	20
750 kcmil	23	211 [†]
800 kcmil	24	22
900 kcmil	26	23
1000 kcmil	28	26
1100 kcmil	285	contact factory
1250 kcmil	29	contact factory
1500 kcmil	30	contact factory

[†] For copper P9CU Series Lugs, use code 21 instead.

* For use with copper conductors only.
 ** Range Taking Shear Bolt Lugs are only available in 600A aluminum (Al/Cu rated).

Sample Part Number is a 15/25 kV 600A CSH kit. Kit includes Size "P" CSH (with Test Point), Stud, Insulating Plug, Aluminum Compression Lug for 500 kcmil Strd/Compr, and a PCRK-GA-05 Shield Adapter kit.

CSH Series

SIZING OPTIONS

The following product sizing information is based on AEIC/ICEA dimensional ranges. The true range of the CSH Series on a particular cable construction may vary. To confirm sizing on non-standard cables, or to check sizing on cables that fall just outside our min or max, contact the factory.

Table XRA-CSH - Range Taking Lug Selection[†]

Elbow Size + Lug Code	Voltage	Kit Conductor Range	
		Minimum	Maximum
OR1	15 kV (175 mil)	1/0 AWG [‡]	300 kcmil
	15 kV (220 mil)	#2 AWG [‡]	
	25 kV (260 mil)	#3 AWG	
OR2	15 kV (175/220 mil)	1/0 AWG [‡]	450 kcmil
	25 kV (260 mil)		350 kcmil
PR3	15 kV (175/220 mil)	350 kcmil [‡]	600 kcmil
	25 kV (260 mil)		
PR4	15 kV (175/220 mil)	350 kcmil [‡]	750 kcmil
	25 kV (260 mil)		
QR4	15 kV (175 mil)	750 kcmil	750 kcmil
	15 kV (220 mil)	600 kcmil	
	25 kV (260 mil)	500 kcmil [‡]	
QR5	15 kV (175 mil)	750 kcmil	1250 kcmil
	25 kV (260 mil)	600 kcmil	

[†] Range Taking Shear Bolt Lugs are only available in aluminum (Al/Cu rated).
[‡] May not fit some compact/compressed cables. See USE RANGE TABLE below.

Use Range-CSH Table

Elbow Size	Voltage Class	Conductor Size	
		Minimum	Maximum
O	15 kV (175 mil)	1/0 AWG*	500 kcmil
	15 kV (220 mil)	#2 AWG**	
	25 kV (260 mil)	#4 AWG	
P	15 kV (175/220 mil)	350 kcmil***	750 kcmil
	25 kV (260 mil)	4/0 AWG	
Q	15 kV (175 mil)	750 kcmil	1500 kcmil
	15 kV (220 mil)	600 kcmil	
	25 kV (260 mil)	500 kcmil****	



3M Electrical Markets Division
 3M Canada
 P.O. Box 5757
 London, Ontario
 N6A 4T1

3M Electrical Markets Division is an authorized dealer for



* May not fit some 1/0 AWG compressed/compact 100% (175mil) insulated power cables. Check minimum insulation diameter to confirm.
 ** May not fit some #2 AWG compact 133% (220 mil) insulated power cables. Check minimum insulation diameter to confirm.
 *** May not fit some 350 kcmil compact 100% (175 mil) insulated power cables. Check minimum insulation diameter to confirm.
 **** May not fit some 500 kcmil compact insulated power cables. Check minimum insulation diameter to confirm.

CSH Series

Cold Shrink Hammerhead
 PRODUCT GUIDE



15/25 kV Class



CSH Series

INTRODUCTION & PRODUCT RATINGS

A proven design. A game-changing transformation.

For over 70 years, Richards has remained dedicated to manufacturing high-quality, innovative products for electrical distribution systems. The Cold Shrink Hammerhead epitomizes this legacy by introducing a truly unique, robust solution for terminating and splicing medium voltage power cable. We've taken our industry-leading 600/900 A Deadbreak Elbow design and given it a cutting-edge transformation.

- **All-In-One Solution:** The CSH is range-taking and includes an integral jacket seal, providing a complete solution in a simple package. Three separate components have been elegantly combined into a single design.
- **100% EPDM:** Richards Cold Shrink Products are molded from 100% EPDM, a proven material in underground electrical applications for decades. This proprietary formulation of Cold Shrink EPDM is produced in-house. To achieve maximum durability in underground environments, the CSH features a fully-integrated, oil-resistant EPDM jacket that provides outstanding mechanical impact/tear resistance.
- **Easy Installation:** We've optimized our design to minimize installation time, complexity, and overall cost. No more cable adapter and no more separate jacket seal kit. The cold shrink Cable Entrance eliminates problems that arise when sliding traditional interference-fit Deadbreak elbows into position. This ergonomic improvement substantially simplifies positioning/aligning the lug in the CSH housing.
- **Designed, Molded & Tested in the USA:** Our team is intimately involved in everything from material development, product and mold design, and production. This allows us to control every aspect of the design, down to the smallest detail.

To Schedule a Demonstration
Contact Your Local Sales Rep



IEEE 386 Interface

EPDM Jacket

Conductor Lugs

Capacitive Test Point

Cable Entrance

Easy-to-Remove Core

Integral Jacket Seal

CSH Series

DESIGN & FEATURES



IEEE 386 - Industry Minimum Requirements

For your reference, IEEE ratings are provided below. Many of our products exceed these ratings. For product-specific information, see appropriate Product Data Sheet or contact the factory.

Voltage Ratings		
Voltage Class, Phase-to-Phase	15 kV	25 kV
Maximum Operating Voltage – (phase-to-ground)	8.3 kV	15.2 kV
Corona Voltage Level – (partial discharge extinction voltage)	11 kV	19 kV
AC Withstand – (1 minute)	34 kV	40 kV
Impulse-Withstand Voltage – (BIL)	95 kV	125 kV

Continuous Current Ratings	
Aluminum	600 A
Copper	900 A

Short-Time Current Ratings	
Aluminum	25 kA, 10 c. and 10 kA, 3 s.
Copper	40 kA, 10 c. and 10 kA, 3 s.

OUR TESTING EXCEEDS INDUSTRY REQUIREMENTS. IEEE REQUIRES PARTIAL DISCHARGE PLUS A CHOICE OF AC OR IMPULSE WITHSTAND. RICHARDS RUNS ALL THREE TO ENSURE THE HIGHEST QUALITY.

Designed and tested per the following industry standards:

- IEEE Std 386: For Separable Insulated Connector Systems
- IEEE Std 592: For Semiconducting Shields

1. Conductor Lugs

The CSH Series is available with a variety of conductor lugs. We offer a range-taking shear bolt option as well as the traditional 600 or 900 A compression connector. One of the most impressive improvements of the CSH is the ease with which the housing can be installed onto the prepared cable/installed lug. Without having to overcome any interference-fit (remember, we've obsoleted the cable adapter), positioning the lug properly is incredibly easy.

2. IEEE 386 Interface

This 600/900A 15/25kV Deadbreak interface accepts IEEE 386 Interface 11 components, such as Apparatus Bushings, Elbow Tap Plugs, Hammerhead Insulating Plugs (HIPs) and more.

3. Capacitive Test Point

The CSH Series is available with an optional capacitive test point. This enables system operators to utilize suitable equipment to test for voltage, or install a faulted circuit indicator (FCI).

4. EPDM Jacket

The entire CSH Series is molded from a proprietary EPDM formulation. This material has excellent mechanical impact/tear resistance—an important trait given the often harsh conditions of the underground environment. The bonded outer jacket is semi-conductive, making the CSH fully shielded.

5. Cable Entrance

The Cable Entrance of the CSH is shrinkable, obsoleting the cable adapter. This eliminates the performance risk associated with cable adapter positioning and makes installation markedly more ergonomic. This cold shrink Cable Entrance also allows the CSH to cover a range of cable sizes, as laid out in our Use Range-CSH Table. With fewer components and range-taking capabilities, customers are able to reduce inventory.

6. Easy-to-Remove Core

Hold-out cores that rely on grease or a ribbon/spiral design can be unreliable and messy. Spiral holdouts can be difficult to remove and may prematurely collapse. Richards product development engineers created a compact core design that is easy to eject, and performs consistently across a variety of installation environments. Once ejected, the Core separates into halves which can be recycled.

7. Integral Jacket Seal

Once the core is removed, a jacket seal is deployed over sealing mastic, completing the jacket restoration without the need for a separate component.