

# 3M™ PPS™ Paint Preparation System Size Guide




## 3M™ PPS™ Kit Mini Size – 1 vehicle panel repair

**3M™ PPS™ Kit Mini Size  
PN 16114**  
180ml full diameter  
200 micron filters

**3M™ PPS™ Kit Mini Size  
PN 16752**  
180ml full diameter  
125 micron filters



Ideal for smart repairs and small areas that require 180ml of material or less, e.g. 1 vehicle panel




## 3M™ PPS™ Kit Midi Size – 2 vehicle panels repair

**3M™ PPS™ Kit Midi Size  
PN 16112**  
400ml full diameter  
200 micron filters

**3M™ PPS™ Kit Midi Size  
PN 16312**  
400ml full diameter  
125 micron filters



Ideal for areas that require 400ml of material or less, e.g. 2 vehicle panels




## 3M™ PPS™ Kit Standard Size – 3 vehicle panels repair

**3M™ PPS™ Kit Standard Size  
PN 16000**  
650ml full diameter  
200 micron filters

**3M™ PPS™ Kit Standard Size  
PN 16026**  
650ml full diameter  
125 micron filters



Ideal for large areas that require 650ml of material or less, e.g. 3 vehicle panels



## 3M™ PPS™ Kit Large Size – 4 vehicle panels repair

**3M™ PPS™ Kit Large Size  
PN 16024**  
850ml full diameter  
200 micron filters

**3M™ PPS™ Kit Large Size  
PN 16740**  
850ml full diameter  
125 micron filters



Ideal for large jobs that require 850ml of material or less, e.g. 4 vehicle panels

