


GLASS OD DIAGONAL: 1475.3 [58.08]
 VIEW AREA DIAGONAL: 1391.0 [54.76]

| | | |
|----------------|----------------|--------------|
| CONTROLLER SKU | SENSOR SKU | PRODUCT SPEC |
| 98-1100-0943-2 | 98-1100-0918-4 | TSD-48013 |



SENSOR FRONT

- NOTES:
1. CONTROLLER LOCATION DEPENDENT ON INDIVIDUAL TAIL LENGTHS BEING ABLE TO REACH RESPECTIVE CONNECTORS AND OTHER INTEGRATION DEPENDENCIES.
 2. FINISH: NONE.
 3. PLEASE READ, UNDERSTAND AND FOLLOW THE INTEGRATION AND SAFETY GUIDE AT WWW.3M.COM/TOUCH.

| | |
|---------------------------------------|------------------|
| UNITS | MILLIMETERS [IN] |
| TOLERANCES UNLESS OTHERWISE SPECIFIED | |
| .X | ±.5 |
| .XX | ±.30 |
| .XXX | ±- |
| ANGLES | ±1° |
| THIRD ANGLE PROJECTION | |
| DO NOT SCALE DRAWING | |
| SCALE | 1 = 1 |

3M 3M TOUCH SYSTEMS
 METHUEN, MA
 USA
 © COPYRIGHT 2017
 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.

DRAWN MTD 1/9/17

| | | | |
|-------------------|-----------------------|-------|--------|
| B | REVISE PER CO 041414 | 4/17 | SB |
| A | RELEASE PER CO 041132 | 1/17 | MTD |
| REV | CHANGE NOTICE | DATE | DRW |
| TITLE | | | |
| MARKETING DRAWING | | | |
| PCT4003 54.76 W D | | | |
| CAD FORMAT | AUTOCAD | SHEET | 1 OF 1 |
| SIZE | DOCUMENT NO. | REV | |
| E | TSD-50165 | B | |