


CONTROLLER SKU	SENSOR SKU	PRODUCT SPEC
98-1100-0951-5	98-1100-0924-2	TSD-48013

GLASS OD DIAGONAL: 1139.5 [44.86]
VIEW AREA DIAGONAL: 1083.3 [42.65]



SENSOR FRONT

- NOTES:
1. CONTROLLER LOCATION DEPENDENT ON INDIVIDUAL TAIL LENGTHS BEING ABLE TO REACH RESPECTIVE CONNECTORS AND OTHER INTEGRATION DEPENDENCIES.
 2. FINISH: NONE
 3. PLEASE READ, UNDERSTAND AND FOLLOW THE INTEGRATION AND SAFETY GUIDE AT WWW.3M.COM/TOUCH.

UNITS	MILLIMETERS [IN]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	±.5
.XX	±.30
.XXX	±
ANGLES	±1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE	1 = 1

3M 3M TOUCH SYSTEMS
METHUEN, MA
USA

© COPYRIGHT 2017
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.

DRAWN	AH	1/17
SCALE	1 = 1	

B	REVISE PER CO 041414	4/17	SB
A	RELEASE PER CO 041189	1/17	AH
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING PCT4003 42.65 W D			
CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE	DOCUMENT NO.	REV	
E	TSD-50215	B	