




GLASS OD DIAGONAL: 1340.6 [52.78]
 VIEW AREA DIAGONAL: 1237.5 [48.72]

CONTROLLER SKU	SENSOR SKU	PRODUCT SPEC
98-1100-0951-5	98-1100-0931-7	TSD-48013



SENSOR FRONT

- NOTES:
1. CONTROLLER LOCATION DEPENDENT ON INDIVIDUAL TAIL LENGTHS BEING ABLE TO REACH RESPECTIVE CONNECTORS AND OTHER INTEGRATION DEPENDENCIES.
 2. FINISH: NONE.
 3. PLEASE READ, UNDERSTAND AND FOLLOW THE INTEGRATION AND SAFETY GUIDE AT WWW.3M.COM/TOUCH.

UNITS	MILLIMETERS [IN]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	±.5
.XX	±.30
.XXX	±-
ANGLES	±1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE	1 = 1

3M 3M TOUCH SYSTEMS
 METHUEN, MA
 USA

© COPYRIGHT 2017
 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.

DRAWN A. Hartofelis 1/17

B	REVISE PER CO 041414	4/17	SB
A	RELEASE PER CO 041197	1/17	AH
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING PCT4003 48.72 W D			
CAD FORMAT AUTOCAD		SHEET 1 OF 1	
SIZE E	DOCUMENT NO. TSD-50259	REV B	