

3M™ Trizact™ Diamond Edge Finishing Sheet 678XATD2S and 3M™ Trizact™ Diamond Edge Finishing Sheet 678XAEL TD2

Product Description

3M™ Trizact™ Diamond Edge Finishing Sheet 678XATD2S and 3M™ Trizact™ Diamond Edge Finishing Sheet 678XAEL TD2 are diamond abrasives with adhesive backing for glass and ceramic edge finishing.

Key Features

- Fast, consistent cut rates
- Fine finish
- Slurry-free finishing (only water-based coolant needed)
- Helps reduce downstream polishing time
- Includes pressure sensitive adhesive (PSA) for tool making

Applications: Edge Finishing

- Glass
- Silicon Carbide
- Sapphire
- Zirconia
- Ceramics

Application Techniques

- Trizact sheet 678XATD2S and Trizact sheet 678XAEL TD2 is used to make edge finishing tools

Typical Physical Properties and Performance Characteristics

- Mineral size not disclosed
- Cut rate and surface finish dependent on substrates and process conditions
- Recommended abrasive speed less than 900 surface feet per minute (sfpm)

Storage and Shelf Life

The shelf life of Trizact sheet 678XATD2S and Trizact sheet 678XAEL TD2 is 24 months from the date of manufacture when stored in the original packaging materials and stored in humidity controlled storage at 10°C/50°F to 30°/86°F and 30-60% relative humidity.

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is manufactured and deemed commercially available from 3M. The COA contains the 3M test methods, specifications limits and test results for the product's performance attributes that the product will be supplied against. Contact your local 3M representative for this product's COA.

3M™ Trizact™ Diamond Edge Finishing Sheet 678XATD2S and 3M™ Trizact™ Diamond Edge Finishing Sheet 678XAEL TD2

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE.** If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Materials Solutions Division
3M Center, Building 224-3N-11
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M and Trizact are trademarks of 3M Company.
Please recycle.
©3M 2021. All rights reserved.
60-5005-0121-2