



361 Glass Cloth Tape

Product Data Sheet

Updated : September 2022
Supersedes : March 1996

Product Description

White woven glass cloth provides good tensile strength with all the ageing properties of glass. The silicone adhesive coating gives good adhesion properties and high temperature performance.

Physical Properties

Not for specification purposes

Adhesive Type	Thermosetting silicone.	
Backing	Glass cloth.	
Thickness (ASTM D-3652)	180 µm	
Tape Colour	White	
Shelf Life	12 months from date of despatch by 3M when stored in the original carton at 21°C (70°F) & 50 % Relative Humidity	

Performance

Characteristics

Not for specification purposes

Adhesion to Stainless Steel ASTM D-3330	4.4 N/10mm	
Tensile Strength ASTM D-3759	233 N/10mm	
Elongation at Break ASTM D-3759	5.0 %	
Temperature Range Maximum Minimum	230 °C -55 °C	

Date : September 2022
361 Glass Cloth Tape

Additional Product Information

It will withstand intermittent temperatures up to 290°C or higher depending upon the type and duration of the heat source

Continuous exposure to temperatures above 230°C will gradually deteriorate the adhesive and darken the glass cloth backing.

361, when cured at high temperatures, has excellent resistance to solvents. A 24 hour cure at 260°C produces maximum solvent resistance.

Shelf life ageing is excellent for over one year under normal storage conditions.

On-the-job ageing is essentially permanent if the above temperature limitations are not exceeded.

Stain resistance to most metallic surfaces is excellent, but stain tests should be conducted if the tape application is not permanent.

Application Techniques

1. Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure develops better adhesive contact & thus improves bond strength.

2. To obtain optimum adhesion, the bonding

surfaces must be clean dry and well unified. A typical surface cleaning solvent is isopropyl alcohol & water. Use proper safety precautions for handling solvents.

3. Ideal tape application temperature range is 21°C to 38°C (70°F to 100°F).

Initial tape application to surfaces at temperatures below 10°C (50°F) is not recommended because the adhesive becomes too firm to adhere readily. However once properly applied low temperature holding is generally satisfactory.

Applications

All high temperature applications requiring high tensile strength and good holding power.

As a back-strip for submerged arc welding.

Permanent sealing of high temperature ducts or chambers.

Applications requiring heat treatment followed by clean removal of the tape with little or no stain.

Features

Glass Cloth.

Silicone adhesive.

Advantages

High temperature performance.
High tensile strength.
Conformable.

High temperature performance.
Long ageing.
Good holding power.

Benefits

Provides permanent seal.

High productivity.

Date : September 2022
361 Glass Cloth Tape

Automotive Disclaimer

Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, including, but not limited to, automotive electric powertrain battery or high voltage applications. This product does not fully adhere to typical automotive design or quality system requirements, such as IATF 16949 or VDA 6.3. This product may not be manufactured in an IATF certified facility and may not meet a Ppk of 1.33 for all properties. The product may not undergo an automotive production part approval process (PPAP). Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's automotive application and for conducting incoming inspections before use of the product. Failure to do so may result in injury, death, and/or harm to property. No written or verbal statement, report, data or recommendation by 3M related to automotive use of the product shall have any force or effect unless in an agreement signed by the Technical Director of 3M's Automotive Division. Customer assumes all responsibility and risk if customer chooses to use this product in an automotive electric powertrain battery or high voltage application, and 3M will not be liable for any loss or damage arising from or related to the 3M product or customer's use of the product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity or recall costs), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. In no event shall 3M be liable for any damages in excess of the purchase price paid for the product.

NOTWITHSTANDING ANY OTHER STATEMENT TO THE CONTRARY, 3M MAKES NO REPRESENTATIONS, WARRANTIES OR CONDITIONS WHATSOEVER, EXPRESS OR IMPLIED, REGARDING THE PRODUCT IF USED IN AN AUTOMOTIVE ELECTRIC POWERTRAIN BATTERY OR HIGH VOLTAGE APPLICATION, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY ON PERFORMANCE, LONGEVITY, SUITABILITY, COMPATIBILITY, OR INTEROPERABILITY, OR ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.

3M is a trademark of the 3M Company.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications.

This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.



Industrial Adhesives & Tapes Division
3M Belgium
Hermeslaan 7
1831 Diegem
Belgium

Industrial Adhesives & Tapes Division
3M Nederland
Molengraafsingel 29
2629 JD Delft
Nederland