



Aluminium Foil Tape 425 & 427

Product Data Sheet

August 2015
Supersedes: April 2008

Product Description

3M™ Aluminium Foil Tapes 425 and 427 are 70µm nominal dead soft aluminium foil backings combined with a transparent acrylic adhesive.

3M™ Aluminium foil tape 427 offers an easy-release liner.

Key Features

- The very low moisture vapour transmission rate makes these tapes a good sealant.
- The acrylic adhesive, combined with the durable aluminium backing, offers ideal properties for long serviceable life in and outdoors.
- Good candidate as a maskant in electroplating of aluminium because it will not contaminate the bath.
- Aluminium backing provides good reflection of both, heat and light.
- Best results obtained when applied to a clean, dry surface above 0°C.

Physical Properties

Adhesive Type	Acrylic
Thickness (ASTM D-3652)	
Backing	0,07 mm
Adhesive layer	0,05 mm
Total tape thickness w/o liner	0,12 mm
Easy-Release Liner for tape 427	0,08 mm
Tape Colour	Shiny silver

Performance Characteristics

	425	427
Adhesion to Stainless Steel Aluminium foil tape 425 (ASTM D- 3330)	51N/100mm	55N/100mm
Approximate Weight	238 g/m ²	
Water Vapour Transmission Rate (ASTM D- 3833)	0,2 g/m ² /24hrs.	
Tensile Strength (ASTM-D-3759)	490 N/100mm	490 N/100mm
Elongation at Break (ASTM D-3759)	6%	6%
Temperature Use Range	-55°C-150°C	

Application ideas

- Aircraft paint stripping maskant
- Moisture barrier in “white goods” appliances.
 - General purpose heat reflector and heat dissipater
 - Mechanically hold wires and cooling coils in “white good” appliances.
 - Repair tears on trucks trailers and aircraft.
 - Splicing of thin gauge foils.
 - General purpose holding, patching, sealing application – indoors and out.

Certifications

- Flame resistant. Meets U.L. 746 (File E 122798) and 723, Class “L” low flammability rating (file 7311)
- 3M™ Aluminium Foil Tape 425 can be certified to meet SAE-AMS-T 23397, L-T-80C and ABS 5604.
- Meets requirements of F.A.R. 25.853(a).

Storage

Store under normal conditions of 16°C - 27°C and 40-60% relative humidity in the original carton.

Shelf Life

To obtain best performance, use this product within 24 months from date of manufacture.

For Additional Information

To request additional product information or to arrange for sales Assistance, go to www.3M.be/bonding or www.3M.nl/bonding

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of 3M Company.



Industrial Adhesives & Tapes Division
3M Belgium
Hermeslaan 7
1831 Diegem
Belgium

Industrial Adhesives & Tapes Division
3M Nederland
Molengraafsingel 29
2629 JD Delft
Nederland