



3M Science.
Applied to Life.™

**Trusted by generations
of electrical professionals.**

3M™ Electrical Tapes Product Guide


Use the right stuff.

3M™ Electrical Tapes

3M has been developing and manufacturing high performance, easy handling electrical tapes since the 1940s. The 3M Electrical Tapes range includes tapes for low and medium voltage insulating, colour coding, moisture sealing, padding, shaping, protective jacketing, bundling, and harnessing.

Technical Applications

- > Semi-conducting tape to reconstruct a medium voltage cable
- > Track resistant tapes for terminations
- > Fire retardant electric arc proofing tapes to protect cables from arcs and fires from nearby cable failures



Taping Tips

To ensure the safest, most reliable use of PVC Electrical Tapes, always:

- > Apply tape with enough stretch to conform to the objects you're wrapping. Be sure to let the last 50 mm relax before tabbing it down to prevent unwinding (sometimes called "flagging").
- > Wrap an irregular mechanical connector, such as a split bolt, with rubber or mastic tape to pad sharp edges, before overwrapping with vinyl electrical tape.
- > Wrap tapered shapes "uphill" – that is, from the smallest to the largest point. This way you always secure the previous layer.
- > Always use scissors or a knife to cut tape. If you must tear it by hand, then keep fingers close together when tearing tape. The farther apart they are, the more the tape will stretch before it tears.
- > Use the right tape for the right conditions. Vinyl tapes are rated for cold weather application in two classes: 0°C and -18°C. Tapes formulated for high temperature environments are typically rated 80°C or 105°C. Only professional grade tapes should be used on cables rated for less than 0°C and higher than 80°C.
- > Wrap weather exposed vertical cables from the bottom up so water will run down without stopping on the tape edges









Wrapping Tips





Type of Tape		Number of Layers/Application Instructions
Vinyl Electrical Tapes	Jacketing and Mechanical Protection	Always use a minimum of two half-lapped layers. The last layer should be wrapped in a more relaxed manner – let the last wrap relax to prevent the layer from flagging.
Rubber Tapes	Electrical Insulation, Mechanical Padding, Water Sealing and Shaping	Wrap tape tightly to achieve the watertight seal. Rubber tapes are typically overwrapped with vinyl tape.
High Voltage Tapes	Insulating and Semi-conductive Layers	Apply outside of roll to the cable, in highly stretched half-lapped layers. Never use a semi-conductive tape as an insulation.
Mastic Compounds	Insulating, Mechanical Padding, Moisture Sealing and Shaping	Overwrapping with vinyl prevents mastic flow and helps to create a watertight seal. Do not apply excessive amount of mastic to prevent oozing.



PVC Electrical Tapes






Tapes		Product Description/Applications	Thickness	Temp. Range	Roll Size
Scotch® Super 33+™ Professional Grade Vinyl Electrical Tape		Highly conformable, super stretchy in all weather applications; resists UV rays, abrasion, corrosion, alkalis and acids. Applications include primary insulation for splices up to 600V and protective jacketing. This tape is CSA certified and UL listed.	0.18 mm	-18°C to 105°C	19 mm x 20 m 19 mm x 33 m 25 mm x 33 m
Scotch® Heavy Duty Grade Vinyl Electrical Tape Super 88		All weather; heavy duty, professional use, abrasion resistant, fast build up. Applications include primary insulation for splices up to 600V and protective jacketing. This tape is CSA certified and UL listed.	0.22 mm	-18°C to 105°C	19 mm x 20 m 19 mm x 33 m 25 mm x 33 m
Scotch® Professional Grade Color Coding Vinyl Electrical Tape 35		Nine fade-resistant colors, super stretchy and conformable, excellent insulating properties. Resists abrasion, corrosion, alkalis and acids. Applications include harnessing, phase identification and marking. Available in a range of colours including blue, green, red, white, yellow, brown, violet, grey and pink. This tape is CSA certified and UL listed.	0.18 mm	0°C to 105°C	19 mm x 20 m
Scotch® Extra Heavy Duty Grade Vinyl Electrical Tape 22		Thicker for increased mechanical strength and abrasion resistance. Applications include electrical insulating, bus bar insulation and cable jacket repair. This tape is CSA certified and UL listed.	0.25 mm	-10°C to 80°C	19mm x 33 m 25 mm x 33 m 38 mm x 33 m 50 mm x 33 m
3M™ Temflex™ General Purpose Vinyl Electrical Tape 1610		Economical, flexible, general purpose tape with in a range of colours including white, red, blue, yellow/green, black, grey, orange and brown. Typical applications include phase identification, colour coding and harnessing.	0.15 mm	0°C to 80°C	19 mm x 20
3M™ General Use PVC Electrical Tape 1710N		Flexible, flame retardant, general purpose tape with good cool temperature adhesion. Available in a range of colours including white, red, blue, green, yellow, yellow/green and black. The tape is CSA certified and UL listed. Typical applications include protective jacketing, identification, colour coding, harnessing, bundling and mechanical protection.	0.18 mm	0°C to 80°C	18 mm x 20 m

Splicing and Insulating Tapes



Tapes	Product Description/Applications	Thickness	Temp Range	Roll Size
Scotch® Professional Grade Linerless Rubber Splicing Tape 130C 	High and low voltage insulating; thermally conductive; self-bonding. Primary electrical insulation for splicing all solid dielectric cables through 69kV.	0.76 mm	continuous: 90°C short-term: 130°C	19 mm x 9 m 25 mm x 9 m 38 mm x 9 m
Scotch® Professional Grade Lined Rubber Splicing Tape 23 	High and low voltage insulation, self-fusing rubber tape. Primary electrical insulation for splicing all solid dielectric cables through 69kV.	0.76 mm	continuous: 90°C short-term: 130°C	19 mm x 9 m 25 mm x 9 m 38 mm x 9 m
3M™ Temflex™ Rubber Splicing Tape 2155 	Economical low voltage rubber insulating tape; self-fusing. Insulating wire splices, split bolt connections and motor leads up to 600V.	0.76 mm	80°C	19 mm x 6.7 m
Scotch® Professional Grade Semi-Conducting Tape 13 	Semi-conductive rubber tape. Compatible with cable semi-conducting jackets. Electrically round high voltage connections. Provide cable shield continuation.	0.76 mm	continuous: 90°C short-term: 130°C	19 mm x 4.5 m
Scotch® Professional Grade Silicone Rubber Tape 70 	Arc and track resistant; self fusing, long lasting silicone rubber. Applications include protective overwrap for terminating high voltage cables against arcing and tracking.	0.30 mm	180°C	25 mm x 9 m
Scotch® Varnished Cambric Professional Grade Tape 2510 and 2520 	Yellow, varnish coated cotton cloth 2510: no adhesive; 2520: adhesive. Insulate bus bars, motor leads (for re-entry), service drop connections.	2510 is 0.18 mm 2520 is 0.20 mm	105°C	2510: 25 mm x 33 m 50 mm x 33 m 2520 19 mm x 18 m 19mm x 33 m 38 mm x 33 m 25 mm x 33 m 51 m x 33m
Scotch® Glass Cloth Tape 27 and 69 	Woven insulating glass cloth; high temperature resistance; high mechanical strength. Heat-stable insulation for furnace and oven controls, motor leads and switches. Both tapes are CSA certified and UL listed.	0.177 mm	27 is class B temp (150°C) 69 is class H temp (200°C)	27: 12.7 mm x 20 m 19 mm x 20 m 25 mm x 55 m 69: 12.7 mm x 33 m 19 mm x 33 m 25 mm x 33 m



Sealing and Insulating Tapes










Tapes		Product Description/Applications	Thickness	Temp. Range	Roll Size
Scotch® Professional Grade Rubber Mastic Sealing Tape 2228		Self-fusing rubber based compound bonded to a moisture sealing mastic; all weather. Insulate, pad and seal bus bar and splice connections up to 35 kV.	1.6 mm	90°C emergency overload of 130°C	25 mm x 3 m 50 mm x 3 m
3M™ Scotch-Seal™ Professional Grade Mastic Sealing Tape 2229		Conformable and durable mastic. Excellent moisture and environmental seal. Sealing low and high voltage cables and accessories.	3.2 mm	90°C	25 mm x 3m 95 mm x 3 m
Scotch® Cable Jacket Repair Professional Grade Tape 2234		Tough, black, abrasion and chemical-resistant backing laminated to a moisture sealing mastic for jacket repair on industrial cables.	1.5 mm	105°C	50 mm x 1.8 m
3M Scotchfil® Electrical Insulation Putty		Self-fusing, insulating putty in tape form. Smooths over irregular shapes and pads sharp edges.	3.2 mm	80°C	38 mm x 1.5 m
Scotch® Heavy Duty Mining Professional Grade Tape 31		Tough, abrasion-resistant backing laminated to a moisture sealing mastic for jacket repair on mining cables. MSHA-approved.	1.5 mm (60 mil)	105°C	50 mm x 2.6 m

Corrosion Protection Tapes

Tapes		Product Description/Applications	Thickness	Temp. Range	Roll Size
3M™ Scotchrap™ Professional Grade Corrosion Protection Tape 50		All-weather performance and corrosion resistance. Resistant to impact and abrasions. Corrosion protection on pipes, conduits and fittings, etc.	0.25 mm (10 mil)	80°C	25 mm x 30 m 50 mm x 30 m 100 mm x 30 m 150 mm x 30m
3M™ Scotchrap™ Professional Grade Pipe Primer		Quick-dry, non-sag rubber base primer that prepares metal surfaces for tape application. For use with 3M Scotchrap tapes 50.	N/A	80°C	3.79 liters



Special Use Tapes

Tapes		Product Description/Applications	Thickness	Temp. Range	Roll Size
Scotch® Thread Sealant and Lubricant Tape 48		Pipe thread sealant that provides a leak proof seal. Helps prevent cross threading on pipe threads.	0.076 mm	260°C	12.7 mm x 33 m
3M™ Temflex™ Cotton Friction Tape 1755		High grade friction tape. Good abrasion resistance. Abrasion protection for splices and connections. Wire bundling.	0.33 mm (13 mil)	80°C	19 mm x 18.3 m
3M™ Performance Plus Duct Tape 8979		Clean removal for up to 6 months outdoors. Moisture resistant. UV resistant backing for up to 1-year of outdoor exposure. Sealing, holding, bundling, reinforcing, identifying, tabbing, wrapping, paint masking, splicing and protecting.	0.31 mm (12 mil)	93°C	48 mm x 23 m 48 mm x 55 m 72 mm x 55 m
3M™ Heavy Duty Duct Tape 3939		Used for demanding duct tape applications. High tack adhesive for a good, quick stick to many surfaces. Conformable and moisture resistant backing that tears easily by hand. Sealing, holding, bundling, reinforcing, identifying, tabbing, wrapping, splicing and protecting.	0.22 mm (9 mil)	93°C	48 mm x 55 m
3M™ VHB™ RP45 Tape		Conformable, double sided, pressure sensitive, UV and water resistant with permanent bonding to most surfaces. Typical applications include washing machine touch panel, bonding, commercial vehicle roof vent attachment etc.	1.1 mm (43 mil)	Continuous 93°C and Emergency 121°C	12.7 mm x 5 m 19 mm x 5 m
3M™ Aluminium Foil Tape 425		Dead-soft aluminium foil backing and acrylic adhesive provide excellent heat and light reflection to protect against high temperatures and UV. Foil serves as an excellent barrier against moisture and dust. Ideal for harsh, long term outdoor environments.	0.12 mm (4.7 mil)	149°C	25 mm x 55 m 38 mm x 55 mm 50 mm x 55 m 75 mm x 55 m 96 mm x 55 m
Scotch® Professional Grade Shielding Tape 24		All metal open weave shielding braid, conformable, temperature stable. Applications include continuous electrostatic shielding across splice.	0.4 mm	130°C	25 mm x 4.5 m
Scotch® Professional Grade Grounding Braid 25		All metal woven braid; high current carrying capacity of 6 AWG wire (approx. 12 mm ²); solderable. Applications include conformable ground braid for splices and terminations.	2.38 mm	130°C	13mm x 4.5m
Scotch® Fire and Electric Arc Proof Professional Grade Tape 77 Black		Protects cable from arc and fire until limiting devices can interrupt faulted circuit. Use on high-energy cables that are within 500 mm of other high energy cables.	0.76 mm	-	38 mm x 6 m



Are you insulating, sealing, protecting or connecting?

Call the 3M Electrical Helpline

 **1800 3M ELEC**

**3M Electrical Products.
Use the right stuff.**

3M

3M Australia Pty Ltd
Electrical Markets Division
Bldg A, 1 Rivett Road
North Ryde NSW 2113

Phone 1800 3M ELEC
Email 3msafetyauucs@mmm.com
Web www.3M.com.au

3M New Zealand Ltd
Electrical Markets Division
94 Apollo Drive, Rosedale
Auckland 0632

Phone 0800 474 787
Email 3mnzitm@mmm.com
Web www.3M.com.nz

3M, Scotchfil, Scotchrap, Super 33+, Super 88+, Scotch-Seal, Tartan, VHB, Temflex, and Scotch are trademarks of 3M.
Please recycle. Printed in Australia.
© 3M 2018. All rights reserved.
AV011475074