




Relax... Success is guaranteed! 3M helps you to get ready... at every stage of your presentation preparation.


Choose the right tools to make a presentation



For more information and to check out compatibility with your printer/copier, please consult your dealer.



LOCAL ADDRESS
OR DISTRIBUTORS
ADDRESS



Relax...
Success is guaranteed!

Prepare your presentation

- Universal films 2
- Ink Jet 3
- Laser 4
- Copier 6


3M Innovation

How do you prepare your presentation?

Not sure?

CG6000 Universal film

Photocopier, Ink jet or Laser, the ONE that does it all




3M universal Transparency Film makes your presentation preparation easier!

- One film for most printers and copiers at your office
- Never jam your printer or copier again from using with the wrong type of film
- Only stock one type of film

Relax... brilliance is guaranteed! Box of 50 sheets

The 3 in 1 Transparency Film



Not compatible with Colour Copiers, B&W copiers requiring a sensing stripe on the long-edge and Apple12/660, Canon CLPB360, Lexmark Optra C

Relax...

Success is guaranteed!

How do you prepare your presentation?

Ink Jet printer

Colour Ink Jet Transparency films


The new quick-dry film from 3M: **CG3490**

Best solution

The brightest colours you can get out of your ink jet printer, whatever the make

- Professional Quality: the new Transparency Film specially designed for the latest generation of Ink Jet printers (still compatible with previous generation of printers).
- A real quick-dry film: slides won't stick to one another in the tray after print out.
- With the brightest colours, the best on-screen performance is guaranteed. Just print on the textured (rough) side of the film and remove the stripe after print out, it won't leave any mark or residue.


Relax... brilliance is guaranteed!



Should you prefer a transparency film specific to your ink jet printer, 3M has the answer!


HP Ink Jet printers: **CG3460**

- Brilliant vivid colours are guaranteed.
- Easy printing, no jamming: a sensing stripe allows optimal feed into your HP printer. Just remove the stripe after printing, it won't leave any mark or residue.



Other Ink Jet printer brands: **CG3420**

- Brilliant vivid colours are guaranteed.
- Universal for all printers that don't need any sensing stripe (Canon, Epson, Lexmark, etc.).



tips

Load your tray with the rough side up i.e. in case of CG3460, the feeding stripe leading and facing down.

Load your tray with the rough side down i.e. in case of CG3460, the feeding stripe leading and facing up.



How do you prepare your presentation?

Laser printer

Colour Laser Transparency films



In colour or Black & White, make astonishing presentations directly from your **LASER** printer with **3M™ Transparency Films**.

The new generation colour laser film: **CG3720**



The brightest colours you can get out of most colour laser printers (printers that don't require films with stripe).

- Professional Quality: the new Transparency Film specially designed for the latest generation of Laser printers (still compatible with previous generation of printers).
- Bright on screen images to attract your audience.
- Feed easily your printer as CG3720 can be imaged on either side.


Relax... brilliance is guaranteed!



Should you prefer a transparency film specific to your colour laser printer, 3M has the answer! Check out the compatibility!

Printers requiring plain films (HP and others): **CG3700**

- Compatible with HP printers (and also Brother, Epson, QMS, Toshiba, etc).
- Brilliant vivid colours guaranteed.
- Feed easily your printer as CG3700 can be imaged on either side.



Printers requiring films with sensing stripe: **CG3710**

- Specially designed for printers requiring a sensing stripe (Apple, Digital, Hitachi, IBM, Tektronic, Minolta, etc.)
- Brilliant vivid colours are guaranteed.
- For optimum results, print on the side without stripe.



Black & White Laser Transparency films



3M designed 2 types of films specific to your Black & White laser printers

CG3360

Paper-backed film for improved printing process (compatible with most B&W laser printers).

- Less distortion of the film as all the heat of the laser printer is absorbed by the paper
- Proof-read your slide after print-out thanks to the paper-backing. Paper will remove neatly afterwards.
- Sharp text and clear images are guaranteed!




CG3300

Clear Transparency Film compatible with most laser printers.

- Sharp text and clear images are guaranteed!
- Feed easily your printer as CG3300 can be imaged on either side.


Relax... best reading of your transparency is guaranteed!



tips

Remove the paper loaded in the tray, look for the symbol or load CG3710 with sensing stripe leading and facing down, or CG3360 with paper side facing down. load C3710 with sensing stripe leading and facing up, or CG3360 with paper side facing up.

Relax... Success is guaranteed!



Why choose 3M transparency films?



• **Full quality**
3M Transparency films and Flip-Frames are produced in Europe. Our Italian plant is highly automated and is ruled with strict quality control procedures.

• **Coating: 3M core competence**
A Transparency film is a piece of polyester (backing) coated with a special solution (coating) that attracts toner or absorbs ink. In this respect, 3M has 40 years of expertise and a promise of

innovation which is fulfilled thanks to 3M R&D team. Laboratory staff keep improving 3M product performance to answer to more changing market demand and technology.

• **Manufacturing from A to Z**
3M is one of the few fully integrated manufacturers in the world. Consistency in product performance is ensured thanks to 3M manufacturing itself from resin to finished goods in pallets.

How do you prepare your presentation?


Copier

Colour Copier Transparency films

Best solution

For high quality visuals: **PP2260**

- The best colours you can get out of your colour copier.
- Professional Quality: a high-tech film from 3M for full-colour copiers.
 - The brightest colours of all are guaranteed.
 - Copy on the side of the transparency Film without the stripe and remove the stripe afterwards, it won't leave any mark or residue.


Relax... brilliance is guaranteed!  Box of 50 sheets

For texts and graphics: **PP2280**

Transparency film compatible with most colour copiers for every day colour copy.

Compatible with most colour copiers sensing stripe to allow easy detection of the film in the printer. Just remove the stripe after printing, it won't leave any mark or residue!

- Brilliant colours are guaranteed.
- Copy on the side of the transparency Film without the stripe and remove the stripe afterwards, it won't leave any mark or residue.

Relax... success is guaranteed!  Box of 100 sheets



In colour or Black & White, make astonishing presentations directly from your COPIER with 3M™ Transparency Films.

t How to load your copier? tips

Refer to the instructions manual of your copier. Check out whether transparency films should be placed in a cassette or through the bypass feed tray.

Relax...
Success is guaranteed!

For more information and to check out compatibility with your printer/copier, please consult your dealer.

Black & White Copier Transparency films

3 families of films depending on your Black & White copier type:

- Copiers without any electronic paper detection system: use PP2500
- Copiers with an electronic paper detection system: use PP2410, PP2480 or PP2200 (read below)
- High-temperature copiers: use PP2950 (Check out copier manufacturer's instruction guide)

PP2500

The universal film for standard copiers without electronic paper detection


- Sharp text and clear images are guaranteed!
- Feed easily your copier as PP2500 can be imaged on either side.


 Box of 20 or 100 sheets

PP2410, PP2480, PP2200

Transparency films for Copiers with an electronic paper detection system

- PP2410 & PP2480, paper backed transparency film for proofreading of document after copy.

 PP2410, for long-edge feeding copiers (most of them), Box of 100 sheets


 PP2480 for short edge-feeding Paper can be removed neatly after copy Box of 100 sheets

 ■ PP2200, transparency film with a sensing stripe on long side which removes neatly after copy Box of 100 sheets

PP2950

Transparency film for hot copiers (check out "High-temperature" copiers list with your dealer)

- Thicker transparency film to avoid distortion caused by heat.
- Feed easily your copier as PP2950 can be imaged on either side.

 Box of 100 sheets

Caring for environment

• Responsible manufacturing:

3M is one of the few fully integrated manufacturer of Transparency Films in the world. The 3M plant is located in Italy. In its history, 3M has always been committed to responsible manufacturing and as such, the plant has been ISO 14001 certified since December 1999.

• **ISO 14001** certificate means industrial wastes are recycled, emission of pollutants are severely controlled and must be reduced; environmental friendly technologies have also been adopted. As an example, none of 3M transparency films contain ozone-depleting chemicals.

• **Less solvent:** to avoid rejecting solvents in the air after coating, 3M has developed alternative coating formulas (especially for copiers films). In this case, solvents are replaced by water: no chemicals are emitted and the performance of the Transparency Film stays the same.

