

3M™ Electrically Conductive Double-Sided Tape 9720

Product Description

3M™ Electrically Conductive Double-Sided Tape 9720 is a XYZ-electrically conductive pressure sensitive adhesive (PSA) tape. 3M tape 9720 consists of a conductive matrix carrier (nickel/copper-coated conductive nonwoven fabric matrix) that is electrically conductive and designed for PSA attachment to the desired grounding surfaces. This tape is an acrylic-based adhesive solution that offers high adhesion and good grounding performance to many surface types. 3M tape 9720 provides improved electrical performance and reliable small size contacts in a thicker format. 3M tape 9720 is useful for grounding, PSA attachment and EMI shielding designs.

Key Features

- XYZ-conductivity through the adhesive
- Excellent conformability and quick bonding
- Good EMI shielding in bond line gap
- Improved electrical contact to small size areas
- Good handling and workability
- Multiple thickness options

Product Construction/Material Description

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. The product is available in 500 mm x 100 meter. Contact your local 3M representative for more information.

3M™ Electrically Conductive Double-Sided Tape 9720	
Property	Value
Color	Face side: metallic gray Back side: metallic gray
Conductive adhesive type	Acrylic conductive adhesive
Release liner	Face side: PET release liner Back side: PET release liner

3M™ Electrically Conductive Double-Sided Tape 9720

Shielding Effectiveness

Many factors determine the shielding effectiveness of a conductive adhesive tape, including type and thickness of the conductive layers, adhesive strength, degree of contact, smoothness of application surface and test frequency. For 3M™ Electrically Conductive Double-Sided Tape 9720 the typical shielding effectiveness is expected to be in the range of 30 dB to 60 dB, using a standard EMI shielding test methods and through the thickness of the sample tested.

Applications

- For applications requiring excellent electrical conductivity from the application substrate through the adhesive to a second substrate
- Grounding and EMI shielding in equipment and components

Application Techniques

Note: Carefully read and follow the manufacturer's precautions and directions for use when working with solvents. Tape application below 10°C (50°F) is not suggested. Once properly applied, low temperature holding power is generally satisfactory.

The bond strength of 3M™ Electrically Conductive Double-Sided Tape 9720 depends on the amount of adhesive-to-surface contact developed during application and substrate type and surface conditions.

1. Firm application pressure helps develop better wet-out and adhesive contact and may lead to improved bond strength as well as electrical conductivity. Pressure must be applied to the bond area after assembly to ensure sufficient wet-out of the 3M tape 9720 adhesive to the substrates and to engage the conductive acrylic adhesive fillers with the substrates to make electrical connection. Mechanical pressure (roller, metal bar) or finger pressure at 5-15 psi. (Optimally the application conditions are determined via a set of Design of Experiments (DOE) using a range of application pressures, dwell time and temperatures (suggested initial range might include 5-15 psi, 2-5 seconds, 21°C-38°C).
2. Heat may be applied simultaneously with pressure to improve wetting, final bond strength and electrical conductivity. Suggested temperature range to evaluate is in the 38°C-60°C range.
3. To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Final product specifications and testing methods will be outlined in the product's Certificate of Analysis (COA) that is shipped with the product.

3M™ Electrically Conductive Double-Sided Tape 9720		
Property	Method ^a	Value
Thickness	ASTM D1000	35µm
Adhesion to SUS	ASTM D1000	1000 gf/inch
XY-axis electrical resistance through adhesive	3M Test Method ETM-7 ^b	0.3 Ω
Z-axis resistance through adhesive	3M Test Method ETM-12 ^c	0.1 Ω


^aMethods listed as ASTM are tested in accordance with the ASTM method noted

^{b,c}3M test methods as described below.

3M™ Electrically Conductive Double-Sided Tape 9720


3M Test Method ETM-7: XY-Axis Electrical Resistance through Adhesive^b

Place a strip of the single (double) side conductive tape in 10 mm x 50 mm with adhesive side down between the electrodes on 3M ETM-7 testing board. After initial hand lamination to provide for a 10 mm x 10 mm contact area between the tape and electrodes, apply a 2kg rubber roller across the tape one time. Application method simulates a typical manufacturing process that might be used to apply the tapes to a surface. After 20 minutes of dwell time, the DC resistance between the electrodes are measured with a micro-ohm meter. The resistance results are recorded after 5 ~ 30 seconds for initial resistance.



3M Test Method ETM-12: Z-Axis Electrical Resistance through Adhesive^c

Place conductive tape pieces in 10 mm x 10 mm on the center of the electrodes on 3M ETM-7 testing board. Then place 3M ETM-12 testing board with the gold-plated side down on the tapes between electrodes. After initial hand lamination to provide for a 10 mm x 10 mm contact area between the tapes and electrodes, apply 2 kg rubber roller across the tape one time. Application method simulates a typical manufacturing process that might be used to apply the tapes to a surface. After 20 minutes of dwell time, the DC resistance between the electrodes are measured with a micro-ohm meter. The resistance results are recorded after 5 ~ 30 seconds for initial resistance.



Typical Operating Temperature Range for Acrylic-Based Pressure Sensitive Adhesives (PSAs)

3M acrylic conductive pressure sensitive adhesives (CPSAs) contain conductive fillers. The grounding and/or substrate interconnection performance of the conductive fillers within the acrylic PSA in an application will vary based on many factors including substrate types, contact grounding area, surface geometry in the bond line, flexibility of substrates, bonding conditions, applied voltage/current, application environment and environmental aging conditions/exposure.

In general, the acrylic PSA polymer itself used in acrylic CPSAs have good short term and long term environmental stability with respect to the PSAs macro-adhesion performance to many substrates. The acrylic polymers typical long term (days-weeks) performance and short-term performance (minutes-hours) based on an adhesion test method is generally 85°C (185°F) long term and 121°C (250°F) short term.

3M CPSAs should be tested in the desired application to ensure the product is appropriate for use based on the application's specific requirements, including substrate types, contact grounding area, surface geometry in the bond

3M™ Electrically Conductive Double-Sided Tape 9720

line, flexibility of substrates, bonding conditions, applied voltage/current, application environment and environmental aging conditions/exposure.

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is commercially available from 3M. The commercially available product will have a COA specification established. The COA contains the 3M specifications and test methods for the products performance limits that the product will be supplied against. The 3M product is supplied to 3M COA test specifications and the COA test methods. Contact your local 3M representative for this product's COA.

This technical data sheet may contain preliminary data and may not match the COA specification limits and/or test methods that may be used for COA purposes.

Final product specifications and testing methods will be outlined in the products Certificate of Analysis (COA) that is shipped with the commercialized product.

Storage and Shelf Life

The shelf life of 3M™ Electrically Conductive Double-Sided Tape 9720 is 12 months from the date of manufacture when stored in the original packaging materials and stored at 21°C (70°F) and 50% relative humidity.

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, visit 3M.com/regs contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Materials Solutions Division
3M Center, Building 224-3N-11
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle.
©3M 2018. All rights reserved.
60-5005-0126-1