

**3M** Science.  
Applied to Life.™



# Three duct tapes that can do it all

3M™ DT Series Duct Tapes





# Be equipped for the day

Tackle your everyday tasks with 3M™ DT Series duct tapes in three strengths. They resist curling, have a consistent unwind and tear off the roll cleanly for the ultimate in ease of handling and application.

Enlarged photo to show unique texture of 3M™ Super Duty Duct Tape DT17.





# The rolls you always want to keep on hand

3M™ DT Series duct tapes offer hand tearability, high tensile strength and conformability.



**3M™ All Purpose  
Duct Tape DT8**

## *Conformable with instant bond*

Unique design offers high instant adhesion coupled with maximum conformability.



- Ideal for contoured surfaces and quick labelling
- Good tensile strength for light-duty bundling
- Use for poly abatement, quick repairs, splicing, temporary holding and fast attachments



**3M™ Heavy Duty  
Duct Tape DT11**

## *Versatility with holding power*

Good holding power with a broad attribute performance make this the go-to choice for demanding jobs.



- Sticks immediately and stays on irregular, hard-to-bond surfaces without lifting—even on most plastics
- Water-resistant, polyethylene backing resists wear and light abrasion—good for securing temporary floor coverings
- Moisture-resistant seal in many containment situations, such as pipe sealing and attaching heavy poly draping
- Low-tack roll edges so rolls stay cleaner



**3M™ Super Duty  
Duct Tape DT17**

## *Super thick for super tough jobs*

Ultra-thick, water-resistant backing resists wear and abrasion while still tearing easily by hand.



- Aggressive rubber adhesive grips instantly to a variety of surfaces including metal, glass, plastic and sealed concrete
- Excellent for repairing, seaming, extra-strength bundling and helps in protecting metal parts and surfaces against sandblast overspray
- Superior strength for the most demanding applications
- Low-tack roll edges so rolls stay cleaner

# Duct tape simplified

Three tapes in three strengths to tackle the bulk of your everyday duct taping tasks.

3M™ DT Series	Backing material	Adhesive type	Thickness (mils)	Tensile strength lb/in (n/100 mm)	Elongation at break %	Adhesion to steel oz/in (N/100 mm)	Temperature range up to 30 minutes	Instant adhesion	Roll size	Colour	UPC
Based on ASTM Test Method:			D-3652*	D-3759	D-3759	D-3330					
3M™ All Purpose Duct Tape DT8	Polyethylene over cloth scrim	Synthetic/natural rubber blend	8	24 (420)	19%	74 (81)	4°C-65°C (40°F-150°F)	✓	1.88" x 60 yds (48 mm x 54.8 m)	Silver	689330172252
										Black	689330178094
									1.88" x 25 yds (48 mm x 22.9 m)	Silver	689330173204
										Black	689330178704
3M™ Heavy Duty Duct Tape DT11	Polyethylene over cloth scrim	Synthetic/natural rubber blend	11	29 (508)	19%	88 (96)	4°C-65°C (40°F-150°F)	✓	1.88" x 60 yds (48 mm x 54.8 m)	Silver	689330172276
										Black	689330172283
									1.88" x 25 yds (48 mm x 22.9 m)	Silver	689330173211
										Black	689330173228
3M™ Super Duty Duct Tape DT17	Polyethylene over cloth scrim	Synthetic/natural rubber blend	17	38 (665)	18%	85 (93)	4°C- 65°C (40°F-150°F)	✓	1.88" x 35 yds (48 mm x 32 m)	Black	689330172290

\*ASTM D-3652 tested at 2.7 psi (18 kPa). To see the full line of 3M™ Duct Tapes and Cloth Tapes, including nuclear grade tape, refer to the 3M™ Masking and Surface Protection Design Guide. Additional colours are available.

**Warranty, Limited Remedy, and Disclaimer:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M Closure and Masking Systems Division

3M Canada  
P.O. Box 5757  
London, Ontario N6A 4T1  
1 800-364-3577  
3M.ca/DTSeries



- Patching
- Bundling
- Reinforcing
- Taping/splicing insulation
- Capping pipe
- Securing conduit ends
- Marking
- Labelling
- Performing temporary repairs
- Hanging polyethylene drapes
- Protecting against sandblast overspray

3M and 3M Science. Applied to Life. are trademarks of 3M. Used under license in Canada. © 2019, 3M. All rights reserved. 1812-13633 E